



THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF L-COM, INC. ANY REPRODUCTION IN PART OR WHOLE WITHOUT THE WRITTEN PERMISSION OF L-COM, INC. IS PROHIBITED.

REVISION					
ZONE	REV	DESCRIPTION	DATE	CHANGED BY	APPROVED
	A	INITIAL RELEASE	05/17/2023	SREITER	PHOSPODAR



INSERT CAP  
FACE VIEW

LABEL 1  
**FCA-M8-PLPLM2MT-XX**  
**MRF: 335J8**  
**SN: XXXXXXXXXXXXXXXXXXXXX**

END A	FIBER	END B
S1	BLUE	P1
S2	GREEN	P2
P1	ORANGE	S1
P2	BROWN	S2



PART NO.	FEET	METERS
FCA-M8-PLPLM2MT-10	32.8	10
FCA-M8-PLPLM2MT-30	98.4	30

**NOTES:**

- CABLE ASSEMBLY DELIVERED HAND COILED.
- FABRICATED, INSPECTED AND TESTED IN ACCORDANCE WITH IPC-A-640 CLASS 3.

**CABLE LENGTH TOLERANCE:**


- LESS THAN (OR EQUAL TO) 20FT: +6"
- GREATER THAN 20FT - 100FT: +12"
- GREATER THAN 100FT: +36"

<small>UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE IN INCHES [mm]</small> OVERALL CABLE LENGTH TOLERANCE: ≤12 [305] = +1 [25] / -0 >12 [305] ≤60 [1524] = +2 [51] / -0 >60 [1524] ≤120 [3048] = +4 [102] / -0 >120 [3048] ≤300 [7620] = +6 [152] / -0 >300 [7620] = +5% / -0 ALL OTHER DIMENSIONAL TOLERANCES: .X = ± .2 [5]   FRACTIONS ± 1/32 .XX = ± .02 [.5]   ANGLES ± 1° .XXX = ± .005 [1.3]	APPROVALS SREITER	DATE 05/17/2023	 an INFINITI® brand CATEGORY <b>CABLE ASSEMBLY</b>	50 High Street, West Mill, North Andover, MA 01845 USA. Phone: 1.800.341.5266 1.978.682.6936		
	CHECKED BY REVANGELIS	05/17/2023			PRODUCT DESCRIPTION COTS M83526 (TFOCA II EQUIVALENT) 83526/16 PLUG TO COTS 83526/16 PLUG, 4 CHANNEL, OM2 62.5/125/5.5mm TACTICAL CABLE, 10m	
THIRD-ANGLE PROJECTION 	CONFIGURATION DETAILS OF UNDIMENSIONED FEATURES MAY VARY	COLOR VARIATIONS MAY OCCUR	SIZE <b>A</b>	CAGE CODE <b>43321</b>	ITEM NO. <b>FCA-M8-PLPLM2MT-10</b>	REV. <b>A</b>
SCALE: NONE			CAD FILE: FCA-M8-PLPLM2MT-10.SLDDRW	SHEET 1 OF 2		

THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF L-COM, INC. ANY REPRODUCTION IN PART OR WHOLE WITHOUT THE WRITTEN PERMISSION OF L-COM, INC. IS PROHIBITED.

REVISION					
ZONE	REV	DESCRIPTION	DATE	CHANGED BY	APPROVED
	A	INITIAL RELEASE	05/17/2023	SREITER	PHOSPODAR

4 CHANNEL  
DISTRIBUTION – MIL-TAC CABLES



FIBER PERFORMANCE	
INDUSTRY STANDARD DESIGNATION	OM2 ISO/IEC 11801
CORE/CLADDING DIAMETER (µm)	50/125
NUMERIC APERTURE	0.20
WAVELENGTH (nm)	850/1310
SECONDARY BUFFER DIAMETER (µm)	900

MECHANICAL AND ENVIRONMENTAL	
IMPACT RESISTANCE TIA-455-25	1500 IMPACTS
CRUSH RESISTANCE TIA-455-41	1800 N/cm
OPERATING TEMPERATURE	-55°C TO +85°C
STORAGE TEMPERATURE	-70°C TO +85°C

INSTALLATION AND OPERATING CHARACTERISTICS		
	INSTALLATION	OPERATING
MAX TENSILE LOAD	1,800 N (400 lbs)	600 N (130 lbs)
MIN BEND RADIUS	5.5 cm (2.2 in)	2.8 cm (1.1 in)

CABLE CHARACTERISTICS	
JACKET COLOR	BLACK
JACKET MATERIAL	POLYURETHANE
CABLE DIAMETER	5.5 mm (0.22 in)

<p>UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE IN INCHES [mm]</p> <p>OVERALL CABLE LENGTH TOLERANCE:            ≤12 [305] = +1 [25] / -0            &gt;12 [305] ≤60 [1524] = +2 [51] / -0            &gt;60 [1524] ≤120 [3048] = +4 [102] / -0            &gt;120 [3048] ≤300 [7620] = +6 [152] / -0            &gt;300 [7620] = +5% / -0</p> <p>ALL OTHER DIMENSIONAL TOLERANCES:            .X = ± .2 [5]   FRACTIONS ± 1/32            .XX = ± .02 [.5]   ANGLES ± 1°            .XXX = ± .005 [.13]</p> <p>THIRD-ANGLE PROJECTION</p>	<p>APPROVALS</p> <p>DRAWN BY SREITER</p> <p>CHECKED BY REVANGELIS</p> <p>APPROVED BY PHOSPODAR</p>	<p>DATE</p> <p>05/17/2023</p> <p>05/17/2023</p> <p>05/17/2023</p>	<p><b>L-com</b> an INFINITI® brand</p> <p>80 High Street, West Mill, North Andover, MA 01845 USA. Phone: 1.800.341.5266 1.978.682.6936</p>	
	<p>CONFIGURATION DETAILS OF UNDIMENSIONED FEATURES MAY VARY</p>		<p>PRODUCT DESCRIPTION</p> <p>COTS M83526 (TFOCA II EQUIVALENT) 83526/16 PLUG TO COTS 83526/16 PLUG, 4 CHANNEL, OM2 62.5/125/5.5mm TACTICAL CABLE, 10m</p>	<p>CATEGORY</p> <p><b>CABLE ASSEMBLY</b></p>
	<p>COLOR VARIATIONS MAY OCCUR</p>	<p>SIZE</p> <p><b>A</b></p>	<p>CAGE CODE</p> <p><b>43321</b></p>	<p>ITEM NO.</p> <p><b>FCA-M8-PLPLM2MT-10</b></p>
	<p>SCALE: NONE</p>		<p>CAD FILE: FCA-M8-PLPLM2MT-10.SLDDRW</p>	<p>SHEET 2 OF 2</p>