


THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF L-COM, INC. ANY REPRODUCTION IN PART OR WHOLE WITHOUT THE WRITTEN PERMISSION OF L-COM, INC. IS PROHIBITED.

REVISIONS			
REV	DESCRIPTION	DATE	APPROVED
A	INITIAL RELEASE	04/24/17	R.CLARK
B	ECN9111;UPDATE DWG TO ALIGN WITH VENDOR PROVIDED DWG.	03/23/2018	B.ZHANG



PART NUMBER	LENGTH METERS [FEET]	TOLERANCE mm[INCHES]
MHD-MHD-05M	0.5[1.64]	+51/-0[+2/-0]
MHD-MHD-1M	1.0[3.28]	+51/-0[+2/-0]
MHD-MHD-2M	2.0[6.56]	+102/-0[+4/-0]
MHD-MHD-3M	3.0[9.84]	+102/-0[+4/-0]

NOTES:

1. CABLES ASSEMBLY SHALL BE 100% TESTED FOR CONTINUITY
2. CABLES SHALL BE 100% ELECTICALLY TESTED
 VOLTAGE TEST: DC 300V, 10ms
 INSULATION RESISTANCE: 5.0M ohm/min
 CONDUCTANCE RESISTANCE: 5.0 ohm/max
3. CABLE SHOULD BE CLEAN AND FREE OF OIL, FLASH, AND BURRS
4. CABLES SHALL BE INDIVIDUALLY PACKAGED IN A CLEAR POLYBAG WITH LPS-010-2 LABEL ON THE BAG

REGULATORY COMPLIANCE:
 CE 2011/65/EU (RoHS DIRECTIVE)

UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE IN INCHES [mm] OVERALL CABLE LENGTH TOLERANCE: ≤ 12 [305] = +1 [25] / -0 > 12 [305] ≤ 60 [1524] = +2 [51] / -0 > 60 [1524] ≤ 120 [3048] = +4 [102] / -0 > 120 [3048] ≤ 300 [7620] = +6 [152] / -0 > 300 [7620] = +3% / -0% ALL OTHER DIMENSIONAL TOLERANCES: .X = $\pm .2$ [5.08] .XX = $\pm .02$ [51] .XXX = $\pm .005$ [13]	APPROVALS DRAWN BY R.CLARK CHECKED BY B.GATES APPROVED BY B.GATES	DATE 4/20/2017 4/24/2017 4/24/2017	50 HIGH STREET NORTH ANDOVER, MA 01845			
	CATEGORY AUDIO VIDEO			PRODUCT DESCRIPTION CA MINI HD TO MINI HD M/M		
	PROJECTION 	CONFIGURATION DETAILS OF UNDIMENSIONED FEATURES MAY VARY COLOR VARIATIONS MAY OCCUR	SIZE A		FSCM NO. 43321	DWG. NO. MHD-MHD
	SCALE: NONE		CAD FILE: MHD-MHD.SLDDRW		SHEET 1 OF 1	