

THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF L-COM, INC. ANY REPRODUCTION IN PART OR WHOLE WITHOUT THE WRITTEN PERMISSION OF L-COM, INC. IS PROHIBITED.

REVISIONS			
REV	DESCRIPTION	DATE	APPROVAL
A	INITIAL RELEASE	10/2/13	D.GRIFFIN

TABLE	
FOBOS1S-M	9/125 MICRON SINGLEMODE OS1 OFNR (RISER) RATED SIMPLEX BEND-INSENSITIVE FIBER JACKET: PVC, 2.0mm JACKET COLOR: YELLOW

GENERAL CHARACTERISTICS FOR RISER RATED (OFNR) SIMPLEX FIBER CABLES

UL LISTING: UL1666

MINIMUM BEND RADIUS:  
INSTALLATION: 3.8 cm (1.5 in)  
OPERATING: 2.5 cm (1.0 in)

OPERATING TEMPERATURE: -40°C TO +85°C (-40° F TO +185° F)

STORAGE TEMPERATURE: -55°C TO +85°C (-67°F TO +185°F)

MAX. TENSILE LOAD:  
INSTALLATION: 300 N (67 LBS)  
OPERATING: 160 N (36 LBS)

OPTICAL PERFORMANCE: MAX ATTENUATION dB/km:  
1310 nm: 0.5 dB/km  
1550 nm: 0.5 dB/km



IMPACT RESISTANCE: 750 IMPACTS

CRUSH RESISTANCE: 500 N/cm

**THESE SPECIFICATIONS ARE SUBJECT TO CHANGE WITHOUT PRIOR NOTIFICATION.**

CABLE LENGTHS 50 METERS AND UNDER WILL BE SECURED WITH TWIST-TIES AND PACKAGED PER L-COM SPECIFICATION PS-0031.

CABLE LENGTHS OVER 50 METERS WILL BE SPOOLED WITH 5' PIGTAILS.

UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE IN INCHES [mm] OVERALL CABLE LENGTH TOLERANCE: ≤12 [305] = +1 [25] / -0 >12 [305] - 60 [1524] = +2 [51] / -0 >60 [1524] - 120 [3048] = +4 [102] / -0 >120 [3048] - 300 [7620] = +6 [152] / -0 >300 [7620] = +5% / -0% ALL OTHER DIMENSIONAL TOLERANCES: .X = .2 [5.08] .XX = .02 [51] .XXX = .005 [13]	APPROVALS	DATE	 45 BEECHWOOD DRIVE NORTH ANDOVER, MA 01845	
	DRAWN BY D. DESJARDIN	10/1/13		
PROJECTION 	CHECKED BY D. FRISIELLO	10/1/13	PRODUCT DESCRIPTION OS1 2mm SIMPLEX OFNR YLW	
	APPROVED BY D. GALLAGHER	10/2/13	SIZE <b>A</b>	FSCM NO. <b>43321</b>
CONFIGURATION DETAILS OF UNDIMENSIONED FEATURES MAY VARY		COLOR VARIATIONS MAY OCCUR		REV. <b>A</b>
SCALE: 1:1		CAD FILE: FOBOS1S-M.SLDRW		SHEET 1 OF 1