


THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF L-COM, INC. ANY REPRODUCTION IN PART OR WHOLE WITHOUT THE WRITTEN PERMISSION OF L-COM, INC. IS PROHIBITED.

REVISIONS			
REV	DESCRIPTION	DATE	APPROVED
A	INITIAL RELEASE	9/1/11	D.FRISIELLO
B	ECN 6415: REDRAWN FROM NEW 3D MODEL	9/18/12	D.FRISIELLO
C	ECN 6881: UPDATED FORMAT AND COMPLIANCE NOTE	6/7/13	D.DESJARDIN



MODEL NUMBER	COLOR
RJTLC6-WT	WHITE
RJTLC6-BLK	BLACK
RJTLC6-IV	IVORY

NOTES:
 MATERIAL:
 HIGH-IMPACT UL94V-0 THERMOPLASTIC.
 COLOR: (SEE TABLE)

PHYSICAL CHARACTERISTICS:
 COMPONENT CAN BE WIRED PER T568A OR T568B.
 CONTACT COMPATIBILITY: ACCOMMODATES 22 TO 24 AWG SOLID.
 OPERATING TEMPERATURE RANGE: -10 °C TO 60 °C.
 RATING: CATEGORY 6

COMPONENT SHALL BE INDIVIDUALLY PACKAGED IN ACCORDANCE WITH L-COM SPECIFICATION PS-0031.
 CABLE TIE SUPPLIED.

ALL DIMENSIONS ARE FOR REFERENCE ONLY.

REGULATORY COMPLIANCE:
 ROHS, CE

UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE IN INCHES [mm] OVERALL CABLE LENGTH TOLERANCE: ≤12 [305] = +1 [25] / -0 >12 [305] ≤60 [1524] = +2 [51] / -0 >60 [1524] ≤120 [3048] = +4 [102] / -0 >120 [3048] ≤300 [7620] = +6 [152] / -0 >300 [7620] = +5% / -0%	APPROVALS	DATE		45 BEECHWOOD DRIVE NORTH ANDOVER, MA 01845
	DRAWN BY D.FRISIELLO	8/12/11		CATEGORY
ALL OTHER DIMENSIONAL TOLERANCES: .X = ± .2 [5.08] .XX = ± .02 [51] .XXX = ±.005 [13]	CHECKED BY D.GUITADAURO	8/12/11	PRODUCT DESCRIPTION	
	APPROVED BY D.GALLAGHER	9/1/11	JACK CAT6 RJ45/TOOLLESS	
PROJECTION	CONFIGURATION DETAILS OF UNDIMENSIONED FEATURES MAY VARY	COLOR VARIATIONS MAY OCCUR	SIZE A	FSCM NO. 43321
			DWG. NO. RJTLC6	REV. C
			SCALE: NONE	CAD FILE: RJTLC6.SLDDRW
				SHEET 1 OF 1