


THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF L-COM, INC. ANY REPRODUCTION IN PART OR WHOLE WITHOUT THE WRITTEN PERMISSION OF L-COM, INC. IS PROHIBITED.

REVISIONS			
REV	DESCRIPTION	DATE	APPROVED
A	INITIAL RELEASE	08-02-2021	PHOSPODAR



PART NUMBER	DESCRIPTION
FOCASE2K1APC02-1	E2000 APC 2mm FIBER OPTIC PIGTAIL 1M
FOCASE2K1APC02-2	E2000 APC 2mm FIBER OPTIC PIGTAIL 2M
FOCASE2K1APC02-5	E2000 APC 2mm FIBER OPTIC PIGTAIL 5M
FOCASE2K1APC02-10	E2000 APC 2mm FIBER OPTIC PIGTAIL 10M
FOCASE2K1APC02-15	E2000 APC 2mm FIBER OPTIC PIGTAIL 15M

UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE IN INCHES [mm]

OVERALL CABLE LENGTH TOLERANCE:
 ≤ 12 [305] = +1 [25] / -0
 > 12 [305] ≤ 60 [1524] = +2 [51] / -0
 > 60 [1524] ≤ 120 [3048] = +4 [102] / -0
 > 120 [3048] ≤ 300 [7620] = +6 [152] / -0
 > 300 [7620] = +5% / -0


ALL OTHER DIMENSIONAL TOLERANCES:
.X = $\pm .2$ [5] | FRACTIONS $\pm 1/32$
.XX = $\pm .02$ [.5] | ANGLES $\pm 1^\circ$
.XXX = $\pm .005$ [.13]

THIRD-ANGLE PROJECTION

APPROVALS	DATE
DRAWN BY MVEERAPPAN	08-02-2021
CHECKED BY GIBACETA	08-02-2021
APPROVED BY PHOSPODAR	08-02-2021

CONFIGURATION DETAILS OF UNDIMENSIONED FEATURES MAY VARY

COLOR VARIATIONS MAY OCCUR



an INFINITO brand

50 High Street, West Mill,
North Andover, MA 01845 USA.
Phone: 1.800.341.5266
1.978.682.6936

CATEGORY		FIBER OPTICS	
PRODUCT DESCRIPTION			
E2000 APC 2mm fiber optic pigtail			
SIZE A	CAGE CODE 43321	ITEM NO. FOCASE2K1APC02	REV. A
SCALE: NONE		CAD FILE: FOCASE2K1APC02.SLDDRW	SHEET 1 OF 1