


THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF L-COM, INC. ANY REPRODUCTION IN PART OR WHOLE WITHOUT THE WRITTEN PERMISSION OF L-COM, INC. IS PROHIBITED.

**RoHS Compliant** ✓

REVISIONS			
REV	DESCRIPTION	DATE	APPROVED
A	INITIAL RELEASE	7/17/12	D.GRIFFIN



FPT9OM2-LC-12PK-1			FPT9OM2-LC-12PK-2			FPT9OM2-LC-12PK-3		
PART NUMBER	LENGTH M [FT]	COLOR	PART NUMBER	LENGTH M [FT]	COLOR	PART NUMBER	LENGTH M [FT]	COLOR
FPT9OM2-LC-BLK-1	1.0 [3.28]	BLACK	FPT9OM2-LC-BLK-2	2.0 [6.56]	BLACK	FPT9OM2-LC-BLK-3	3.0 [9.84]	BLACK
FPT9OM2-LC-ORG-1	1.0 [3.28]	ORANGE	FPT9OM2-LC-ORG-2	2.0 [6.56]	ORANGE	FPT9OM2-LC-ORG-3	3.0 [9.84]	ORANGE
FPT9OM2-LC-YLW-1	1.0 [3.28]	YELLOW	FPT9OM2-LC-YLW-2	2.0 [6.56]	YELLOW	FPT9OM2-LC-YLW-3	3.0 [9.84]	YELLOW
FPT9OM2-LC-GRY-1	1.0 [3.28]	GRAY	FPT9OM2-LC-GRY-2	2.0 [6.56]	GRAY	FPT9OM2-LC-GRY-3	3.0 [9.84]	GRAY
FPT9OM2-LC-BLU-1	1.0 [3.28]	BLUE	FPT9OM2-LC-BLU-2	2.0 [6.56]	BLUE	FPT9OM2-LC-BLU-3	3.0 [9.84]	BLUE
FPT9OM2-LC-GRN-1	1.0 [3.28]	GREEN	FPT9OM2-LC-GRN-2	2.0 [6.56]	GREEN	FPT9OM2-LC-GRN-3	3.0 [9.84]	GREEN
FPT9OM2-LC-AQU-1	1.0 [3.28]	AQUA	FPT9OM2-LC-AQU-2	2.0 [6.56]	AQUA	FPT9OM2-LC-AQU-3	3.0 [9.84]	AQUA
FPT9OM2-LC-BRN-1	1.0 [3.28]	BROWN	FPT9OM2-LC-BRN-2	2.0 [6.56]	BROWN	FPT9OM2-LC-BRN-3	3.0 [9.84]	BROWN
FPT9OM2-LC-RED-1	1.0 [3.28]	RED	FPT9OM2-LC-RED-2	2.0 [6.56]	RED	FPT9OM2-LC-RED-3	3.0 [9.84]	RED
FPT9OM2-LC-WHT-1	1.0 [3.28]	WHITE	FPT9OM2-LC-WHT-2	2.0 [6.56]	WHITE	FPT9OM2-LC-WHT-3	3.0 [9.84]	WHITE
FPT9OM2-LC-VIO-1	1.0 [3.28]	VIOLET	FPT9OM2-LC-VIO-2	2.0 [6.56]	VIOLET	FPT9OM2-LC-VIO-3	3.0 [9.84]	VIOLET
FPT9OM2-LC-ROS-1	1.0 [3.28]	ROSE	FPT9OM2-LC-ROS-2	2.0 [6.56]	ROSE	FPT9OM2-LC-ROS-3	3.0 [9.84]	ROSE

**NOTES:**

- LC CONNECTOR ASSEMBLY POLISH TYPE: PC.
- ALL CONNECTORS ACCOMPANIED WITH A DUST CAP INSTALLED (NOT SHOWN).
- CABLE ASSEMBLY SHALL BE PACKAGED 12 PIECES PER BAG IN ACCORDANCE WITH L-COM SPECIFICATION PS-0031.

UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE IN INCHES [mm] OVERALL CABLE LENGTH TOLERANCE: $\leq 12$ [305] = +1 [25] / -0 $>12$ [305] $\leq 60$ [1524] = +2 [51] / -0 $>60$ [1524] $\leq 120$ [3048] = +4 [102] / -0 $>120$ [3048] $\leq 300$ [7620] = +6 [152] / -0 $>300$ [7620] = +3% / -0% ALL OTHER DIMENSIONAL TOLERANCES: .X = ± .2 .XX = ± .02 .XXX = ± .005	APPROVALS DRAWN BY D.PARHAM CHECKED BY D.GUITADAURO APPROVED BY D.GALLAGHER	DATE 05/11/2012 05/15/2012 07/13/2012	45 BEECHWOOD DRIVE NORTH ANDOVER, MA 01845	
	CONFIGURATION DETAILS OF UNDIMENSIONED FEATURES MAY VARY COLOR VARIATIONS MAY OCCUR	CATEGORY <b>FIBER OPTIC</b>		PRODUCT DESCRIPTION <b>LC OM2 SMLPX 900um OFNR</b>
PROJECTION 	SIZE <b>A</b>	FSCM NO. <b>43321</b>	DWG. NO. <b>FPT9OM2-LC-12PK</b>	REV. <b>A</b>
SCALE: NONE		CAD FILE: FPT9OM2-LC-12PK.SLDDRW		SHEET 1 OF 1