


**Bulk Cable Specification**

**TC2380 Category 5e Cable**

| <p>Cross-Sectional View</p>    |                        | <p>Color Code</p> <p>Pair 1. Blue, White/Blue</p> <p>Pair 2. Orange, White/Orange</p> |
|---|------------------------|---|
| ITEM  |                        | DESCRIPTION   |
| Conductor   | No. of Conductors      | 2 Twisted Pairs   |
|   | Material               | Tinned copper   |
|   | Construction           | 24 AWG 7/32   |
| Insulation  | Material               | High Density Polyethylene   |
|   | Nominal Diameter       | .039"   |
| Jacket  | Material               | PVC   |
|   | Nominal Wall Thickness | .023"   |
|   | Nominal Diameter       | .200"   |
|   | Color                  | Beige   |
| <p>Marking:<br/>QUABBIN DATAMAX PATCH CORD/JUMPER 5210--(UL) TYPE CM 24 AWG 75C—CSA LL51726—TYPE CMG 60C—ETL VERIF. TIA-568-C.2 CAT 5e—RoHS (LOT DESIGNATOR) (SEQUENTIAL FOOTAGE)</p> |                        |   |
| <b>ELECTRICAL PROPERTIES</b>  |                        |   |
| Conductor Resistance  | 26.0 Ω/100 meters      |   |
| Mutual capacitance  | 13.5pF/ft at 1MHz      |   |
| Impedance   | 100Ω ± 15Ω 1-350 MHz   |   |
| <b>LISTINGS / RATINGS</b>   |                        |   |
| NEC (UL) Type CM, CSA Type CMG, ETL Verified TIA-568-C.2, RoHS  |                        |   |
| Temperature Rating, MAX: +60°C & +75°C  |                        |   |