


THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF L-COM, INC. ANY REPRODUCTION IN PART OR WHOLE WITHOUT THE WRITTEN PERMISSION OF L-COM, INC. IS PROHIBITED.

REVISION					
ZONE	REV	DESCRIPTION	DATE	CHANGED BY	APPROVED
	A	INITIAL RELEASE	7/18/2023	SREITER	GUTTADAURO



PART NUMBER	LENGTH	
	METER	FEET
HD20-SCWN-MM-1M	1	3.3
HD20-SCWN-MM-2M	2	6.6

PINOUT			
P1	P2	P1	P2
1	1	14	14
3	3	19	19
5	5	17	17
4	4	13	13
6	6	15	15
2	2	16	16
7	7	18	18
9	9	S	S
11	11		
10	10		
12	12		
8	8		

**NOTES:**



- CABLE ASSEMBLY SHALL BE TESTED FOR CONTINUITY.
- CABLE ASSEMBLY SHALL RECEIVE INSERTION LOSS TEST PER STANDARD SPECIFICATIONS.
- CABLE ASSEMBLY SHALL BE INDIVIDUALLY PACKAGED.

**ELECTRICAL PROPERTIES:**

- VOLTAGE TEST: DC 300V, 10ms
- INSULATION RESISTANCE: 5.0MΩ/MIN
- CONDUCTANCE RESISTANCE: 5.0Ω MAX

**REGULATORY COMPLIANCE:**

EU RoHS DIRECTIVE (MOST RECENT RELEASED VERSION)

UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE IN INCHES [mm] OVERALL CABLE LENGTH TOLERANCE: ≤12 [305] = +1 [25] / -0 >12 [305] ≤60 [1524] = +2 [51] / -0 >60 [1524] ≤120 [3048] = +4 [102] / -0 >120 [3048] ≤300 [7620] = +6 [152] / -0 >300 [7620] = +5% / -0 ALL OTHER DIMENSIONAL TOLERANCES: .X = ± .2 [5]   FRACTIONS ± 1/32 .XX = ± .02 [5]   ANGLES ± 1° .XXX = ± .005 [13]	APPROVALS SREITER	DATE 7/18/2023	 50 High Street, West Mill, North Andover, MA 01845 USA. Phone: 1.800.341.5266 1.978.682.6936	
	DRAWN BY RCARLESKO	CHECKED BY GUTTADAURO		DATE 7/18/2023
	APPROVED BY GUTTADAURO			
	THIRD-ANGLE PROJECTION 			
CONFIGURATION DETAILS OF UNDIMENSIONED FEATURES MAY VARY		PRODUCT DESCRIPTION <b>HDMI 2.0 MALE TOP SCREW TO HDMI MALE NON SCREW</b>		
COLOR VARIATIONS MAY OCCUR		SIZE <b>A</b>	CAGE CODE <b>43321</b>	
		ITEM NO. <b>HD20-SCWN-MM</b>	REV. <b>A</b>	
		SCALE: NONE	CAD FILE: HD20-SCWN-MM.SLDDRW	
		SHEET 1 OF 1		