

6

5


4

3

2

1

REVISION					
ZONE	REV	DESCRIPTION	DATE	CHANGED BY	APPROVED
	A	INITIAL RELEASE	08/30/2024	KGLEBOVA	THOUGHTON



F

F

E

E

D

D

C




C

B


B

A

A



NUMBER	COLOR	NUMBER	COLOR
1	BLUE	9	BLUE
2	ORANGE	10	ORANGE
3	GREEN	11	GREEN
4	BROWN	12	BROWN
5	GREY	13	GREY
6	WHITE	14	WHITE
7	RED	15	RED
8	BLACK	16	BLACK



DIMENSIONS ARE FOR REFERENCE ONLY.
DIMENSIONS ARE SHOWN IN MILLIMETERS.

THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF INFINITE ELECTRONICS, INC. ANY REPRODUCTION IN PART OR WHOLE WITHOUT THE WRITTEN PERMISSION OF INFINITE ELECTRONICS, INC. IS PROHIBITED. THESE COMMODITIES, TECHNOLOGY OR SOFTWARE WERE EXPORTED FROM THE UNITED STATES IN ACCORDANCE WITH THE EXPORT ADMINISTRATION REGULATIONS. DIVERSION CONTRARY TO U.S. LAW PROHIBITED.

UNLESS OTHERWISE SPECIFIED
LEADING DIMENSIONS ARE INCHES
DIMENSIONS IN [] ARE MILLIMETERS

TOLERANCES:

X = ±.1 [5]	FRACTIONS
.XX = ±.02 [0.5]	± 1/32
.XXX = ±.005 [0.125]	ANGLES ± 1°

CABLE LENGTH TOLERANCES:

≤ 12 [305]	= ±.125 [-0]
> 12 [305] ≤ 60 [1524]	= +.2 [-.1] / -0
> 60 [1524] ≤ 120 [3048]	= +.4 [-.1] / -0
> 120 [3048] ≤ 300 [7620]	= +.6 [-.2] / -0
> 300 [7620]	= +.5% / -0

ALL DIMENSIONS ARE FOR REFERENCE ONLY
AND SUBJECT TO CHANGE WITHOUT NOTICE
UN-DIMENSIONED NON-CRITICAL FEATURES
MAY VARY IN SIZE AND LOCATION
COLORS MAY VARY

L-com
an INFINITE brand

Website: www.L-com.com
Phone: 1.800.341.5266 | 1.978.682.6936

INTERPRET ALL DIMENSIONS AND TOLERANCES PER ASME Y14.5

SCALE	SHEET
NONE	1 OF 1

DESCRIPTION
DISTRIBUTION BOX 16 PORTS WITH 16X SC SM DUPLEX ADAPTER AND 1:16 SC PLC SPLITTER

SIZE	CAGE CODE	DRAWN BY	ITEM NO.	REV
A	43321	KGLEBOVA	LCFDB-416A-P16SC	A

6

5

4

3

2

1