


THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF L-COM, INC. ANY REPRODUCTION IN PART OR WHOLE WITHOUT THE WRITTEN PERMISSION OF L-COM, INC. IS PROHIBITED.

REVISIONS			
REV	DESCRIPTION	DATE	APPROVED
E	ECN 12060: UPDATED MOLD DESIGN AND DIMENSIONS	9/1/2022	DGUITADAURO



WIRING MAP		
P1	COLOR	J1
1	BROWN	1
2	WHITE	2
3	BLUE	3
4	BLACK	4
5	GREEN	5

PART NUMBER	LENGTH	
	FEET	METERS
M12M12F5A-0.5	1.64	0.5
M12M12F5A-1	3.28	1
M12M12F5A-2	6.56	2
M12M12F5A-3	9.84	3
M12M12F5A-5	16.41	5
M12M12F5A-10	32.81	10

NOTES:

1. WATERPROOF RATING: IP68.
2. MOLDED HOOD: POLYURETHANE, BLACK.
3. SCREW NUT: ZINC ALLOY, NICKEL PLATED.
4. PINS: COPPER ALLOY, GOLD PLATED.
5. CABLE ASSEMBLIES INDIVIDUALLY PACKAGED IN A POLY BAG PER L-COM SPECIFICATION PS-0031.
6. ALL DIMENSIONS ARE FOR REFERENCE ONLY.
7. CABLE ASSEMBLIES TO BE TESTED FOR CONTINUITY.

**REGULATORY COMPLIANCE:**  
CE2011/65/EU(RoHS DIRECTIVE)

UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE IN INCHES [mm] OVERALL CABLE LENGTH TOLERANCE: ≤12 [305] = +1 [25] / -0 >12 [305] ≤60 [1524] = +2 [51] / -0 >60 [1524] ≤120 [3048] = +4 [102] / -0 >120 [3048] ≤300 [7620] = +6 [152] / -0 >300 [7620] = +5% / -0 ALL OTHER DIMENSIONAL TOLERANCES: .X = ± .2 [5]   FRACTIONS ± 1/32 .XX = ± .02 [5]   ANGLES ± 1° .XXX = ± .005 [13]	APPROVALS DRAWN BY D.PARHAM CHECKED BY P.MCNEIL APPROVED BY D.CASTRO	DATE 01/22/2010 01/25/2010 01/25/2010	50 High Street, West Mill, North Andover, MA 01845 USA. Phone: 1.800.341.5266 1.978.682.6936	
	THIRD-ANGLE PROJECTION 	CONFIGURATION DETAILS OF UNDIMENSIONED FEATURES MAY VARY COLOR VARIATIONS MAY OCCUR		CATEGORY <b>TELECOM/MODULAR</b>
SIZE <b>A</b>		CAGE CODE <b>43321</b>	ITEM NO. <b>M12M12F5A</b>	REV. <b>E</b>
SCALE: NONE		CAD FILE: M12M12F5A.SLDDRW		SHEET 1 OF 1