



8 7 6 5 4 3 2 1

THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF L-COM, INC. ANY REPRODUCTION IN PART OR WHOLE WITHOUT THE WRITTEN PERMISSION OF L-COM, INC. IS PROHIBITED.

REVISIONS			
REV	DESCRIPTION	DATE	APPROVED
A	INITIAL RELEASE	9/30/13	D.GRIFFIN
B	ECN 7587: SHOWED LANYARD ON CABLE	9/4/14	D. CASTRO



MODEL NUMBER	LENGTH METERS [FEET]
TRD8RGMT6-01	1.0 [3.28]
TRD8RGMT6-02	2.0 [6.56]
TRD8RGMT6-03	3.0 [9.84]
TRD8RGMT6-05	5.0 [16.41]
TRD8RGMT6-10	10.0 [32.81]

**NOTES:**

CRUSH RESISTANCE (1 INCH SQ. AREA): 1500 POUNDS, MIN.

TEMPERATURE RANGE: -40°C TO +80°C (-40°F TO +176°F)

CABLE ASSEMBLY SHALL BE TESTED FOR CONTINUITY.

CABLE ASSEMBLY SHALL BE INDIVIDUALLY PACKAGED IN ACCORDANCE WITH L-COM SPECIFICATION PS-0031.

**REGULATORY COMPLIANCE:**  
CE2011/65/EU (RoHS DIRECTIVE)

UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE IN INCHES [mm] OVERALL CABLE LENGTH TOLERANCE: ≤12 [305] = +1 [25] / -0 >12 [305] ≤60 [1524] = +2 [51] / -0 >60 [1524] ≤120 [3048] = +4 [102] / -0 >120 [3048] ≤300 [7620] = +6 [152] / -0 >300 [7620] = +5% / -0%	APPROVALS	DATE		45 BEECHWOOD DRIVE NORTH ANDOVER, MA 01845		
	DRAWN BY D.FRISIELLO	9/27/13				
ALL OTHER DIMENSIONAL TOLERANCES: .X = ± .2 [5.08] .XX = ± .02 [.51] .XXX = ±.005 [0.13]	CHECKED BY D.GUITADAURO	9/27/13	CATEGORY TELECOM/MODULAR			
	APPROVED BY D.GALLAGHER	9/27/13	PRODUCT DESCRIPTION IP68 RGRJ45 P/J ANOD TPE			
PROJECTION 	CONFIGURATION DETAILS OF UNDIMENSIONED FEATURES MAY VARY	COLOR VARIATIONS MAY OCCUR	SIZE <b>A</b>	FSCM NO. <b>43321</b>	DWG. NO. TRD8RGMT6	REV. <b>B</b>
			SCALE: NONE	CAD FILE: TRD8RGMT6.SLDDRW	SHEET 1 OF 1	