


THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF L-COM, INC. ANY REPRODUCTION IN PART OR WHOLE WITHOUT THE WRITTEN PERMISSION OF L-COM, INC. IS PROHIBITED.

REVISIONS			
REV	DESCRIPTION	DATE	APPROVED
A	INITIAL RELEASE	3/7/13	D.GRIFFIN
B	ECN 7107: ADDED JACKET TYPE TO CHART. REMOVED ALL OM4 P/N'S. UPD ROHS	10/17/13	D.FRISIELLO
C	ECN 9116: REVISED CHART SHEET 2	3/23/18	D.FRISIELLO





MULTIMODE WIRING MAP (8 MPO CONNECTOR)	
"P1"	"P2"
N/C	N/C
2	2
3	3
4	4
5	5
6	6
7	7
N/C	N/C

SINGLE MODE WIRING MAP (12 MPO CONNECTOR)	
"P1"	"P2"
N/C	N/C
N/C	N/C
N/C	N/C
4	4
5	5
6	6
7	7
8	8
9	9
N/C	N/C
N/C	N/C
N/C	N/C

**NOTES:**

- SEE SHEET 2 FOR PART NUMBERS, FIBER MODES, JACKET TYPES, COLORS, AND LENGTHS.
- MPO CONNECTOR MULTIMODE ASSEMBLY POLISH TYPE: UPC  
MPO CONNECTOR SINGLE MODE ASSEMBLY POLISH TYPE: APC
- ALL CONNECTORS ACCOMPANIED WITH A DUST CAP INSTALLED (NOT SHOWN).
- CABLE ASSEMBLY SHALL BE INDIVIDUALLY PACKAGED IN ACCORDANCE WITH L-COM PACKAGING SPECIFICATION PS-0031.

**REGULATORY COMPLIANCE:**  
CE2011/65/EU(RoHS DIRECTIVE)

UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE IN INCHES [mm] OVERALL CABLE LENGTH TOLERANCE: ≤12 [305] = +1 [25] / -0 >12 [305] ≤60 [1524] = +2 [51] / -0 >60 [1524] ≤120 [3048] = +4 [102] / -0 >120 [3048] ≤300 [7620] = +6 [152] / -0 >300 [7620] = +5% / -0%	APPROVALS	DATE	 50 HIGH STREET NORTH ANDOVER, MA 01845			
	DRAWN BY D.FRISIELLO	3/1/13		CATEGORY FIBER OPTICS		
ALL OTHER DIMENSIONAL TOLERANCES: .X = ± .2 [5.08] .XX = ± .02 [1.51] .XXX = ±.005 [1.13]	CHECKED BY D.GUITADAURO	3/1/13	PRODUCT DESCRIPTION 6-RIB MPO- M/M			
	APPROVED BY D. GALLAGHER	3/1/13		<table border="1"> <tr> <td>SIZE <b>A</b></td> <td>FSCM NO. <b>43321</b></td> <td>DWG. NO. <b>MPMM6</b></td> <td>REV. <b>C</b></td> </tr> </table>	SIZE <b>A</b>	FSCM NO. <b>43321</b>
SIZE <b>A</b>	FSCM NO. <b>43321</b>	DWG. NO. <b>MPMM6</b>	REV. <b>C</b>			
PROJECTION 	CONFIGURATION DETAILS OF UNDIMENSIONED FEATURES MAY VARY		SCALE: NONE			
COLOR VARIATIONS MAY OCCUR	CAD FILE: MPMM6.SLDDRW		SHEET 1 OF 2			

THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF L-COM, INC. ANY REPRODUCTION IN PART OR WHOLE WITHOUT THE WRITTEN PERMISSION OF L-COM, INC. IS PROHIBITED.



CABLE CHART

MODEL NUMBER	LENGTH, MTR [FT]	CABLE MODE	JACKET TYPE	CABLE COLOR
MPMM6OM1-1	1.0 [3.28]	62.5/125 MULTIMODE OM1	OFNR (RISER) RATED	ORANGE
MPMM6OM1-3	3.0 [9.84]			
MPMM6OM1-5	5.0 [16.41]			
MPMM6OM1-10	10.0 [32.81]			
MPMM6OM1-25	25.0 [82.03]			
MPMM6OM1-50	50.0 [164.05]			
MPMM6OM1-100	100.0 [328.10]			
MPMM6OM2-1	1.0 [3.28]	50/125 MULTIMODE OM2	OFNR (RISER) RATED	ORANGE
MPMM6OM2-3	3.0 [9.84]			
MPMM6OM2-5	5.0 [16.41]			
MPMM6OM2-10	10.0 [32.81]			
MPMM6OM2-25	25.0 [82.03]			
MPMM6OM2-50	50.0 [164.05]			
MPMM6OM2-100	100.0 [328.10]			
MPMM6OM3-1	1.0 [3.28]	50/125 MULTIMODE OM3 LASER OPTIMIZED	OFNR (RISER) RATED	AQUA
MPMM6OM3-3	3.0 [9.84]			
MPMM6OM3-5	5.0 [16.41]			
MPMM6OM3-10	10.0 [32.81]			
MPMM6OM3-25	25.0 [82.03]			
MPMM6OM3-50	50.0 [164.05]			
MPMM6OM3-100	100.0 [328.10]			
MPMM6S-1	1.0 [3.28]	9/125 SINGLE MODE OS1	OFNR (RISER) RATED	YELLOW
MPMM6S-3	3.0 [9.84]			
MPMM6S-5	5.0 [16.41]			
MPMM6S-10	10.0 [32.81]			
MPMM6S-25	25.0 [82.03]			
MPMM6S-50	50.0 [164.05]			
MPMM6S-100	100.0 [328.10]			

		50 HIGH STREET NORTH ANDOVER, MA 01845	
CATEGORY			
FIBER OPTICS			
PRODUCT DESCRIPTION			
6-RIB MPO- M/M			
SIZE	FSCM NO.	DWG. NO.	REV.
<b>A</b>	<b>43321</b>	<b>MPMM6</b>	<b>C</b>
SCALE: NONE		CAD FILE: MPMM6.SLDDRW	
		SHEET 2 OF 2	