



THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF L-COM, INC. ANY REPRODUCTION IN PART OR WHOLE WITHOUT THE WRITTEN PERMISSION OF L-COM, INC. IS PROHIBITED.

REVISIONS			
REV	DESCRIPTION	DATE	APPROVED
F	ECN 7890: UPDATED FORMAT, PACKAGING, ROHS	4/2/15	D. DESJARDIN



PART NUMBER	LENGTH		PART NUMBER	LENGTH	
	FEET	METERS		FEET	METERS
TRDU45-1	1	0.31	TRDU45-30	30	9.14
TRDU45-2	2	0.61	TRDU45-40	40	12.19
TRDU45-3	3	0.91	TRDU45-50	50	15.24
TRDU45-5	5	1.52	TRDU45-60	60	18.29
TRDU45-7	7	2.13	TRDU45-75	75	22.86
TRDU45-10	10	3.05	TRDU45-80	80	24.38
TRDU45-15	15	4.57	TRDU45-90	90	27.43
TRDU45-20	20	6.1	TRDU45-100	100	30.48
TRDU45-25	25	7.62			

NOTES:

MATERIAL:
 PLUG HOUSING: POLYCARBONATE, CLEAR, UL94V-0
 CONTACTS: PHOSPHOR BRONZE
 CABLE JACKET: PVC, GRAY

FINISH:
 CONTACTS: 50 μINCHES GOLD IN CONTACT AREA
 OVER 100 μINCHES NICKEL PLATE OVERALL.

CABLE CHARACTERISTICS:
 UNSHIELDED TWO TWISTED PAIR MODULAR CABLE,
 24 AWG (7X32) STRANDED COPPER

MISCELLANEOUS:
 PLUG CONFORMS TO TIA-1096
 OPERATING TEMPERATURE RANGE: -20°C TO +60°C
 CABLE ASSEMBLY SHALL BE TESTED FOR CONTINUITY.
 CABLE ASSEMBLY SHALL BE INDIVIDUALLY PACKAGED IN
 ACCORDANCE WITH L-COM SPECIFICATION PS-0031.

REGULATORY COMPLIANCE:
 CE2011/65/EU (RoHS DIRECTIVE)

UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE IN INCHES [mm] OVERALL CABLE LENGTH TOLERANCE: ≤12 [305] = +1 [25] / -0 >12 [305] ≤60 [1524] = +2 [51] / -0 >60 [1524] ≤120 [3048] = +4 [102] / -0 >120 [3048] ≤300 [7620] = +6 [152] / -0 >300 [7620] = +5% / -0% ALL OTHER DIMENSIONAL TOLERANCES: .X = ± .2 [5.08] .XX = ± .02 [1.51] .XXX = ± .005 [1.13]	APPROVALS DRAWN BY C.MCCORMICK	DATE 07/18/2006		45 BEECHWOOD DRIVE NORTH ANDOVER, MA 01845	
	CHECKED BY ENG APPROVED BY J.ROBERTS	DATE 07/18/2006		CATEGORY TELECOM/MODULAR	
	CONFIGURATION DETAILS OF UNDIMENSIONED FEATURES MAY VARY	PRODUCT DESCRIPTION RJ11/RJ11 UTP USOC4 CABLE			
	PROJECTION 	COLOR VARIATIONS MAY OCCUR	SIZE A	FSCM NO. 43321	DWG. NO. TRDU45

SCALE: NONE | CAD FILE: TRDU45.SLDDRW | SHEET 1 OF 1