

THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF L-COM, INC. ANY REPRODUCTION IN PART OR WHOLE WITHOUT THE WRITTEN PERMISSION OF L-COM, INC. IS PROHIBITED.

REVISION					
ZONE	REV	DESCRIPTION	DATE	CHANGED BY	APPROVED
	A	INITIAL RELEASE	04/18/2023	DZINN	GUTTADAURO

1. CONSTRUCTION:

CONDUCTOR: 14 AWG TINNED COPPER  
 INSULATION: POLYVINYLCHLORIDE, .022" NOM. WALL THICKNESS  
 INNER JACKET: NYLON, MIN THICKNESS .004"  
 JACKET: POLYVINYLCHLORIDE, BLACK, .045" NOM. WALL THICKNESS.  
 OVERALL CABLE DIAMETER

NOM. DIA.  
 .076"  
 .118"  
 .128"  
 .394±.012"

2. PHYSICAL PROPERTIES:

TEMPERATURE RATING, MAX 90°C  
 TEMPERATURE RATING, MIN. -40°C  
 JACKET IS UV RESISTANT

3. ELECTRICAL CHARACTERISTICS:

DIELECTRIC STRENGTH (kv/1min) 2.0(AC)  
 VOLTAGE RATING, MAX. 600V  
 MAX COND D.C. RESISTANCE AT 20°C (W/km) ≤8.96

4. REFERENCE STANDARD:

UL1277 & UL1581 & UL83  
 MEETS (UL) VW-1 FLAME TEST

5. MARKING IN WHITE:


E497465 (UL) TYPE TC-ER THHN/THWN 3C 14AWG 90°C DRY/75°C WET  
 600V SUN RES VW-1 -40°C JHOSIN

6. CONDUCTOR COLOR:



1. RED
2. BLACK
3. BLUE

REGULATORY COMPLIANCE:

EU RoHS DIRECTIVE (MOST RECENT RELEASED VERSION)



CROSS-SECTIONAL VIEW

UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE IN INCHES [mm] OVERALL CABLE LENGTH TOLERANCE: ≤12 [305] = +1 [25] / -0 >12 [305] ≤60 [1524] = +2 [51] / -0 >60 [1524] ≤120 [3048] = +4 [102] / -0 >120 [3048] ≤300 [7620] = +6 [152] / -0 >300 [7620] = +5% / -0 ALL OTHER DIMENSIONAL TOLERANCES: .X = ±.2 [5]   FRACTIONS ± 1/32 .XX = ±.02 [5]   ANGLES ± 1° .XXX = ±.005 [13]	APPROVALS	DATE	 50 High Street, West Mill, North Andover, MA 01845 USA. Phone: 1.800.341.5266 1.978.682.6936		
	DRAWN BY DZINN	04/18/2023			
	CHECKED BY HBAKKE	04/18/2023			
	APPROVED BY DGUST	04/18/2023			
THIRD-ANGLE PROJECTION 	CONFIGURATION DETAILS OF UNDIMENSIONED FEATURES MAY VARY	PRODUCT DESCRIPTION POWER BULK TRAY CABLE, ER, 14AWG, 3C, BLK, 600V, 1KFT	CATEGORY BULK CABLE		
	COLOR VARIATIONS MAY OCCUR	SIZE A	CAGE CODE 43321	ITEM NO. PBTC143	REV. A
		SCALE: NONE	CAD FILE: PBTC143.SLDDRW	SHEET 1 OF 1	