




THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF L-COM, INC. ANY REPRODUCTIONS IN PART OR WHOLE WITHOUT THE WRITTEN PERMISSION OF L-COM, INC. IS PROHIBITED.

REVISIONS			
REV	DESCRIPTION	DATE	CHANGED BY
A	INITIAL RELEASE	3/20/18	D.FRISIELLO



BACK PANEL  
HARDWARE INCLUDED

NOTES:

1. MATERIAL: .06 THICK COLD ROLLED STEEL.
2. FINISH: FLAT BLACK POWDER COAT.
3. ALL INSIDE RADII .031 UNLESS OTHERWISE SPECIFIED.
4. PANEL ASSEMBLY SHALL BE INDIVIDUALLY PACKAGED IN ACCORDANCE WITH L-COM SPECIFICATION PS-0031.

REGULATORY COMPLIANCE:  
CE2011/65/EU(RoHS DIRECTIVE)

UNLESS OTHERWISE SPECIFIED,  
DIMENSIONS ARE IN INCHES (mm)  
OVERALL CABLE LENGTH TOLERANCE:  
≤12 [305] ≤60 [1524] = +.25(1) / -0  
>60 [1524] ≤120 [3048] = +.4 [102] / -0  
>120 [3048] ≤300 [7620] = +.6 [152] / -0  
>300 [7620] = +.75 / -0  
ALL OTHER DIMENSIONAL TOLERANCES:  
X = ±.2 [5.08]  
XX = ±.02 [5.1]  
XXX = ±.005 [1.3]

APPROVALS	DATE
DRAWN BY D.FRISIELLO	3/19/18
CHECKED BY M.MARTINEZ	3/20/18
APPROVED BY M.MARTINEZ	3/20/18

		50 HIGH STREET NORTH ANDOVER, MA 01845	
CATEGORY <b>RACK PANELS</b>			
PRODUCT DESCRIPTION <b>1U PANEL, W/24 PORTS, SC DPLX/LC QUAD</b>			
SIZE <b>B</b>	PSCM NO. <b>43321</b>	DWG. NO. <b>PR175SCDLCQ24</b>	REV. <b>A</b>
SCALE: 1:1		CAD FILE: PR175SCDLCQ24.SLDDRW	
			SHEET 1 OF 1

