

THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF L-COM, INC. ANY REPRODUCTION IN PART OR WHOLE WITHOUT THE WRITTEN PERMISSION OF L-COM, INC. IS PROHIBITED.

REVISIONS			
REV	DESCRIPTION	DATE	APPROVED
A	INITIAL RELEASE	4/1/10	D.GRIFFIN
B	ECN 5095: REVISE PACKAGING SPEC. AND NEW FORMAT	10/22/10	D.FRISIELLO





CHART A					
PART NO.	SIZE (IN)	NOM. I.D. (IN)	NOM. WALL THICK. (IN)	PITCH	MAX. DIA. INNER WIRE BUNDLE
TUBSWT-0.125	1/8	.125	.031	.188	1/2
TUBSWT-0.25	1/4	.250	.046	.375	2
TUBSWT-0.5	1/2	.500	.062	.562	4

RoHS Compliant ✓

NOTES:
 MATERIAL: POLYETHYLENE, CLEAR
 OPERATING TEMPERATURE: -20° C TO +80° C.

UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE IN INCHES [mm] OVERALL CABLE LENGTH TOLERANCE: ≤ 12 [305] = +1 [25] / -0 >12 [305] ≤ 60 [1524] = +2 [51] / -0 >60 [1524] ≤ 120 [3048] = +4 [102] / -0 >120 [3048] ≤ 300 [7620] = +6 [152] / -0 >300 [7620] = +3% / -0% ALL OTHER DIMENSIONAL TOLERANCES: .X = ± .2 .XX = ± .02 .XXX = ± .005	APPROVALS DRAWN BY D.FRISIELLO CHECKED BY MARTINEZ APPROVED BY S.SMITH	DATE 4/1/10 4/1/10 4/1/10	45 BEECHWOOD DRIVE NORTH ANDOVER, MA 01845	
	CONFIGURATION DETAILS OF UNDIMENSIONED FEATURES MAY VARY			CATEGORY TUBING
	PROJECTION 	COLOR VARIATIONS MAY OCCUR	SIZE A	FSCM NO. 43321
	DWG. NO. TUBSWT		REV. B	SCALE: NONE CAD FILE: TUBSWT.SLDDRW SHEET 1 OF 1