


THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF L-COM, INC. ANY REPRODUCTION IN PART OR WHOLE WITHOUT THE WRITTEN PERMISSION OF L-COM, INC. IS PROHIBITED.

REVISIONS			
REV	DESCRIPTION	DATE	APPROVED
A	INITIAL RELEASE	11/12/07	D.FRISIELLO
B	ECN 7306: ADD COLOR ORANGE, SHEET 2, REVISE ROHS NOTE, FORMAT	2/24/14	D.FRISIELLO



4X LC CONNECTOR

MODEL NO.	JACKET COLOR	LENGTH MTR [FT]
SFODLC-RD-01	RED	1 M [3.28 FT]
SFODLC-RD-02	RED	2 M [6.56 FT]
SFODLC-RD-03	RED	3 M [9.84 FT]
SFODLC-RD-04	RED	4 M [13.12 FT]
SFODLC-RD-05	RED	5 M [16.40 FT]
SFODLC-RD-10	RED	10 M [32.81 FT]
SFODLC-RD-15	RED	15 M [49.22 FT]
SFODLC-GR-01	GREEN	1 M [3.28 FT]
SFODLC-GR-02	GREEN	2 M [6.56 FT]
SFODLC-GR-03	GREEN	3 M [9.84 FT]
SFODLC-GR-04	GREEN	4 M [13.12 FT]
SFODLC-GR-05	GREEN	5 M [16.40 FT]
SFODLC-GR-10	GREEN	10 M [32.81 FT]
SFODLC-GR-15	GREEN	15 M [49.22 FT]
SFODLC-BL-01	BLUE	1 M [3.28 FT]
SFODLC-BL-02	BLUE	2 M [6.56 FT]
SFODLC-BL-03	BLUE	3 M [9.84 FT]
SFODLC-BL-04	BLUE	4 M [13.12 FT]
SFODLC-BL-05	BLUE	5 M [16.40 FT]
SFODLC-BL-10	BLUE	10 M [32.81 FT]
SFODLC-BL-15	BLUE	15 M [49.22 FT]
SFODLC-OR-01	ORANGE	1 M [3.28 FT]
SFODLC-OR-02	ORANGE	2 M [6.56 FT]
SFODLC-OR-03	ORANGE	3 M [9.84 FT]
SFODLC-OR-04	ORANGE	4 M [13.12 FT]
SFODLC-OR-05	ORANGE	5 M [16.40 FT]
SFODLC-OR-10	ORANGE	10 M [32.81 FT]
SFODLC-OR-15	ORANGE	15 M [49.22 FT]

**NOTES:**



**CABLE CHARACTERISTICS:**  
 9/125 SINGLE MODE DUPLEX FIBER ZIPCORD.  
 JACKET RATING: PVC, OFNR.  
 JACKET COLOR: SEE CHART.  
 CABLE O.D.: 3.0 mm.

**TESTING:**  
 BACK REFLECTION TESTED AT 1310 nm WITH A < -40dB RESULT.

CONNECTOR POLISH: THIS ASSEMBLY UTILIZES A PC POLISH.

**MISCELLANEOUS:**  
 OPERATING TEMPERATURE: -20° C TO +70° C.  
 CABLE ASSEMBLY TO SHIP WITH DUST CAPS INSTALLED. (NOT SHOWN).  
 CABLE ASSEMBLY SHALL BE INDIVIDUALLY PACKAGED IN ACCORDANCE WITH L-COM SPECIFICATION PS-0031.

**REGULATORY COMPLIANCE:**  
 CE2011/65/EU (RoHS DIRECTIVE)

UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE IN INCHES [mm] OVERALL CABLE LENGTH TOLERANCE: ≤12 [305] = +1 [25] / -0 >12 [305] ≤60 [1524] = +2 [51] / -0 >60 [1524] ≤120 [3048] = +4 [102] / -0 >120 [3048] ≤300 [7620] = +6 [152] / -0 >300 [7620] = +5% / -0% ALL OTHER DIMENSIONAL TOLERANCES: .X = ± .2 [5.08] .XX = ± .02 [51] .XXX = ±.005 [1.3]	APPROVALS	DATE	 45 BEECHWOOD DRIVE NORTH ANDOVER, MA 01845	
	DRAWN BY D.FRISIELLO	11/12/07		CATEGORY FIBER OPTICS
PROJECTION 	CHECKED BY D.PARHAM	11/12/07	PRODUCT DESCRIPTION <b>LC-LC DPLX ASSEMBLY</b>	
	APPROVED BY P.McNEIL	11/12/07		CONFIGURATION DETAILS OF UNDIMENSIONED FEATURES MAY VARY COLOR VARIATIONS MAY OCCUR REF
SIZE <b>A</b>		FSCM NO. <b>43321</b>	DWG. NO. <b>SFODLC-COLOR</b>	REV. <b>B</b>
SCALE: NONE		CAD FILE: SFODLC-COLOR.SLDDRW		SHEET 1 OF 1

A

B

A

B

8 7 6 5 4 3 2 1

8 7 6 5 4 3 2 1