


THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF L-COM, INC. ANY REPRODUCTION IN PART OR WHOLE WITHOUT THE WRITTEN PERMISSION OF L-COM, INC. IS PROHIBITED.

REVISIONS			
REV	DESCRIPTION	DATE	APPROVED
A	INITIAL RELEASE	07/17/06	MCCORMICK
B	ECN2547: UPDATE DRAWING FORMAT. CORRECT NOTES.	08/30/06	D. PARHAM
C	ECN3306: ADDED 1, 2, 5, 10, 50 & 100 FT LENGTHS. UPDATED FORMAT.	04/29/08	D. PARHAM



PART NUMBER	LENGTH	
	FEET	METERS
TDC201	1.0	0.31
TDC202	2.0	0.61
TDC205	5.0	1.52
TDC207	7.0	2.13
TDC210	10.0	3.05
TDC214	14.0	4.27
TDC225	25.0	7.62
TDC250	50.0	15.24
TDC2100	100.0	30.48

WIRING MAP	
"P1"	"P2"
2	5
3	4
4	3
5	2

NOTES:

MATERIAL:

PLUG HOUSING: POLYCARBONATE, CLEAR, UL94V-0
 CONTACTS: PHOSPHOR BRONZE
 CABLE JACKET: PVC, GRAY

FINISH:

CONTACTS: 50 μINCHES GOLD IN CONTACT AREA
 OVER 100 μINCHES NICKEL PLATE OVERALL.

CABLE CHARACTERISTICS:

4 CONDUCTOR FLAT MODULAR CORD, SILVER SATIN PVC OUTER JACKET
 U.L. STYLE 20251, 26 AWG STRANDED

MISCELLANEOUS:

PLUG CONFORMS TO TIA-1096
 OPERATING TEMPERATURE RANGE: -20°C TO +60°C
 CORDS TO BE TESTED FOR CONTINUITY
 CORDS TO BE INDIVIDUALLY PACKAGED IN A POLYBAG

RoHS Compliant ✓

UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE IN INCHES (mm)	APPROVALS	DATE		45 BEECHWOOD DRIVE NORTH ANDOVER, MA 01845	
	DRAWN BY C.MCCORMICK	07/17/2006			
OVERALL CABLE LENGTH TOLERANCE: ≤12 (305) = +1 (25) / -0 >12 (305) ≤60 (1524) = +2(51) / -0 >60 (1524) ≤120 (3048) = +4 / -0 >120 (3048) ≤300 (7620) = +6 / -0 >300 (7620) = +5% / -0%	CHECKED BY ENG	07/17/2006	CATEGORY MODULAR		
	APPROVED BY J.ROBERTS	07/17/2006	PRODUCT DESCRIPTION FLAT CABLE (6X4) CROSSED		
ALL OTHER DIMENSIONAL TOLERANCES: .X = .3 .XX = .15	CONFIGURATION DETAILS OF UNDIMENSIONED FEATURES MAY VARY	SIZE A	FSCM NO. 43321	DWG. NO. TDC207	REV. C
PROJECTION 	COLOR VARIATIONS MAY OCCUR	SCALE: NONE	CAD FILE: TDC207.SLDDRW	SHEET 1 OF 1	