| THE INFORMATION CONTAINED IN THIS DRAWING PROPERTY OF L-COM, INC. ANY REPRODUCTION IN WHOLE WITHOUT THE WRITTEN PERMISSION OF L-CC IS PROHIBITED. | IS THE SOLE PART OR M, INC. | REV | REVISIONS DESCRIPTION | DATE APPROVAL 09/28/2018 DFRISIELLO |
|---|--|-----------------------------|--|--|
| B ECN 9957: REVISED JACKET MARKING 07/08/2019 DFRISIELLO | | | | |
| TFPC6A-WHT TFPC6A-WHT CONSISTS OF 1000 FEET OF CONTINUOUS LENGTH BULK CABLE CROSS-SECTIONAL VIEW | | | | |
| NOTES: | | | PAIR JACKET DRAIN RIP CORD SHIELD PE TAPE | COLOR CODE 1) BLUE × WHITE/BLUE 2) ORANGE × WHITE/ORANGE 3) GREEN × WHITE/GREEN 4) BROWN × WHITE/BROWN |
| 1.CONSTRUCTION: | | | | |
| CONDUCTOR: 23 AWG SOLID BARE COPPER PAIRS: COLOR CODED SINGLES TWISTED INTO PAIRS | | | | |
| CABLE: (4) TWISTED PAIRS TWISTED TOGETHER TO FORM A CABLE CORE WITH A SPLINE DIVIDER SHIELD: AN ALUMINUM POLYESTER FOIL SHIELD (100% COVERAGE) OVER PE TAPE WRAP. A SOLID TINNED COPPER DRAIN WIRE IN CONTACT WITH THE OUTER SURFACE. JACKET: PLENUM, PVC, COLOR, WHITE, WITH RIP CORD OVERALL CABLE DIAMETER: 0.268±0.012 [6.8 ±0.3mm] | | | | |
| 2.PHYSICAL PROPERTIES: TEMPERATURE RATING, MAX. TEMPERATURE RATING, MIN. | 80°C -20°C | | | |
| 3.AGENCY APPROVALS: NEC ARTICLE 800, UL 444TYPE CMP RATING FT6, ETL VERIFIED TO ANSI-TIA 568.2 CATEGORY 6, C(ETL)US ROHS COMPLIANT | | | | |
| 4. JACKET PRINT: VERTICAL CABLE E191267 (UL) c(UL) CMP FT 75C 23AWG 4PR CAT6A F/UTP ANSI/TIA 568C.2 RoHS COMPLIANT XXXXFT | | | | |
| 5. ELECTRICAL CHARACTERISTICS: (FOR 100m OF CABLE) VOLTAGE RATING 30V CAPACITANCE 5.6nF/100m NOMINAL VELOCITY OF PROPAGATION 65% MAX CONDUCTOR D.C. RESISTANCE 9.38 Ω/100m NOMINAL MAX D.C. RESISTANCE, UNBALANCE 5% 6. CHARACTERISTIC IMPEDANCE 100 ± 15% 101 MHz 100 ± 12% 251 MHz 100 ± 22% | | | | |
| 251 MHz - 550 MHz 100 ± 25% 7.PACKAGING: | | | | |
| CABLE SHIPPED ON A SPOOL REGULATORY COMPLIANCE: CE2011/65/EU(RoHS DIRECTIVE) UL LISTED | | | | |
| | UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE IN INCHES [mm] | DRAWN BY DFRISIELLO | | 50 HIGH STREET Connectivity 01845 |
| | OVERALL CABLE LENGTH TOLERANCE: \$12 [305] = +1 [25] / -0 >12 [305] - 60 [1524] = +2 [51] / -0 >60 [1524] - 120 [3048] = +4 [02] / -0 >120[3048] - 300] / 620] = +6 [152] / -0 | APPROVED BY | 09/28/2018 CATEGORY 09/28/2018 | TELECOM/MODULAR |
| | > 120[304] - 300[7620] = +6 [152] / -0 > 300[7620] = +5% / -0% ALL OTHER DIMENSIONAL TOLERANCES: X = .2 [5.08] .XX = .05 [.13] | DOUTIADAUK | AILS OF | · · · · · · · · · · · · · · · · · · · |
| .XX = .02 [.51] .XXX = .005 [.13] PROJECTION | | COLOR VARIATIC MAY OCCUR | DNS SIZE FSCM NC | DWG. NO. |
| | | | A 4002 | D FILE: TFPC6A-WHT.SLDDRW SHEET 1 OF 1 |

B