



THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF L-COM, INC. ANY REPRODUCTION IN PART OR WHOLE WITHOUT THE WRITTEN PERMISSION OF L-COM, INC. IS PROHIBITED.

REVISIONS			
REV	DESCRIPTION	DATE	APPROVED
E	ECN 7890: UPDATED FORMAT, PACKAGING, ROHS	4/2/15	D. DESJARDIN



"P1"
 POSITION 1
 2X RJ45 PLUG
 (8P8C)

"P2"
 POSITION 1



PART NUMBER	LENGTH		PART NUMBER	LENGTH	
	FEET	METERS		FEET	METERS
TRD450CR-1	1	0.31	TRD450CR-30	30	9.14
TRD450CR-2	2	0.61	TRD450CR-40	40	12.19
TRD450CR-3	3	0.91	TRD450CR-50	50	15.24
TRD450CR-5	5	1.52	TRD450CR-60	60	18.29
TRD450CR-7	7	2.13	TRD450CR-75	75	22.86
TRD450CR-10	10	3.05	TRD450CR-80	80	24.38
TRD450CR-15	15	4.57	TRD450CR-90	90	27.43
TRD450CR-20	20	6.1	TRD450CR-100	100	30.48
TRD450CR-25	25	7.62			

NOTES:

MATERIAL:

PLUG HOUSING: POLYCARBONATE, CLEAR, UL94V-0
 CONTACTS: PHOSPHOR BRONZE
 CABLE JACKET: PVC, GRAY

FINISH:

CONTACTS: 50 μINCHES GOLD IN CONTACT AREA
 OVER 100 μINCHES NICKEL PLATE OVERALL.

CABLE CHARACTERISTICS:

UNSHIELDED TWO TWISTED PAIR MODULAR CABLE
 24 AWG STRANDED COPPER

MISCELLANEOUS:

PLUG CONFORMS TO TIA-1096
 OPERATING TEMPERATURE RANGE: -20°C TO +60°C
 CABLES TO BE TESTED FOR CONTINUITY
 CABLE ASSEMBLY SHALL BE INDIVIDUALLY PACKAGED IN ACCORDANCE WITH L-COM SPECIFICATION PS-0031.



REGULATORY COMPLIANCE:

CE2011/65/EU (RoHS DIRECTIVE)

UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE IN INCHES [mm] OVERALL CABLE LENGTH TOLERANCE: ≤12 [305] = +1 [25] / -0 >12 [305] ≤60 [1524] = +2 [51] / -0 >60 [1524] ≤120 [3048] = +4 [102] / -0 >120 [3048] ≤300 [7620] = +6 [152] / -0 >300 [7620] = +5% / -0% ALL OTHER DIMENSIONAL TOLERANCES: .X = ± .2 [5.08] .XX = ± .02 [5.1] .XXX = ±.005 [1.3]	APPROVALS	DATE	45 BEECHWOOD DRIVE NORTH ANDOVER, MA 01845
	DRAWN BY D. PARHAM	08/29/2006	
PROJECTION 	APPROVED BY J. KIEZULAS	08/31/2006	CATEGORY TELECOM/MODULAR
	CONFIGURATION DETAILS OF UNDIMENSIONED FEATURES MAY VARY COLOR VARIATIONS MAY OCCUR	PRODUCT DESCRIPTION CBL RJ45/RJ45 CAT5E XOVER	SIZE A FSCM NO. 43321 DWG. NO. TRD450CR REV. E
SCALE: NONE		CAD FILE: TRD450CR.SLDDRW	
			SHEET 1 OF 1