






THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF L-COM, INC. ANY REPRODUCTION IN PART OR WHOLE WITHOUT THE WRITTEN PERMISSION OF L-COM, INC. IS PROHIBITED.

REVISIONS			
REV	DESCRIPTION	DATE	APPROVED
A	DRAWING REPLACES UAD016MM-OD1 AT REV E	11/19/14	D. CASTRO



WIRE MAP	
"P1"	"P2"
1	1
2	2
3	3
4	4
GRD	GRD

**NOTES:**

**MATERIALS:**  
OVERMOLD: PVC  
CONTACTS: BRASS  
INSULATOR: PBT, UL94V-0

**FINISH:**  
SHELL: NICKEL SILVER  
CONTACTS: GOLD OVER NICKEL

**ELECTRICAL:**  
CURRENT RATING: 3 AMP  
DIELECTRIC STRENGTH: 1000V AC FOR ONE MINUTE  
INSULATOR RESISTANCE: 1000Ω MIN AT 500V DC

**MISCELLANEOUS:**  
ADAPTER SHALL BE USB 2.0 COMPLIANT.  
ALL DIMENSIONS ARE FOR REFERENCE ONLY.  
ADAPTER SHALL BE TESTED FOR CONTINUITY.  
ADAPTER SHALL BE INDIVIDUALLY PACKAGED IN ACCORDANCE WITH L-COM SPECIFICATION PS-0031.

**REGULATORY COMPLIANCE:**  
CE2011/65/EU (RoHS DIRECTIVE)

UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE IN INCHES [mm] OVERALL CABLE LENGTH TOLERANCE: ≤12 [305] = +1 [25] / -0 >12 [305] ≤60 [1524] = +2 [51] / -0 >60 [1524] ≤120 [3048] = +4 [102] / -0 >120 [3048] ≤300 [7620] = +6 [152] / -0 >300 [7620] = +5% / -0%  ALL OTHER DIMENSIONAL TOLERANCES: .X = ±.2 [5.08] .XX = ±.02 [51] .XXX = ±.005 [1.27]	APPROVALS DRAWN BY C.MCCORMICK CHECKED BY D.PARHAM APPROVED BY R.CARRICK	DATE 12/18/2002 12/18/2002 12/18/2002	45 BEECHWOOD DRIVE NORTH ANDOVER, MA 01845	
	CATEGORY USB		PRODUCT DESCRIPTION ADPT, USB B-M/B-M	
	PROJECTION 	CONFIGURATION DETAILS OF UNDIMENSIONED FEATURES MAY VARY	COLOR VARIATIONS MAY OCCUR	SIZE <b>A</b> FSCM NO. <b>43321</b> DWG. NO. UAD016MM REV. <b>A</b>
	SCALE: NONE		CAD FILE: UAD016MM.SLDDRW	SHEET 1 OF 1