




THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF L-COM, INC. ANY REPRODUCTION IN PART OR WHOLE WITHOUT THE WRITTEN PERMISSION OF L-COM, INC. IS PROHIBITED.

REVISIONS			
REV	DESCRIPTION	DATE	APPROVED
E	ECN 6479: REVISE DESCRIPTION TO J1 FROM TYPE A TO B	10/19/12	D.FRISIELLO
F	ECN 7842: REVISED DIM .55 TO .58, FORMAT, ROHS	3/11/15	D.FRISIELLO



MODEL NUMBER	LENGTH METERS [FEET]
UPMBB-03M	0.3 [.98]
UPMBB-05M	0.5 [1.64]
UPMBB-075M	0.75 [2.46]
UPMBB-1M	1.0 [3.28]
UPMBB-2M	2.0 [6.56]
UPMBB-3M	3.0 [9.84]
UPMBB-4M	4.0 [13.12]
UPMBB-5M	5.0 [16.41]

- NOTES:
- CABLE ASSEMBLY SHALL HAVE 360° SHIELD TERMINATION.
  - CABLE ASSEMBLY SHALL MEET USB 2.0 REQUIREMENTS.
  - CABLE ASSEMBLY SHALL BE TESTED FOR CONTINUITY.
  - MOUNTING HARDWARE INCLUDED: 2X #4-40 X .38 LG. PHILLIPS HD SCREW
  - CABLE ASSEMBLY SHALL BE INDIVIDUALLY PACKAGED IN ACCORDANCE WITH L-COM SPECIFICATION PS-0031.

REGULATORY COMPLIANCE:  
CE2011/65/EU (RoHS DIRECTIVE)

UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE IN INCHES [mm]

OVERALL CABLE LENGTH TOLERANCE:  
 $\leq 12$  [305] = +1 [25] / -0  
 $>12$  [305]  $\leq 60$  [1524] = +2 [51] / -0  
 $>60$  [1524]  $\leq 120$  [3048] = +4 [102] / -0  
 $>120$  [3048]  $\leq 300$  [7620] = +6 [152] / -0  
 $>300$  [7620] = +5% / -0%

ALL OTHER DIMENSIONAL TOLERANCES:  
 .X = ± .2 [5.08]  
 .XX = ± .02 [51]  
 .XXX = ± .005 [1.27]

PROJECTION

APPROVALS	DATE
DRAWN BY D. PARHAM	01/04/2010
CHECKED BY D. CASTRO	01/12/2010
APPROVED BY S. SMITH	01/13/2010

**L-com** Global Connectivity 45 BEECHWOOD DRIVE NORTH ANDOVER, MA 01845

CATEGORY: USB

PRODUCT DESCRIPTION: CA USB-B PNL/USB-BM

SIZE <b>A</b>	FSCM NO. <b>43321</b>	DWG. NO. <b>UPMBB</b>	REV. <b>F</b>
------------------	--------------------------	--------------------------	------------------

SCALE: NONE CAD FILE: UPMBB.SLDDRW SHEET 1 OF 1