









THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF L-COM, INC. ANY REPRODUCTION IN PART OR WHOLE WITHOUT THE WRITTEN PERMISSION OF L-COM, INC. IS PROHIBITED.

REVISIONS			
REV	DESCRIPTION	DATE	APPROVED
A	INITIAL RELEASE	02/18/2022	GUTTADAURO




NOTES:

MATERIAL:
 FRONT SHELL&BACK SHELL: COLD ROLLED STEEL
 INSULATION: THERMOPLASTIC,UL 94V-0 RATED, BLUE
 CONTACTS: COPPER ALLOY

FINISH:
 SHELLS: NICKEL PLATED
 CONTACTS: 30μ" GOLD PLATED OVER NICKEL PLATED

MISCELLANEOUS:
 CONTACT CURRENT RATING: POWER PIN 1.8A, OTHER 0.25A MAX.
 DIELECTRIC WITHSTANDING VOLTAGE: AC 100V FOR A MINUTE
 INSULATION RESISTANCE: 100 MEGOHMS MIN.
 CONTACT RESISTANCE: 30 MILLIOHMS MAX.
 OPERATING TEMPERATURE: -40 °C TO +85 °C.
 INSERTION FORCE: 35N MAX.
 EXTRACTION FORCE: 10N MIN.
 DURABILITY: 1500 CYCLES MIN.
 COMPONENT SHALL BE INDIVIDUALLY PACKAGED IN ACCORDANCE WITH L-COM SPECIFICATION PS-0031.

UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE IN INCHES [mm] OVERALL CABLE LENGTH TOLERANCE: ≤12 [305] = +1 [25] / -0 >12 [305] ≤60 [1524] = +2 [51] / -0 >60 [1524] ≤120 [3048] = +4 [102] / -0 >120 [3048] ≤300 [7620] = +6 [152] / -0 >300 [7620] = +5% / -0 ALL OTHER DIMENSIONAL TOLERANCES: .X = ± .2 [5] FRACTIONS ± 1/32 .XX = ± .02 [.5] ANGLES ± 1° .XXX = ± .005 [.13]	APPROVALS	DATE	 50 High Street, West Mill, North Andover, MA 01845 USA. Phone: 1.800.341.5266 1.978.682.6936	
	DRAWN BY SLI	01/26/2022		
	CHECKED BY GUTTADAURO	01/26/2022	CATEGORY	USB
	APPROVED BY GUTTADAURO	01/26/2022	PRODUCT DESCRIPTION	CONN USB 3.0 TYPE B MALE
THIRD-ANGLE PROJECTION	CONFIGURATION DETAILS OF UNDIMENSIONED FEATURES MAY VARY	COLOR VARIATIONS MAY OCCUR	SIZE A CAGE CODE 43321 DWG. NO. USBCN3-B REV. A SCALE: NONE CAD FILE: USBCN3-B.SLDDRW SHEET 1 OF 1	