


THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF L-COM, INC. ANY REPRODUCTION IN PART OR WHOLE WITHOUT THE WRITTEN PERMISSION OF L-COM, INC. IS PROHIBITED.

REVISIONS			
REV	DESCRIPTION	DATE	APPROVED
A	INITIAL RELEASE	12/08/2017	B.ZHANG



MODEL NUMBER	LENGTH FEET [METERS]
VMA00001-3F	3 [.914]
VMA00001-5F	5 [1.524]
VMA00001-10F	10 [3.048]
VMA00001-15F	15 [4.572]
VMA00001-25F	25 [7.620]

WIRING MAP		
P1	COLOR	P2
TIP	BLACK	TIP
RING	RED	RING
SLEEVE	SHIELD	SLEEVE

- NOTES:**
- LSZH CABLE CHARACTERISTICS  
 FLAME RATING: IEC 60332-1  
 CORROSIVE GAS: IEC 60754  
 SMOKE EMISSION: IEC 61034
  - CABLE ASSEMBLY SHALL BE TESTED FOR CONTINUITY.
  - CABLE ASSEMBLY SHALL BE INDIVIDUALLY PACKAGED IN ACCORDANCE WITH L-COM SPECIFICATION PS-0031.
- REGULATORY COMPLIANCE:**  
 CE2011/65/EU(RoHS DIRECTIVE)

UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE IN INCHES [mm] OVERALL CABLE LENGTH TOLERANCE: $\leq 12$ [305] = +1 [25] / -0 $> 12$ [305] $\leq 60$ [1524] = +2 [51] / -0 $> 60$ [1524] $\leq 120$ [3048] = +4 [102] / -0 $> 120$ [3048] $\leq 300$ [7620] = +6 [152] / -0 $> 300$ [7620] = +3% / -0% ALL OTHER DIMENSIONAL TOLERANCES: .X = ± .2 [5.08] .XX = ± .02 [51] .XXX = ± .005 [1.27]	APPROVALS B.ZHANG	DATE 11/02/2017		50 HIGH STREET NORTH ANDOVER, MA 01845		
	CHECKED BY B.GATES	DATE 11/03/2017		CATEGORY AUDIO/VIDEO		
	APPROVED BY B.GATES	DATE 11/03/2017	PRODUCT DESCRIPTION CA, 3.5mm AUDIO STEREO M/M LSZH			
	PROJECTION 	CONFIGURATION DETAILS OF UNDIMENSIONED FEATURES MAY VARY	COLOR VARIATIONS MAY OCCUR	SIZE <b>A</b>	FSCM NO. <b>43321</b>	DWG. NO. VMA00001
SCALE: NONE			CAD FILE: VMA00001.SLDDRW		SHEET 1 OF 1	