


THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF L-COM, INC. ANY REPRODUCTIONS IN PART OR WHOLE WITHOUT THE WRITTEN PERMISSION OF L-COM, INC. IS PROHIBITED.

REVISIONS			
REV	DESCRIPTION	DATE	CHANGED BY
A	DRAWING REPLACES WPHD15CA-OD1 AT REV B	12/01/2014	D.CASTRO
B	ECN 9762: REMOVED 2X THUMBSCREWS FROM J1	04/05/2019	BGATES



NOTES:

1. WALL PLATE MATERIAL: STAINLESS STEEL
2. SPECIFICATIONS
 - 2.1 CABLE:
 - U.L. STYLE 2919
 - CONDUCTORS: FIVE MINIATURE 75Ω COAXIAL
 - SHIELDING: ALUMINIZED MYLAR AND COPPER BRAID
 - JACKET: GRAY PVC
 - 2.2 D-SUB CONNECTOR
 - INSULATOR: UL94V-0 THERMOPLASTIC
 - CONTACTS: GOLD PLATED
 - SHELL: TIN FINISH
 - HOOD: GRAY PVC
 - HARDWARE: 4-40UNC
 - 2.3 BNC
 - SHELL: NICKEL PLATED BRASS
 - CONTACTS: GOLD PLATED BRASS
 - INSULATOR: DELRIN
 - CHARACTERISTIC IMPEDANCE: 75Ω
 - STRAIN RELIEF: GRAY PVC
3. ALL BNC SHIELDS ELECTRICALLY TIED TO HDB15F SHELL.
4. CABLE ASSEMBLY SHALL BE TESTED FOR CONTINUITY.
5. CABLE ASSEMBLY SHALL BE INDIVIDUALLY PACKAGED IN ACCORDANCE WITH L-COM SPECIFICATION PS-0031.

WIRE MAP	
J1	BNC JACKS
PIN 1	J2
PIN 2	J3
PIN 3	J4
PIN 4	N/C
PIN 5	SHIELD
PIN 6	SHIELD
PIN 7	SHIELD
PIN 8	SHIELD
PIN 9	N/C
PIN 10	SHIELD
PIN 11	N/C
PIN 12	N/C
PIN 13	J6
PIN 14	J5
PIN 15	N/C
SHELL	SHIELD

UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE IN INCHES [mm]
 OVERALL CABLE LENGTH TOLERANCE:
 ≤12 [305] = +1 [25] / -0
 >12 [305] ≤60 [1524] = +2[51] / -0
 >60 [1524] ≤120 [3048] = +4 [102] / -0
 >120 [3048] ≤300 [7620] = +6 [152] / -0
 >300 [7620] = +5% / -0%
 ALL OTHER DIMENSIONAL TOLERANCES:
 .X = ±.2 [5.08]
 .XX = ±.02 [5.1]
 .XXX = ±.005 [1.3]

APPROVALS	DATE
DRAWN BY B.MAZEJKA	09/25/2003
CHECKED BY D.PARHAM	09/26/2003
APPROVED BY C.MCCORMICK	09/26/2003

L-com Global Connectivity
 50 HIGH STREET
 NORTH ANDOVER, MA
 01845

CATEGORY AUDIO/VIDEO			
PRODUCT DESCRIPTION WLPLTE ASSMBLY HD15F- 5 BNC F			
SIZE B	FSCM NO. 43321	DWG. NO. WPHD15CA	REV. B
SCALE: 1:1.5 CAD FILE: WPHD15CA.SLDDRW			SHEET 1 OF 1

