

HyperLink Wireless brand Weatherproof Hi-Power 10/100 Base-T CAT5 Lightning and Surge Protector - Model: AL-CAT5HPWT

Applications

- Wireless Access Points, Servers & Outdoor Routers
- IP, Network or Web Cameras
- VoIP Telephone
- 10/100 Base-T Networks

Features

- Individual protection for all 8 wires
- Three-Stage protection
- Superior to diode or TVS only based designs
- Weatherproof ABS enclosure with removable screw terminal blocks
- 802.3af Modes A and B Power-Over-Ethernet



(Shown with cover removed)

Description

The AL-CAT5HPWT is a high performance 3-stage weatherproof protector that provides superior protection 10/100 Base-T networks. This model is fully compatible with industry-standard Power-over-Ethernet (PoE) devices and provides individual protection to both the Ethernet data pairs as well as the PoE DC power feeds. The unit supports both modes A and B of the 802.3af standard for of supplying DC power.

The first stage is comprised of a differential gas discharge tube. Stage two is a pair of current limiting series resistors and the final stage is a low capacitance diode array. The second stage series resistance limits the power dissipation of the fast diode clamp array in the third stage. This allows time for the slower but higher power gas tubes to flash over. The diode array clamps the leading edge of fast transients to safe levels until the high power gas tubes turn on. This eliminates the damaging leading edge spike that single stage gas tube protectors let leak through. The diode array's low capacitance assures that the suppressor will not degrade the high-speed signals. The 3-stage design can handle higher-level transients than a protector that uses only diodes. The design utilizes Thyristor diode technology which has superior power handling capability compared to TVS or Avalanche diode based designs.

Failsafe Feature

The AL- CAT5HPWT series is designed to convert into a failsafe mode in the rare case of a catastrophic surge or lightning event. For this mode, the resistors in the second stage will fuse and portions of the diode array will short. This effectively disconnects the line from sensitive equipment thus limiting damage. The units are factory repairable.



These protectors feature a weatherproof ABS enclosure with gasketed cover and concealed mounting holes. Removable screw terminal strips are provided on the input and output for convenience. To ease installation, the terminal strips can be removed. A ground clamp provides a tie point for earth ground.

Specifications

Mechanical Specifications

Enclosure Material	Dark Gray ABS
Ground Lug	10 AWG Max.
Operating Temperature	-40 C (-40 F) to +80 C (+176 F)
Weight	.38 lbs. (.17 kg)
Dimensions	6.3 x 3.15 x 2.17 (in) 160 x 80 x 55 (mm)
RoHS Compliant	Yes

Electrical Specifications

Connectors	(2) Screw Terminal Blocks
Stage 1 Clamping Voltage	± 90 volts
Stage 2 Resistance	3.3 Ohms
Stage 3 Clamping Voltage	± 58 volts
PoE Mode Support	Mode A and B for power

