

0-6 GHz Lightning Surge Protector RP-SMA Plug to RP-SMA Jack Bulkhead Model: AL6-RSPRSJBW-9

Applications and Features

- Applications:**
- IEEE 802.11b and 802.11g Wireless LAN Applications
 - ISM
 - MMDS
 - Cellular
 - PCS Applications
- Features:**
- Reliable Performance from DC ~ 6 GHz
 - High Quality Construction
 - Easily Replaced Gas Tube Element
 - Multi-Strike Capability
 - Bi-Directional Protection / Protector will pass I



Product Description


The AL6-RSPRSJBW-9 is a very high-performance gas discharge tube suppressor featuring wide-band operation up to 6 GHz. The unit features a bulkhead Reverse Polarity SMA Jack connector for mounting through an enclosure wall or using the optional stainless steel mounting bracket.

Due to its superior RF performance this unit is ideal for IEEE 802.11a and other 5.2 - 5.8 GHz ISM and UNII applications, as well as 3.5 GHz WLL applications. Since this protector will pass DC it is suitable for applications where DC is carried through the coax cable such as remote amplifiers and LNA's.

Both connector ports of this unit are equally protected. This provides protection no matter which way it is installed. Either port can face the antenna and either port can face the equipment.

The unit's replaceable gas tube element, multi-strike capability and fast response time make it suitable for a wide range of applications. A ground lug and terminal is provided directly on the lightning protector housing, which provides superior grounding.

Replacement gas tubes are available (LPX090-6) as well as an optional stainless steel mounting bracket (HGX-LPMOUNT01).



Specifications

Electrical Specifications

Frequency Range	0 - 6 GHz
VSWR	1:1.2 Max (0 - 6 GHz)
Insertion Loss	0.6 dB Max (0 - 6 GHz)
Impedance	50 Ohm
Gas Tube Breakdown Voltage	90 V ± 20%

Mechanical Specifications

Connectors	RP-SMA Plug to RP-SMA Jack Bulkhead
Connector Body Material	Nickel Plated Brass
Body Material	Nickel Plated Brass
Pin Material	Gold Plated Brass
"O"-Ring Material	Rubber
Dimensions (max)	2.0 x 0.9 x 1.2 in (52.3 x 23 x 31 mm)
Weight	0.25 lbs. (0.11 kg)

