



Digital Video Extender
Low Power, Small Form Factor,
HDMI with Audio

ADDERLink DVI04T

Digital video/audio switch and extender to drive up to four remote displays



PRODUCT IN BRIEF

ADDERLink DVI04T is a high performance digital video extender and splitter that enables you to locate your critical play out hardware in a secure and temperature controlled environment away from the display point environment whilst maintaining the same user experience.

- Proof of Display (P.O.D.)
- 50 meter extension distance
- Plug and Play
- Two video inputs, four video outputs
- 2x4 HD Digital matrix
- Line powered receivers

FEATURES

Two video inputs, four video output splitter and extender

The ALDVI04 is an intelligent non blocking cross point switch and extender. These configurations can be selected dynamically via the web interface or controlled by a 3rd party control system.

Proof of display via IP network

The unit determines if the entire system is operating correctly and video is visible on the monitors. It can detect if video is present from the player and whether the cables to the monitors are attached and the monitor is turned on. This information is available by an IP socket thus allowing remote diagnostics and integration into content management systems.

Source failover

The unit can be set to detect that a video stream is present at the input. The unit can be set to automatically switch over to the second video input if the primary fails.

Security

Security on the web interface is by HTTP digest authentication (RFC 2617) with username and password as requested information.

API for 3rd party integration

The API documentation to control and receive data from the unit is provided with the system.

Digital audio

Supports 8 channels of HDMI audio.

Perfect HD Digital Video

The ALDVI04T uses an uncompressed video system where every frame is sent without loss with resolutions up to 1920 x 1200@60Hz (WUXGA) including 1080p, 720p and 480p resolutions.

50 meters over a single CATx cable

Video, audio and power all pass along a single CATx cable, providing up to 50m of extension. Distance can be dependent upon CATx cable types and the number of connection breaks for patch panels and wall plates. See overleaf for details.

Dual head extension

With two inputs, the system is suited to extending and splitting dual head systems.

Highly energy efficient - no external power supplies are required


The receivers are designed to be highly power efficient, using less than an eighth of the power required by competing systems. Power is supplied along the CATx cable meaning the support infrastructure required is minimal.

EDID management

The system has intelligent EDID management allowing the true characteristics of the monitor to be passed back to the computer.

Plug and Play

The DVI04T is delivered in a zero config state so you can plug and play. There is no need for additional drivers or software.



ADDERLink DVI04T

Digital video/audio switch and extender to drive up to four remote displays

EXTENSION DISTANCE INFORMATION

Recommended cables are CAT7a shielded foiled twisted pairs:

Resolution	Cable type	Patch connections	Total distance
1920 x 1200@60Hz	CAT7a	0	50 meters
1920 x 1200@60Hz	CAT6a (shielded)	0	50 meters
1920 x 1200@60Hz	CAT6a (shielded)	2	40 meters
1920 x 1200@60Hz	CAT7a	2	40 meters

Daetwyler 7702 Flexible patch cable
Daetwyler 7120 Bulk cable

Category 6 (or better) shielded twisted pair cable must be used to connect the local and remote units in order to maintain compliance with radio frequency energy emission regulations and ensure a suitably high level of immunity to electromagnetic disturbances.

TECHNICAL SPECIFICATIONS

Hardware compatibility

All computers with HDMI connections - requirement dependent. Will also connect to DVI/DisplayPort with suitable cables

HDMI interface

The system supports resolutions such as 480p, 720p, 1080P or WUXGA (1920x1200) @60Hz and 24 bit color depth. Does not support HDCP

Software compatibility

All known operating systems

Audio

The system delivers eight channels of HDMI audio with sample sizes of 16, 20 or 24 bit at 32kHz, 44.1kHz, 48kHz, 88.2kHz, 96kHz, 176.4kHz, or 192kHz

Connections

2 x HDMI type A male,
4 x CATx sockets for link outputs,
1 x 10/100Base-TX network port (config),
1 x 6P6C RJ12 connector (options port)
2.5mm DC power jack

Operating temperature

0 to 40°C / 32 to 104°F

ORDERING INFORMATION

ALDV104K-XX: DVI04 Transmitter unit plus 4 receivers
ALDV104T-XX: ALDV104T only
XX = Mains Lead Country Code:
UK = United Kingdom
US = United States
EURO = Europe
AUS = Australia

ADDITIONAL ACCESSORIES

VSCD12: locking HDMI 1.5 metre cable
VSCAT7-50: 50m CAT7 Shielded foiled twisted pair cable
ALAV-RMK-CHASSIS: 19" 3U rack mount chassis
ALDV-RMK-FASCIA: Universal fascia & mounting kit
ALDV100R - HDMI receiver
ALDV120R - DVI-D receiver

Physical design

Compact case, robust metal construction:
115mm / 4.5" (w) x 114mm / 4.5" (d) x
26mm / 1" (h). Weight 440g / 0.97 lb

Power

3pin Toby jack (power adapter included), 100-240VAC 50/60Hz, 0.8A, input to power adapter. 12VDC 18W output from power adapter

Approvals

CE, FCC

RELATED PRODUCTS

Adder offer a vast range of products to suit your needs. Other products you may be interested in include:

ADDERLink DV120
ALDV120P;ALDV120R



ADDERLink DV100
ALDV100P;ALDV100R



ADDERLink LPV150
ALPV150P;ALPV150R



ADDERLink LPV154T
ALPV154T



Proof Of Display (P.O.D):

Adder's unique P.O.D. system can be accessed by any computer, connected to your network.

© Copyright 2014 Adder Technology Ltd. All brand names and trademarks are the property of their respective owners. LM-ALDV104t_v6.indd

ADDER TECHNOLOGY

Head Office
Tel: +44 (0)1954 780044 Fax: +44 (0)1954 780081
email: sales@adder.com www.adder.com

ADDER CORPORATION

USA and Canada
Tel: +1 888 932 3337 Fax: +1 888 275 1117
email: usasales@adder.com www.adder.com

ADDER ASIA

Asia Pacific
Tel: +65 6288 5767 Fax: +65 6284 1150
email: asiasales@adder.com www.adder.com

