

**Outlet Tester  
Model OT-2**



**► FEATURES**

- Detects faulty wiring in three-wire receptacles
- Detects open grounds and neutrals
- Detects reversed hot/ground connections
- Simply plug in and note red and amber indicators
- For use on 100 to 125Vac

**► APPLICATIONS**

- Test GFCI for proper operation
- 120V - three-wire US

**AC Line Splitter  
Model ALS-1**

**For use with clamp-on meters & multimeters using current probes**



**► FEATURES**

- Avoids splitting lines - makes reading current easy
- Increases sensitivity of clamp-on current probes and clamp-on meters ten times in X10 mode

- Direct reading X1 mode
- Voltmeter input jacks
- Integral ground conductor
- Facilitates reading current draw of device plugged into it
- Facilitates reading current draw through extension cords
- 120V, 15A capacity

**Non-Contact AC Voltage Detector  
Model NC-1**



**► SPECIFICATIONS**

MODEL	NC-1
<b>Voltage Sensitivity</b>	100 to 240Vac
<b>Frequency</b>	50/60Hz
<b>Detection Distance</b>	<5mm
<b>Over Voltage</b>	600V CAT III
<b>Battery</b>	2 x 1.5V AAA Alkaline (included)
<b>Safety</b>	For indoor use and in accordance with over voltage 600V CAT III, Pollution Degree 2

CATALOG NO.	DESCRIPTION	PRICE	NIST CALIBRATION
2121.03	Outlet/GFCI Tester Model OT-2 (110V US)	\$ 7.95	-
2121.05	AC Line Splitter Model ALS-1	\$14.95	-
2121.09	Non-Contact AC Voltage Detector Model NC-1	\$ 9.95	-

