

Fiber Optic Sensor Cable, 2M Flat Bracket Type, Thru-beam, R2 POF, 4 mm Thick Rectangular Sensing End and Flat Side Beam Exit



FOACAMPTF54UA

Fiber Optic Sensor Cable

Features

- Durable stainless steel head
- Flexible jacket
- Standard 2.2mm diameter ferrules
- Stable performance

Applications

- Industrial automation
- Discrete manufacturing
- High volume production
- Automotive manufacturing
- Stamping and plastic injection molding
- Packaging
- Food and Beverage
- Warehouse automation

Description

L-com's FOACAMPTF54UA fiber optic sensor cable is a thru-beam type optical cable. This 2M (meter) fiber optic sensor cable is in stock and ready to ship on the same business day of the order. Our black thru-beam sensor cable has a durable stainless steel head, R2 bend radius, and flexible polyethylene jacket, which makes the cable well-suited for demanding industrial environments. The 2.2mm amplifier ends make this cable compatible with industry-standard amplifier ports, making interchanging quick and easy.

General Specifications

Type	Flat Bracket
Design Type	Thru-beam
Cable Type	POF
Jacket Type	PE Black
Sensing Distance	450 to 1,300 mm
Cable Length	2 m
Cable Head Material	Stainless Steel
Bend Radius	2 mm
Compatible Products	Fiber Optic Sensor Amplifiers
Detected Object	0.05mm
Beam Exit	Flat Side
Cable Head Shape	Rectangular
Notes, Electrical/Optical	Minimum sensing distance with FOACAMPG1 amp, maximum sensing distance with FOACAMPC1 amp
Notes	Different amplifiers will impact sensing distance.

Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications:
[Fiber Optic Sensor Cable, 2M Flat Bracket Type, Thru-beam, R2 POF, 4 mm Thick Rectangular Sensing End and Flat Side Beam Exit FOACAMPT-](#)

Fiber Optic Sensor Cable, 2M Flat Bracket Type, Thru-beam, R2 POF, 4 mm Thick Rectangular Sensing End and Flat Side Beam Exit



FOACAMPTF54UA

Fiber Optic Sensor Cable

Environmental Specifications

Temperature

Operating Range -20 to +50 deg C

Storage Range -30 to +85 deg C

Humidity

Operating Relative 35% to 85%

Compliance Certifications

CE Compliance Yes

Fiber Optic Sensor Cable, 2M Flat Bracket Type, Thru-beam, R2 POF, 4 mm Thick Rectangular Sensing End and Flat Side Beam Exit from L-com has same day shipment for domestic and International orders. Our portfolio includes coaxial cable assemblies, connectors, adapters and custom products as well as lightning and surge protectors, NEMA rated enclosures, and an RF product line which includes antennas, amplifiers, passive, and active components.

The information contained within this document is accurate to the best of our knowledge and representative of the part described herein. It may be necessary to make modifications to the part and/or the documentation of the part in order to impliment improvements. L-com reserves the right to make such changes as required. Unless otherwise stated, all specifications are nominal. L-com does not make any representation or warranty regarding the suitability of the part described herein for any particular purpose, and L-com does not assume liability arising out of the use of any part or document.

Fiber Optic Sensor Cable, 2M Flat Bracket Type, Thru-beam, R2 POF, 4 mm Thick Rectangular Sensing End and Flat Side Beam Exit

L-com CAD Drawing

