

Fiber Optic Transceiver, SFP, 850nm, SX MMF 550m, 1000Base DDM, Juniper



FXC-SFP-SX-1G-JUN

Features

- Operating Data Rate up to 1.25 Gbps
- Distance Range 550M
- Single 3.3V Power Supply and TTL Logic Interface
- Pluggable SFP Duplex LC Connector
- Standard and Industrial Operating Temperature
- Compliant with Juniper SFP Specification

Applications

- Telecom (Service Provider)
- Datacom
- Enterprise Networks
- Government
- Fiber to the home/business

Description

The L-com FXC-SFP-SX-1G-JUN is an SFP form-factor transceiver, supporting 1G Ethernet rates. The L-com FXC-SFP-SX-1G-JUN supports 550M distance and it is Juniper compliant transceiver. The L-com FXC-SFP-SX-1G-JUN features digital diagnostics for performance monitoring of the transceiver. The L-com FXC-SFP-SX-1G-JUN is one of thousands of fiber optic connectivity products available from L-com in-stock and ready to ship. Contact our knowledgeable technical support and sales staff for your answers on fiber optic connectivity or other L-com products.

Configuration

Data Rate	1 Gbps
Form Factor	SFP
Connector	LC
Connector Mode	Duplex
Mode	Multimode
Distance	0.55 km
Mfg Platform Compatibility	Juniper

Electrical Specifications

Description	Minimum	Typical	Maximum	Units
Wattage			1.04	W
Power Supply Voltage Vcc	3.15	3.3	3.45	V
Power Supply Current Icc			300	mA

Optical Specifications

Description	Minimum	Typical	Maximum	Units
TX Center Wavelength	830	850	860	nm
TX Data Rate		1.25		Gbps
TX Spectral Width			0.85	nm
TX Average Output Power	-9.5		-3	dBm
TX Extinction Ratio	9			dB

Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications:
[Fiber Optic Transceiver, SFP, 850nm, SX MMF 550m, 1000Base DDM, Juniper FXC-SFP-SX-1G-JUN](#)

Fiber Optic Transceiver, SFP, 850nm, SX MMF 550m, 1000Base DDM, Juniper



FXC-SFP-SX-1G-JUN

RX Center Wavelength	760	860	nm
RX Receiver Sensitivity	-17		dBm
RX Receiver Overload		-3	dBm

Environmental Specifications

Temperature

Operating Range

0 to +70 deg C

Storage Range

-40 to +85 deg C

Notes:

Compliance Certifications (see [product page](#) for current document)

Plotted and Other Data


Notes:

Fiber Optic Transceiver, SFP, 850nm, SX MMF 550m, 1000Base DDM, Juniper



FXC-SFP-SX-1G-JUN

Small Form-factor Pluggable (SFP) Transceiver MultiSource Agreement (MSA)



Fiber Optic Transceiver, SFP, 850nm, SX MMF 550m, 1000Base DDM, Juniper



FXC-SFP-SX-1G-JUN




Figure 1. Diagram of Host Board Connector Block Pin Numbers and Names

Fiber Optic Transceiver, SFP, 850nm, SX MMF 550m, 1000Base DDM, Juniper from L-com has same day shipment for domestic and International orders. Our portfolio includes coaxial cable assemblies, connectors, adapters and custom products as well as lightning and surge protectors, NEMA rated enclosures, and an RF product line which includes antennas, amplifiers, passive, and active components.

The information contained within this document is accurate to the best of our knowledge and representative of the part described herein. It may be necessary to make modifications to the part and/or the documentation of the part in order to impliment improvements. L-com reserves the right to make such changes as required. Unless otherwise stated, all specifications are nominal. L-com does not make any representation or warranty regarding the suitability of the part described herein for any particular purpose, and L-com does not assume liability arising out of the use of any part or document.

L-com CAD Drawing

