

2300-2700/5150-5850/5900-7200 MHz, 16 / 18 / 17 dBi, Wifi MIMO Sector Antenna, 90-degree, +/-45 Dual Pol, 4-Port, Type N Female Connector



HG2371-17XP-090-4NF

Features

- Tri Band frequency coverage for 2.3 GHz to 2.7 GHz, 5.15 GHz to 5.85 GHz and 5.9 GHz to 7.2 GHz
- Very High Gain 17 dBi to 20 dBi Directional Antenna with 2X2 MIMO peak performance
- Supports low-latency, bandwidth-hungry applications like high-definition video and augmented reality/virtual reality applications
- 2 Type N female connector x (2.3 GHz to 2.7 GHz + 5.15 GHz to 5.85 GHz) and 2 Type N female connectors x (5.9 GHz to 7.2 GHz)
- 90° beamwidth with dual +/-45 slant polarization
- 100 W max input power per port
- Easy Install mounting bracket provided
- Weatherproof ABS – UV Resistance PVC radome

Applications

- 2X2 MIMO ready with Dual bands in one shell configuration
- Outdoor and indoor tri band Wi-Fi6 and Wi-Fi 6E 2.4/5GHz/6GHz applications support
- Wireless LAN systems & IEEE.802.16ax applications with MU-MIMO and OFDMA
- WiFi 6 and WiFi 6E enables higher data rates up to 35% with enhanced efficiency and speed
- Increased Bandwidth enhances spectral efficiency and supports faster radio applications
- Smart cities expansion for coverage and IOT / IIOT
- Point-to-point (PtP) or point-to-multipoint (PtMP) applications

Description

L-Com's WiFi 6e Sector Antenna HG2371-17XP-090-4NF is in stock and ready to ship on the same-day of order. The frequency range of the HG2371-17XP-090-4NF sector antennas is 2300 MHz to 7200 MHz with a gain of 16-18-17 dBi. This multi band MIMO antenna supports Wi-Fi latest frequency band and has a 90-degree beam width. The 4- ports 2300-5850 MHz sector antenna include N-type female connectors with +/-45 slant polarization.

The N-type MIMO omni antenna covers a wide range of frequency bands up to 7.2GHz and is shorter than 40-inches for universal zoning compliance. The HG2371-17XP-090-4NF unlicensed WiFi 6 frequency bands sector antenna is "future-proof" in regard to network capabilities without any add-ons. The type N female sector antenna can handle maximum input power of 100 watts and uses universal radio mounts.

The WiFi 6e antenna is 2x2 MIMO ready and offers Dual slant +/- 45 polarizations, degree and 90-degree options and covers extensive frequency bands up to 7.2 GHz. These Wi-Fi 6 antennas are a good fit for the telecommunications industry and for indoor (stadium, large arenas) plus outdoor applications. The HG2371-17XP-090-4NF antennas are equipped with universal radio brackets.

These MIMO multi-port Wi-Fi 6e antennas can operate in the unlicensed bands of 6 GHz. These omni antennas can also operate within the latest Wi-Fi bands of 2.3 GHz to 5.8 GHz.

Contact L-Com's expert technical support for assistance with the Wi-Fi 6 sector antenna or any sector antenna. Download our HG2371-17XP-090-4NF datasheet with specifications and CAD drawing with dimensions for details. Our knowledgeable sales team simplifies the purchasing process and ensures that your Wi-Fi 6e sector antenna cable will be exact to specification.

Order your Wi-Fi 6e Sector Antenna HG2371-17XP-090-4NF from L-com today. There is no MOQ (minimum order quantity) and the product ships same day from our warehouse

Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications: [2300-2700/5150-5850/5900-7200 MHz, 16 / 18 / 17 dBi, Wifi MIMO Sector Antenna, 90-degree, +/-45 Dual Pol, 4-Port, Type N Female Connector](#)

2300-2700/5150-5850/5900-7200 MHz, 16 / 18 / 17 dBi, Wifi MIMO Sector Antenna, 90-degree, +/-45 Dual Pol, 4-Port, Type N Female Connector



HG2371-17XP-090-4NF

Configuration

Design	Sector
Band Type	Multi
Radiation Pattern	Omni Directional
Polarization	45 Deg. Slant
Connector Type	N Female
Interface 2	N Female
Interface 3	N Female
Interface 4	N Female
Number of Ports	4
Lightning Protection	DC Grounded

Electrical Specifications

Description	Minimum	Typical	Maximum	Units
Input VSWR			2:1	
Impedance		50		Ohms
Front to Back Ratio	25			dB
Electrical Downtilt		3		Degrees
Port to Port Isolation	25			dB
Input Power			100	Watts

Specifications by Band

Description	Band 1	Band 2	Band 3	Band 4	Band 5	Units
Range	2.3 to 2.7	5.15 to 5.85	5.9 to 7.2			GHz
Gain	16	18	17			dBi
Horizontal HPBW	90	90	90			Degrees
Vertical HPBW	7	5	5			Degrees
Port to Port Isolation	25	25	25			dB
Front to Back Ratio	25	25	25			dB

Mechanical Specifications

Radome Material	PVC
Size	
Length	35.43 in [899.92 mm]
Width	11.02 in [279.91 mm]
Height	3.14 in [79.76 mm]

2300-2700/5150-5850/5900-7200 MHz, 16 / 18 / 17 dBi, Wifi MIMO Sector
Antenna, 90-degree, +/-45 Dual Pol, 4-Port, Type N Female Connector



HG2371-17XP-090-4NF

Mounting Mast Diameter	1.181 to 2.362 in [30.00 to 59.99 mm]
Weight	12.12 lbs [5.5 kg]

Environmental Specifications

Temperature

Operating Range	-40 to +60 deg C
Wind Survivability	134 MPH [215.65 KPH]

Compliance Certifications (see [product page](#) for current document)

Plotted and Other Data

Notes:


2300-2700/5150-5850/5900-7200 MHz, 16 / 18 / 17 dBi, Wifi MIMO Sector Antenna, 90-degree, +/-45 Dual Pol, 4-Port, Type N Female Connector



HG2371-17XP-090-4NF


Frequency: 2300 MHz

Gain: 14.74 dBi



Frequency: 5700 MHz

Gain: 14.73 dBi



2300-2700/5150-5850/5900-7200 MHz, 16 / 18 / 17 dBi, Wifi MIMO Sector Antenna, 90-degree, +/-45 Dual Pol, 4-Port, Type N Female

2300-2700/5150-5850/5900-7200 MHz, 16 / 18 / 17 dBi, Wifi MIMO Sector
Antenna, 90-degree, +/-45 Dual Pol, 4-Port, Type N Female Connector

HG2371-17XP-090-4NF



Connector from L-com has same day shipment for domestic and International orders. Our portfolio includes coaxial cable assemblies, connectors, adapters and custom products as well as lightning and surge protectors, NEMA rated enclosures, and an RF product line which includes antennas, amplifiers, passive, and active components.

The information contained within this document is accurate to the best of our knowledge and representative of the part described herein. It may be necessary to make modifications to the part and/or the documentation of the part in order to impliment improvements. L-com reserves the right to make such changes as required. Unless otherwise stated, all specifications are nominal. L-com does not make any representation or warranty regarding the suitability of the part described herein for any particular purpose, and L-com does not assume liability arising out of the use of any part or document.

2300-2700/5150-5850/5900-7200 MHz, 16 / 18 / 17 dBi, Wifi MIMO Sector Antenna, 90-degree, +/-45 Dual Pol, 4-Port, Type N Female Connector

L-com CAD Drawing

