

## HyperLink Wireless Brand 698-960/1710-2170 MHz 4/7 dBi Omni DAS Antenna Model: HG72107U-PRO

### Applications

- DAS (Distributed Antenna Systems)
- 700 MHz and cellular applications
- AWS (Advanced wireless services) band applications
- PCS (Personal communications service) band applications
- LTE networks

### Features

- Frequency coverage for 700 MHz, 850 MHz, AWS and PCS bands
- All weather operation
- Heavy duty steel mounting brackets
- Integral N-Female connector
- Internal combiner eliminates the need for separate coax cables for each frequency



### Description

The HyperLink HG72107U-PRO is a professional grade Omni-directional antenna specifically designed for DAS (Distributed Antenna Systems). This outdoor all weather antenna helps wireless carriers to quickly increase capacity as well as deploy new spectrum in zoning challenged locations. The HG72107U-PRO combines several different frequency bands to allow multi-user options. Applications for the HG72107U-PRO include:

- Densely populated urban areas
- Educational campuses
- Resorts and theme parks
- Parks and nature centers

### Rugged and Weatherproof

This antenna's construction features a durable fiberglass radome for durability and aesthetics. Its mounting system features twin heavy-duty mounting brackets and U-Bolts for superior strength. The thick brass elements provide long life in hostile environments.

### Single Antenna Feed

The HG72107U-PRO features a single N-Female connector due to the antenna's internal combiner. This simplifies installation since only one coax cable is required to be sent to the antenna.



**Specifications**

**Electrical Specifications**

<b>Frequency Range</b>	698 – 960 MHz	1710 – 2170 MHz
<b>Gain</b>	4 dBi	7 dBi
<b>Horizontal Beamwidth</b>	360°	
<b>Vertical Beamwidth</b>	55°	28°
<b>Polarization</b>	Vertical	
<b>Impedance</b>	50 Ohm	
<b>Max. Input Power</b>	200 Watts	
<b>VSWR</b>	< 1.8	
<b>Lightning Protection</b>	DC Short	

**Mechanical Specifications**

<b>Connector</b>	Integral N-Female
<b>Weight</b>	2.6 lbs (1.17 kg)
<b>Length</b>	40.25 in. (1.02m)
<b>Base Diameter / Radome Diameter</b>	1.69 in. (42.9mm) / 1.52 in. (38.6mm)
<b>Radome Material</b>	Gray Fiberglass Weatherproof
<b>Mounting Mast Size</b>	1.18 – 2.36 in. (30 – 60mm)
<b>Rated Wind Velocity</b>	130mph (210km/h)
<b>Operating Temperature</b>	-40° C to 85° C (-40° F to 185° F)
<b>RoHS Compliant</b>	Yes

**RF Antenna Patterns**

