

0.141 Semi Rigid Non-Magnetic Cable with Silver Plated Copper Conductor



LC141SRNM-BULK

Configuration

- Non-Magnetic Semi-Rigid Cable
- 1 Shield(s)

Features

- Max Frequency 34 GHz
- Magnetic Susceptibility 10⁻⁵

Applications

- General Purpose Test
- Medical
- Quantum Computing
- Custom Cable Assemblies
- Military and Aerospace

Description

L-com's 0.141 semi-rigid non-magnetic cable uses series coaxial is available for same-day shipping from our facility. LC141SRNM-BULK cables from L-com are great choices for solutions requiring high quality and rapid shipping. Our non-magnetic RF cable has a 50 Ohm impedance and is rated for a 34 GHz maximum operating frequency. This high-quality cable is part of a large selection of in-stock, commercial-off-the-shelf, and custom-built coaxial cable assemblies for RF and microwave that all ship the same business day as they are ordered.

These semi-rigid RF cable assemblies are built with RF shielding of 165 dB and have a cable weight of 0.0183 lbs/ft. Our RF coaxial cable has a 0.036-inch SPC (silver-plated copper) conductor and a bending moment of 0.250 lbs-ft. The coaxial RF cable has a maximum attenuation of 82.8 dB/100ft and a maximum power of 70 Watts at a frequency of 26.5 GHz.

The technical performance specifications of this 34 GHz cable are located on the LC141SRNM-BULK datasheet PDF, along with a CAD drawing and dimensions. Our non-magnetic RF cable has a PTFE dielectric type. This RF non-magnetic cable has a copper outer conductor and a maximum operating temperature of 125 deg C. The L-com 0.141 semi-rigid RF cable assembly data sheet with specs and drawing dimensions can be found on this product page just above.

0.141 semi-rigid non-magnetic cable is one of a large selection of in-stock RF products available. L-com not only has this off-the-shelf but also custom versions of our cable assemblies are available for same-day shipping, we have thousands of other products that have same day shipping. Our expert technical support and knowledgeable sales teams are ready to help and answer your RF coaxial cable assembly questions.

Electrical Specifications

Description	Minimum	Typical	Maximum	Units
Frequency Range	DC		34	GHz
Impedance		50		Ohms
Velocity of Propagation		69.5		%
Shielding Effectiveness	165			dB
Operating Voltage (AC)			5,000	Vrms

0.141 Semi Rigid SMA Non-Magnetic Cable with Silver Plated Copper Conductor



LC141SRNM-BULK

Performance by Frequency Band

Description	F1	F2	F3	F4	F5	Units
Frequency	0.5	1	5	10	18	GHz
Attenuation, Typ	7.6	11.1	28.1	43.4	63.6	dB/100ft
	24.93	36.42	92.19	142.39	208.66	
Input Power (CW), Max	600	450	180	120	73	Watts

Description	F6	F7	F8	F9	F10	Units
Frequency	26.5					GHz
Attenuation, Typ	82.8					dB/100ft
	271.65					
Input Power (CW), Max	70					Watts

Mechanical Specifications

Min. Bend Radius (Repeated) 0.25 in [6.35 mm]

Construction Specifications

Description	Material and Plating	Diameter
Inner Conductor	Silver Plated Copper , 1 Strands Strand(s)	0.036in 0.91mm
Conductor Type	Solid	
Dielectric	PTFE	0.118in [3mm]
	PTFE	
Outer Conductor	Copper	0.141 in 3.58 mm
	100% coverage	
Jacket	Copper	∅

Environmental Specifications

Temperature
 Operating Range -55deg C to +125deg C
 Storage Range -55deg C to +125deg C

0.141 Semi Rigid SMA Non-Magnetic Cable with
Silver Plated Copper Conductor



LC141SRNM-BULK


Compliance Certifications (see [product page](#) for current document)

Plotted and Other Data

0.141 Semi Rigid SMA Non-Magnetic Cable with Silver Plated Copper Conductor from L-com has same day shipment for domestic and International orders. Our portfolio includes coaxial cable assemblies, connectors, adapters and custom products as well as lightning and surge protectors, NEMA rated enclosures, and an RF product line which includes antennas, amplifiers, passive, and active components.

The information contained within this document is accurate to the best of our knowledge and representative of the part described herein. It may be necessary to make modifications to the part and/or the documentation of the part in order to implement improvements. L-com reserves the right to make such changes as required. Unless otherwise stated, all specifications are nominal. L-com does not make any representation or warranty regarding the suitability of the part described herein for any particular purpose, and L-com does not assume liability arising out of the use of any part or document.

0.141 Semi Rigid SMA Non-Magnetic Cable with Silver Plated Copper Conductor



REVISION					
ZONE	REV	DESCRIPTION	DATE	CHANGED BY	APPROVED
	A	INITIAL RELEASE	08/01/2023	DZINN	AGANWANI

L-com
an INFINITE® brand
Website: www.L-com.com
Phone: 1.800.341.5266 | 1.978.682.6936

INTERPRET ALL DIMENSIONS AND TOLERANCES PER ASME Y14.5
SCALE NONE SHEET 1 OF 1

UNLESS OTHERWISE SPECIFIED, DIMENSIONS IN [] ARE MILLIMETERS

TOLERANCES:
 .X = ±.2 (5)
 .XX = ±.02 (0.5)
 .XXX = ±.005 (0.13)
 ANGLES ± 1°
 CABLE LENGTH TOLERANCES:
 ≤ 12 [305] = ±.1 [25] / -0
 > 12 [305] ≤ 60 [1524] = ±.2 [51] / -0
 > 60 [1524] ≤ 120 [3048] = ±.4 [102] / -0
 > 120 [3048] ≤ 300 [7620] = ±.8 [20] / -0
 > 300 [7620] = ±.1 [2.5] / 0

ALL DIMENSIONS ARE FOR REFERENCE ONLY AND SUBJECT TO CHANGE WITHOUT NOTICE. UNIFORMITY IN SIZE AND LOCATION MAY VARY. COLORS MAY VARY.

DESCRIPTION: .141 DIA COAX CABLE, SEMI-RIGID, COPPER OUTER CONDUCTOR, NON-MAGNETIC

SIZE A CAGE CODE 43321 DRAWN BY DZINN ITEM NO LC141SRNM-BULK REV A

THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF INFINITE ELECTRONICS, INC. ANY REPRODUCTION IN PART OR WHOLE WITHOUT THE WRITTEN PERMISSION OF INFINITE ELECTRONICS, INC. IS PROHIBITED. THESE COMMODITIES, TECHNOLOGY OR SOFTWARE WERE EXPORTED FROM THE UNITED STATES IN ACCORDANCE WITH THE EXPORT ADMINISTRATION REGULATIONS. DIVERSION CONTRARY TO U.S. LAW PROHIBITED.