

Lead Free 1553 TRB 3-Lug Jack Bulkhead Non-Isolated to Blunt Cut Genderless Cable Assembly using 30-02001-LC Coax, 3 FT with Bend Relief



**LC3MSA00561-36**

**Configuration**

- Connector 1: TRB 3-Lug Jack Bulkhead Nonisolated
- Connector 2: Blunt Cut Genderless
- Cable Type: 30-02001-LC

**Features**

- MIL-STD-1553
- -20°C to +75°C
- 78 ohms

**Applications**

- MIL-STD-1553
- Data

**Description**

L-com's LC3MSA00561-36 is a lead free 1553 TRB 3-Lug jack bulkhead non-isolated to blunt cut genderless cable assembly using 30-02001-LC coax, 3 FT with bend relief and ships same-day. These flexible RF cable assemblies are ideal for applications where flexure is required. Our L-com TRB 3-Lug to Blunt Cut cable assembly has a jack to genderless gender configuration with 78 Ohm flexible 30-02001-LC series coax and operates to 400 MHz.

Custom versions of this TRB 3-Lug jack to TRB 3-Lug genderless cable, along with the rest of L-com's other RF assemblies, can also be built and shipped same day. Other available RF cable assembly value added services from L-com include connector orientation or clocking, heat shrink booting and custom labeling. RF testing can also be performed to document the electrical performance of your cable assembly. Contact a sales representative for testing or custom RF cable quotes. Part number LC3MSA00561-36 L-com Lead Free 1553 TRB 3-Lug Jack Bulkhead Non-Isolated to Blunt Cut Genderless Cable Assembly using 30-02001-LC Coax, 3 FT with Bend Relief data sheet PDF includes details of the RF product specifications, CAD drawing(s) and dimensions below.

**Electrical Specifications**

| Description            | Minimum | Typical      | Maximum | Units        |
|------------------------|---------|--------------|---------|--------------|
| Frequency Range        | DC      |              | 400     | MHz          |
| Capacitance            |         | 19.7 [64.63] |         | pF/ft [pF/m] |
| Operating Voltage (AC) |         |              | 1,000   | Vrms         |

Insertion Loss (Typ.)  
Electrical Specification Notes:

The Insertion Loss data above is based on the performance specifications of the coax and connectors used in this assembly. The Insertion Loss includes an estimated insertion loss of 0.1 dB per connector.

**Mechanical Specifications**

**Cable Assembly**

- Length\* 36 in [914.4 mm]
- Weight 0.179 lbs [81.19 g]

**Cable**

- Cable Type 30-02001-LC
- Impedance 78 Ohms

Lead Free 1553 TRB 3-Lug Jack Bulkhead Non-Isolated to Blunt Cut Genderless Cable Assembly using 30-02001-LC Coax, 3 FT with Bend Relief



## LC3MSA00561-36

|                                      |                      |
|--------------------------------------|----------------------|
| Inner Conductor Type                 | Stranded             |
| Inner Conductor Material and Plating | Copper, Silver       |
| Dielectric Type                      | PE                   |
| Shield Layer 1                       | Silver Plated Copper |
| Jacket Material                      | PVC, Blue            |
| One Time Minimum Bend Radius         | 2.42 in [61.47 mm]   |

### Connectors

| Description                           | Connector 1                         | Connector 2          |
|---------------------------------------|-------------------------------------|----------------------|
| Type                                  | TRB 3-Lug Jack Bulkhead Nonisolated | Blunt Cut Genderless |
| Impedance                             | 78 Ohms                             |                      |
| Contact Material and Plating          | Bronze, Gold 30 micro inches        |                      |
| Contact Plating Specification         | ASTM-B-488                          |                      |
| Dielectric Type                       | Teflon                              |                      |
| Outer Conductor Material and Plating  | Phosphor Bronze, Gold               |                      |
| Outer Conductor Plating Specification | 30 micro inches                     |                      |
| Body Material and Plating             | Brass, Nickel                       |                      |
| Body Plating Specification            | ASTM-B-733                          |                      |

### Environmental Specifications

#### Temperature

Operating Range -20 to +75 deg C

**Compliance Certifications** (see [product page](#) for current document)

### Plotted and Other Data

Notes:

Lead Free 1553 TRB 3-Lug Jack Bulkhead Non-Isolated to Blunt Cut Genderless Cable Assembly using 30-02001-LC Coax, 3 FT with Bend Relief



## LC3MSA00561-36

### How to Order

Part Number Configuration:

**LC3MSA00561**

- **xx**

**uu**

Unit of Measure:  
cm = Centimeters  
<blank> = Inches  
Length  
Base Number


Example: LC3MSA00561-12 = 12 inches long cable  
LC3MSA00561-100cm = 100 cm long cable

Lead Free 1553 TRB 3-Lug Jack Bulkhead Non-Isolated to Blunt Cut Genderless Cable Assembly using 30-02001-LC Coax, 3 FT with Bend Relief from L-com has same day shipment for domestic and International orders. L-com is a leading manufacturer of wired and wireless connectivity products and committed to in-stock availability and same day shipping. Our portfolio includes coaxial cable assemblies, connectors, adapters and custom products as well as lightning and surge protectors, NEMA rated enclosures, and an RF product line which includes antennas, amplifiers, passive, and active components.

The information contained within this document is accurate to the best of our knowledge and representative of the part described herein. It may be necessary to make modifications to the part and/or the documentation of the part in order to implement improvements. L-com reserves the right to make such changes as required. Unless otherwise stated, all specifications are nominal. L-com does not make any representation or warranty regarding the suitability of the part described herein for any particular purpose, and L-com does not assume liability arising out of the use of any part or document. The information contained within this document is accurate to the best of our knowledge and representative of the part described herein. It may be necessary to make modifications to the part and/or the documentation of the part in order to implement improvements. L-com reserves the right to make such changes as required. Unless otherwise stated, all specifications are nominal. L-com does not make any representation or warranty regarding the suitability of the part described herein for any particular purpose, and L-com does not assume liability arising out of the use of any part or document.

Lead Free 1553 TRB 3-Lug Jack Bulkhead Non-Isolated to Blunt Cut Genderless Cable Assembly using 30-02001-LC Coax, 3 FT with Bend Relief

L-com CAD Drawing



| ZONE | REV | DESCRIPTION     | DATE      | CHANGED BY | APPROVED |
|------|-----|-----------------|-----------|------------|----------|
|      | A   | INITIAL RELEASE | 8/25/2023 | KDANG      | EKIM     |

LEAD FREE SOLDER

|                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                             |                                                                                                                                          |
|-------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|------------------------------------------------------------------------------------------------------------------------------------------|
| <p><b>L-com</b><br/>an INFINITE® brand<br/>Website: www.L-com.com<br/>Phone: 1.800.341.5266   1.978.682.6936</p>                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                            | <p>INTERPRET ALL DIMENSIONS AND TOLERANCES PER ASME Y14.5</p>                                                                            |
|                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                             | <p>SCALE: NONE<br/>SHEET: 1 OF 1</p>                                                                                                     |
| <p>UNLESS OTHERWISE SPECIFIED, LEADING DIMENSIONS ARE IN INCHES, DIMENSIONS IN [ ] ARE MILLIMETERS.</p> <p>TOLERANCES:<br/>                 .X = ±.2 [5]<br/>                 .XX = ±.02 [0.5]<br/>                 .XXX = ±.005 [0.13]<br/>                 ANGLES ± 1°<br/>                 FRACTIONS ± 1/32<br/>                 CABLE LENGTH TOLERANCES:<br/>                 ≤12 [305] = +1 [25] / -0<br/>                 &gt;12 [305] ≤ 60 [1524] = +2 [51] / -0<br/>                 &gt;60 [1524] ≤ 120 [3048] = +4 [102] / -0<br/>                 &gt;120 [3048] ≤ 300 [7620] = +6 [152] / -0<br/>                 &gt;300 [7620] = +5% / -0</p> | <p>DESCRIPTION<br/>                 Lead Free Bend Relief 3-Lug TRB Non-Insulated Bulkhead Jack with Blunt Cut for 30-02001-LC Cable</p> |
| <p>ALL DIMENSIONS ARE FOR REFERENCE ONLY AND SUBJECT TO CHANGE WITHOUT NOTICE UNLESS INDICATED OTHERWISE. DIMENSIONS MAY VARY. COLORS MAY VARY.</p>                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                         | <p>SIZE: A<br/>CAGE CODE: 43321<br/>DRAWN BY: KDANG<br/>ITEM NO.: LC3MSA00561</p>                                                        |

- NOTES:**
- CABLE ASSY LENGTH LABEL PLACEMENT: 36 INCHES OR LESS, ONE LABEL APPROX CENTERED. LONGER THAN 36 INCHES, TWO LABELS APPROX 6 INCHES FROM EACH CONNECTOR.
  - CABLE ASSEMBLY LENGTH DETERMINED BY ILLUSTRATED: LC3MSA00561-XX (-XX = OAL IN INCHES)
  - CABLES ASSEMBLIES SHALL BE TESTED FOR CONTINUITY.
- THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF INFINITE ELECTRONICS, INC. ANY REPRODUCTION IN ANY MANNER WITHOUT THE WRITTEN PERMISSION OF INFINITE ELECTRONICS, INC. IS PROHIBITED. THESE COMMODITIES, TECHNOLOGY OR SOFTWARE WERE EXPORTED FROM THE UNITED STATES IN ACCORDANCE WITH THE EXPORT ADMINISTRATION REGULATIONS. DIVERSION CONTRARY TO U.S. LAW PROHIBITED.

T-RW-D2