

Lead Free LSZH Bend Relief 3-Lug TRB Bulkhead Insulated Jack with Blunt Cut for 78 Ohm TWCH-78-2-LC, 36" Cable



## LC3MSA00592-36

### Configuration

- Connector 1: TRB 3-Lug Jack Bulkhead
- Connector 2: Blunt Cut Genderless
- Cable Type: TWCH-78-2-LC

### Features

- MIL-STD-1553
- -30°C to +80°C
- 78 ohms
- ROHS Low Smoke Zero Halogen
- Non-Toxic

### Applications

- Military Contractors
- MIL-STD-1553
- Data
- Safer Environments
- Ventilation critical areas
- Hospitals

### Description

L-com's LC3MSA00592-36 is a lead free LSZH bend relief 3-Lug TRB bulkhead insulated jack with blunt cut for 78 Ohm TWCH-78-2-LC, 36" cable and ships same-day. These flexible RF cable assemblies are ideal for applications where flexure is required. Our L-com TRB 3-Lug to Blunt Cut cable assembly has a jack to genderless gender configuration with 78 Ohm flexible TWCH-78-2-LC series coax and operates to 500 MHz. L-com's RF cable assembly with TRB 3-Lug bulkhead interface enables system designers to have external connections on their product enclosures or to be used for other rack mount and panel mount applications.

Custom versions of this TRB 3-Lug jack to TRB 3-Lug genderless cable, along with the rest of L-com's other RF assemblies, can also be built and shipped same day. Other available RF cable assembly value added services from L-com include connector orientation or clocking, heat shrink booting and custom labeling. RF testing can also be performed to document the electrical performance of your cable assembly. Contact a sales representative for testing or custom RF cable quotes. Part number LC3MSA00592-36 L-com Lead Free LSZH Bend Relief 3-Lug TRB Bulkhead Insulated Jack with Blunt Cut for 78 Ohm TWCH-78-2-LC, 36" Cable data sheet PDF includes details of the RF product specifications, CAD drawing(s) and dimensions below.

### Electrical Specifications

| Description            | Minimum | Typical      | Maximum | Units        |
|------------------------|---------|--------------|---------|--------------|
| Frequency Range        | DC      |              | 500     | MHz          |
| Capacitance            |         | 21.2 [69.55] |         | pF/ft [pF/m] |
| Operating Voltage (AC) |         |              | 1,000   | Vrms         |

Insertion Loss (Typ.)

### Mechanical Specifications

#### Cable Assembly

|         |                    |
|---------|--------------------|
| Length* | 36 in [914.4 mm]   |
| Weight  | 0.17 lbs [77.11 g] |

#### Cable

|            |              |
|------------|--------------|
| Cable Type | TWCH-78-2-LC |
|------------|--------------|

Lead Free LSZH Bend Relief 3-Lug TRB Bulkhead Insulated Jack with Blunt Cut for 78 Ohm TWCH-78-2-LC, 36" Cable



## LC3MSA00592-36

|                                      |                      |
|--------------------------------------|----------------------|
| Impedance                            | 78 Ohms              |
| Inner Conductor Type                 | Stranded             |
| Inner Conductor Material and Plating | Copper, Silver       |
| Dielectric Type                      | PE                   |
| Shield Layer 1                       | Silver Plated Copper |
| Jacket Material                      | HF POF, Blue         |
| One Time Minimum Bend Radius         | 1.25 in [31.75 mm]   |

### Connectors

| Description                           | Connector 1                  | Connector 2          |
|---------------------------------------|------------------------------|----------------------|
| Type                                  | TRB 3-Lug Jack Bulkhead      | Blunt Cut Genderless |
| Impedance                             | 78 Ohms                      |                      |
| Contact Material and Plating          | Bronze, Gold 30 micro inches |                      |
| Contact Plating Specification         | ASTM-B-488                   |                      |
| Dielectric Type                       | Teflon                       |                      |
| Outer Conductor Material and Plating  | Phosphor Bronze, Gold        |                      |
| Outer Conductor Plating Specification | 30 micro inches              |                      |
| Body Material and Plating             | Brass, Nickel                |                      |
| Body Plating Specification            | ASTM-B-733                   |                      |

### Environmental Specifications

#### Temperature

Operating Range -30 to +80 deg C

**Compliance Certifications** (see [product page](#) for current document)

### Plotted and Other Data

Notes:

Lead Free LSZH Bend Relief 3-Lug TRB Bulkhead Insulated Jack with Blunt Cut for 78 Ohm TWCH-78-2-LC, 36" Cable



## LC3MSA00592-36

### How to Order

Part Number Configuration:

**LC3MSA00592**

- **xx**

**uu**

Unit of Measure:  
cm = Centimeters  
<blank> = Inches  
Length  
Base Number


Example: LC3MSA00592-12 = 12 inches long cable  
LC3MSA00592-100cm = 100 cm long cable

Lead Free LSZH Bend Relief 3-Lug TRB Bulkhead Insulated Jack with Blunt Cut for 78 Ohm TWCH-78-2-LC, 36" Cable from L-com has same day shipment for domestic and International orders. L-com is a leading manufacturer of wired and wireless connectivity products and committed to in-stock availability and same day shipping. Our portfolio includes coaxial cable assemblies, connectors, adapters and custom products as well as lightning and surge protectors, NEMA rated enclosures, and an RF product line which includes antennas, amplifiers, passive, and active components.

The information contained within this document is accurate to the best of our knowledge and representative of the part described herein. It may be necessary to make modifications to the part and/or the documentation of the part in order to implement improvements. L-com reserves the right to make such changes as required. Unless otherwise stated, all specifications are nominal. L-com does not make any representation or warranty regarding the suitability of the part described herein for any particular purpose, and L-com does not assume liability arising out of the use of any part or document contained within this document is accurate to the best of our knowledge and representative of the part described herein. It may be necessary to make modifications to the part and/or the documentation of the part in order to implement improvements. L-com reserves the right to make such changes as required. Unless otherwise stated, all specifications are nominal. L-com does not make any representation or warranty regarding the suitability of the part described herein for any particular purpose, and L-com does not assume liability arising out of the use of any part or document.

Lead Free LSZH Bend Relief 3-Lug TRB Bulkhead Insulated Jack with Blunt Cut for 78 Ohm TWCH-78-2-LC, 36" Cable

L-com CAD Drawing



|  |  |        |
|--|--|--------|
| UNLESS OTHERWISE SPECIFIED, LEADING DIMENSIONS ARE IN INCHES UNLESS INDICATED OTHERWISE IN MILLIMETERS | <br>INTERPRET ALL DIMENSIONS AND TOLERANCES PER ASME Y14.5 |        |
| TOLERANCES:  | SCALE  | SHEET  |
| .X = ±.2 [5]   | NONE   | 1 OF 1 |
| .XX = ±.02 [0.5]   |  |        |
| .XXX = ±.005 [0.13]  |  |        |
| FRACTIONS ± 1/32   |  |        |
| ANGLES ± 1°  |  |        |
| CABLE LENGTH TOLERANCES:   |  |        |
| <math>\le 12 [305]</math> = +1 [25] / -0   |  |        |
| > 12 [305] <math>\le 60 [1524]</math> = +2 [51] / -0   |  |        |
| > 60 [1524] <math>\le 120 [3048]</math> = +4 [102] / -0  |  |        |
| > 120 [3048] <math>\le 300 [7620]</math> = +6 [152] / -0   |  |        |
| > 300 [7620] = +5% / -0  |  |        |
| ALL DIMENSIONS ARE FOR REFERENCE ONLY AND SUBJECT TO CHANGE WITHOUT NOTICE UNLESS OTHERWISE INDICATED  |  |        |
| MAX VARIATIONS MAY VARY  |  |        |
| DESCRIPTION  | ITEM NO.   | REV    |
| LEAD FREE LSZH BEND RELIEF 3-LUG TRB BULKHEAD INSULATED JACK WITH BLUNT CUT FOR 78 OHM TWCH-78-2 CABLE | LC3MSA00592  | A      |
| SIZE   | DRAWN BY   |        |
| A  | DMAY   |        |
| CAGE CODE  | ITEM NO.   |        |
| 43321  | LC3MSA00592  |        |

LEAD FREE SOLDER

RECOMMENDED PANEL CUTOUT

WIRING MAP

NOTES:

- CABLE ASSEMBLY LENGTH LABEL PLACEMENT: 36 INCHES OR LESS, ONE LABEL APPROXIMATELY CENTERED. LONGER THAN 36 INCHES, TWO LABELS APPROXIMATELY 6 INCHES FROM EACH CONNECTOR.
- CABLE ASSEMBLIES SHALL BE TESTED FOR CONTINUITY.
- CABLE ASSEMBLY LENGTH DETERMINED BY PN AS ILLUSTRATED: LC3MSA00592-XX (-XX = OAL IN INCHES)

THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF INFINITE ELECTRONICS, INC. ANY REPRODUCTION IN WHOLE OR IN PART WITHOUT THE WRITTEN PERMISSION OF INFINITE ELECTRONICS, INC. IS PROHIBITED. THESE COMMODITIES, TECHNOLOGY OR SOFTWARE WERE EXPORTED FROM THE UNITED STATES IN ACCORDANCE WITH THE EXPORT ADMINISTRATION REGULATIONS. DIVERSION CONTRARY TO U.S. LAW PROHIBITED.