

LSZH 1553 TRB 2-Slot Plug to TRB 2-Slot Plug Cable Assembly using TWCH-78-2-LC Coax, 5 FT



**LC3MSA00603-60**

**Configuration**

- Connector 1: TRB 2-Slot Plug
- Connector 2: TRB 2-Slot Plug
- Cable Type: TWCH-78-2-LC

**Features**

- MIL-STD-1553
- -30°C to +80°C
- 78 ohms
- Low Smoke Zero Halogen
- Non-Toxic

**Applications**

- Military Contractors
- MIL-STD-1553
- Data
- Safer Environments
- Ventilation critical areas
- Hospitals

**Description**

L-com's LC3MSA00603-60 is a LSZH 1553 TRB 2-Slot plug to TRB 2-Slot plug cable assembly using TWCH-78-2-LC coax, 5 FT and ships same-day. These flexible RF cable assemblies are ideal for applications where flexure is required. Our L-com TRB 2-Slot to TRB 2-Slot cable assembly has a plug to plug gender configuration with 78 Ohm flexible TWCH-78-2-LC series coax and operates to 500 MHz. The LC3MSA00603 cable assembly consists of a 78 Ohm Low Smoke Zero Halogen TRB 2-Slot Solder/Clamp Plug to Plug for TWCH-78-2 cable (.242 O.D.) suitable for MIL-STD-1553 Applications. The zero halogen jacket cable reduces the amount of toxic and corrosive gases emitted during combustion. Typically used in poorly ventilated areas, zero halogen is very popular with military contractors and anywhere the protection of people and equipment from toxic and corrosive gases is critical.

Custom versions of this TRB 2-Slot plug to TRB 2-Slot plug cable, along with the rest of L-com's other RF assemblies, can also be built and shipped same day. Other available RF cable assembly value added services from L-com include connector orientation or clocking, heat shrink booting and custom labeling. RF testing can also be performed to document the electrical performance of your cable assembly. Contact a sales representative for testing or custom RF cable quotes. Part number LC3MSA00603-60 L-com LSZH 1553 TRB 2-Slot Plug to TRB 2-Slot Plug Cable Assembly using TWCH-78-2-LC Coax, 5 FT data sheet PDF includes details of the RF product specifications, CAD drawing(s) and dimensions below.

**Electrical Specifications**

Description	Minimum	Typical	Maximum	Units
Frequency Range	DC		500	MHz
Capacitance		21.2 [69.55]		pF/ft [pF/m]
Operating Voltage (AC)			1,000	Vrms

**Specifications by Frequency**

Description	F1	F2	F3	F4	F5	Units
Frequency	10	50	100	200	500	MHz
Insertion Loss (Typ.)	0.31	0.455	0.575	0.725	1	dB

Electrical Specification Notes:

LSZH 1553 TRB 2-Slot Plug to TRB 2-Slot Plug Cable  
Assembly using TWCH-78-2-LC Coax, 5 FT



## LC3MSA00603-60

The Insertion Loss data above is based on the performance specifications of the coax and connectors used in this assembly. The Insertion Loss includes an estimated insertion loss of 0.1 dB per connector.

### Mechanical Specifications

#### Cable Assembly

Length*	60 in [152.4 cm]
Weight	0.44 lbs [199.58 g]

#### Cable

Cable Type	TWCH-78-2-LC
Impedance	78 Ohms
Inner Conductor Type	Stranded
Inner Conductor Material and Plating	Copper, Silver
Dielectric Type	PE
Shield Layer 1	Silver Plated Copper
Jacket Material	HF POF, Blue

One Time Minimum Bend Radius	1.25 in [31.75 mm]
------------------------------	--------------------

### Connectors

Description	Connector 1	Connector 2
Type	TRB 2-Slot Plug	TRB 2-Slot Plug
Impedance	78 Ohms	78 Ohms
Contact Material and Plating	Bronze, Gold 30 micro inches	Bronze, Gold 30 micro inches
Contact Plating Specification	ASTM-B-488	ASTM-B-488
Dielectric Type	Teflon	Teflon
Outer Conductor Material and Plating	Phosphor Bronze, Gold	Phosphor Bronze, Gold
Outer Conductor Plating Specification	30 micro inches	30 micro inches
Body Material and Plating	Brass, Nickel	Brass, Nickel
Body Plating Specification	ASTM-B-733	ASTM-B-733

### Environmental Specifications

#### Temperature

Operating Range	-30 to +80 deg C
-----------------	------------------

LSZH 1553 TRB 2-Slot Plug to TRB 2-Slot Plug Cable Assembly using TWCH-78-2-LC Coax, 5 FT



**LC3MSA00603-60**

**Compliance Certifications** (see [product page](#) for current document)


**Plotted and Other Data**

Notes:

**How to Order**

Part Number Configuration:

**LC3MSA00603 - xx uu**




Example: LC3MSA00603-12 = 12 inches long cable  
LC3MSA00603-100cm = 100 cm long cable

LSZH 1553 TRB 2-Slot Plug to TRB 2-Slot Plug Cable Assembly using TWCH-78-2-LC Coax, 5 FT from L-com has same day shipment for domestic and International orders. L-com is a leading manufacturer of wired and wireless connectivity products and committed to in-stock availability and same day shipping. Our portfolio includes coaxial cable assemblies, connectors, adapters and custom products as well as lightning and surge protectors, NEMA rated enclosures, and an RF product line which includes antennas, amplifiers, passive, and active components.

The information contained within this document is accurate to the best of our knowledge and representative of the part described herein. It may be necessary to make modifications to the part and/or the documentation of the part in order to implement improvements. L-com reserves the right to make such changes as required. Unless otherwise stated, all specifications are nominal. L-com does not make any representation or warranty regarding the suitability of the part described herein for any particular purpose, and L-com does not assume liability arising out of the use of any part or document. The information contained within this document is accurate to the best of our knowledge and representative of the part described herein. It may be necessary to make modifications to the part and/or the documentation of the part in order to implement improvements. L-com reserves the right to make such changes as required. Unless otherwise stated, all specifications are nominal. L-com does not make any representation or warranty regarding the suitability of the part described herein for any particular purpose, and L-com does not assume liability arising out of the use of any part or document.

LSZH 1553 TRB 2-Slot Plug to TRB 2-Slot Plug Cable Assembly using TWCH-78-2-LC Coax, 5 FT

L-com CAD Drawing




78 OHM TWINAX CABLE  
 NOM. DIA.: .242" [6.15]  
 OPER. TEMP.: -30°C TO +80°C

WWW.L-COM.COM  
 LCXXXXXX

LABEL  
 SEE NOTE 1

2X TRB 2-SLOT  
 SOLDER PLUG TYPE



NOTES:

1. CABLE ASSEMBLY LENGTH LABEL PLACEMENT: 36 INCHES OR LESS, ONE LABEL APPROXIMATELY CENTERED. LONGER THAN 36 INCHES, TWO LABELS APPROXIMATELY 6 INCHES FROM EACH CONNECTOR.
2. CABLE ASSEMBLIES SHALL BE TESTED FOR CONTINUITY.
3. CABLE ASSEMBLY LENGTH DETERMINED BY PN AS ILLUSTRATED: LC3MSA00603-XX (XX = OAL IN METERS).

THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF INFINITE ELECTRONICS, INC. ANY REPRODUCTION IN PART OR WHOLE WITHOUT THE WRITTEN PERMISSION OF INFINITE ELECTRONICS, INC. IS PROHIBITED. THESE COMMODITIES, TECHNOLOGY OR SOFTWARE WERE EXPORTED FROM THE UNITED STATES IN ACCORDANCE WITH THE EXPORT ADMINISTRATION REGULATIONS. DIVERSION CONTRARY TO U.S. LAW PROHIBITED.

UNLESS OTHERWISE SPECIFIED, ALL DIMENSIONS ARE IN INCHES. DIMENSIONS IN PARENS ARE IN MILLIMETERS.		L-com <sup>®</sup> an INFINITE brand		INTERPRET ALL DIMENSIONS AND TOLERANCES PER ASME Y14.5	
TOLERANCES:		Website: www.L-com.com		SCALE: NONE	
.X = ±.2 [5]		Phone: 1.800.341.5266   1.978.682.6936		SHEET: 1 OF 1	
.XX = ±.02 [0.5]		DESCRIPTION: LSZH 78 OHM TRB 2-SLOT SOLDER/CLAMP PLUG TO PLUG FOR TWCH-78-2 TWINAX MIL-STD-1553 CABLE -30C +80C		REV: A	
.XXX = ±.005 [0.13]		ITEM NO: LC3MSA00603-XX		REV: A	
ANGLES ±.1°		DRAWN BY: LNAGARAJ		REV: A	
CABLE LENGTH TOLERANCES:		CAGE CODE: 43321		REV: A	
≤12 [305] ≤60 [1524] = +2 [51] / -0		ITEM NO: LC3MSA00603-XX		REV: A	
>12 [305] ≤60 [1524] = +2 [51] / -0		CAGE CODE: 43321		REV: A	
>60 [1524] ≤120 [3048] = +4 [102] / -0		DRAWN BY: LNAGARAJ		REV: A	
>120 [3048] ≤300 [7620] = +5/8 [1.6]		CAGE CODE: 43321		REV: A	
>300 [7620] = +5/8 [1.6]		DRAWN BY: LNAGARAJ		REV: A	
ALL DIMENSIONS ARE FOR REFERENCE ONLY AND SUBJECT TO CHANGE WITHOUT NOTICE UNLESS OTHERWISE SPECIFIED.		CAGE CODE: 43321		REV: A	
MAY VARY IN SIZE AND LOCATION		DRAWN BY: LNAGARAJ		REV: A	
COLORS MAY VARY		CAGE CODE: 43321		REV: A	