

406 MHz - 512 MHz 2 Folded Dipole antenna, 7 dBi gain, 1/2 Wave Bidirectional pattern, V-pol, Type N Female Connector



## LCANED1010

### Features

- Frequency coverage for 406 MHz to 512 MHz with Type N Female connector
- Very High Gain 7 dBi / 4.85 dBd antennas
- Easy and quick time to installations
- Industrially tuned dipoles made of high-grade aluminum alloys
- 2-Folded dipole antenna has bidirectional pattern with ½ wave spacing
- 35° vertical beamwidth with Vertical Polarization
- 100 W max input power

### Applications

- Outdoor point-to-point (PtP) or point-to-multipoint (PtMP) applications
- UHF radio applications supported with Trunking for two-way radio communications
- Wireless LAN systems, IOT and IIOT low data high coverage applications
- TV Broadcasts and FM radio applications
- Air traffic controllers / Public Safety / Emergency services / Marine communications
- Tetra and P-25 Applications exclusively supported
- Land Mobile Radio (LMR) and Private Mobile Radio (PMR)

### Description

The L-com LCANED1010 is a high performance, two element exposed folded dipole antenna designed to operate from 406 to 512 MHz for UHF frequency band communication systems. The LCANED1010 has 7 dBi / 4.85 dBd of high gain and can be used for long distance communications over a wide range of applications. The LCANED1010 is ideal for boosting radar, GPR/WPR, FM Radio, TV broadcasts, public safety, LMR / PMR and aviation.

The folded exposed dipole LCANED1010 has 35 vertical beamwidth. This antenna has Vertical polarization, and the included mounting kit allows for very easy and quick time installations with less effort. These exposed dipoles are already tuned to be Half wavelength away from the mast and do not require any further field adjustments. The LCANED1010 exposed dipole antennas are robust, outdoor, weatherproof, and high velocity wind sustainable antennas made up of high-grade aluminum alloys for longevity and resistant to corrosion. These dipole antennas are side mounted ½ wave spacing from the mast, has a pigtail terminated with 1 Type N female connector. This premium quality 2-bay dipole antenna has bidirectional pattern with 100W maximum power handling capability.

L-com's 406 to 512 MHz two element half wave exposed folded dipole LCANED1010 antennas with 7 dBi/ 4.85 dBd max gain for UHF communication applications. The central support mast is precisely designed for easy dipole attachments which fit tightly for error free and quick installations and ease for transportation. This half wave folded exposed dipole antenna with N Female Type connector is in stock and ready to ship the same day. Contact our knowledgeable and friendly technical support and sales staff for your answers on antennas or other L-com products.

### Configuration

Band Type	Single
Radiation Pattern	Directional
Polarization	Vertical
Connector Type	N Female
Number of Ports	1

Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications:  
406 MHz - 512 MHz 2 Folded Dipole antenna, 7 dBi gain, 1/2 Wave Bidirectional pattern, V-pol, Type N Female Connector [LCANED1010](#)

406 MHz - 512 MHz 2 Folded Dipole antenna, 7 dBi gain, 1/2 Wave Bidirectional pattern, V-pol, Type N Female Connector



## LCANED1010

### Electrical Specifications

Description	Minimum	Typical	Maximum	Units
Frequency Range	406		512	MHz
Input VSWR			1.8:1	
Gain		7		dBi
Vertical (Elevation) HPBW		35		Degrees
Input Power			100	Watts

### Mechanical Specifications

Radome Material	Aluminum Alloy
<b>Size</b>	
Length	63 in [160.02 cm]
Width	18.9 in [480.06 mm]
Height	2.4 in [60.96 mm]
Mounting Mast Diameter	1.5748 to 1.9685 in [40.00 to 50.00 mm]
Weight	23.1 lbs [10.48 kg]

### Environmental Specifications

Wind Survivability	124.274 MPH [200 KPH]
Humidity	5 to 95

**Compliance Certifications** (see [product page](#) for current document)

### Plotted and Other Data

Notes:

406 MHz - 512 MHz 2 Folded Dipole antenna, 7 dBi gain, 1/2 Wave Bidirectional pattern, V-pol, Type N Female Connector from L-com has same day shipment for domestic and International orders. Our portfolio includes coaxial cable assemblies, connectors, adapters and custom products as well as lightning and surge protectors, NEMA rated enclosures, and an RF product line which includes antennas, amplifiers, passive, and active components.

The information contained within this document is accurate to the best of our knowledge and representative of the part described herein. It may be necessary to make modifications to the part and/or the documentation of the part in order to implement improvements. L-com reserves the right to make such changes as required. Unless otherwise stated, all specifications are nominal. L-com does not make any representation or warranty regarding the suitability of the part described herein for any particular purpose, and L-com does not assume liability arising out of the use of any part or document.

406 MHz - 512 MHz 2 Folded Dipole antenna, 7 dBi gain, 1/2 Wave Bidirectional pattern, V-pol, Type N Female Connector

L-com CAD Drawing

