

4 Cellular, 1 GPS Combination Antenna
4 N Type, 1 SMA Connector Black



LCANOM1112

Features

- 4 x Cellular 4G/5G N Male
- 1 x GPS L1 / G1 SMA Male
- MIMO Capable
- 17 ft Cable Leads
- Indoor/Outdoor IP69K Rated
- UV Stabilized Black ABS

Applications

- Public Safety
- Emergency Services
- Mobile Base Stations
- Autonomous Vehicles
- Fleet Management
- Smart Cities
- Smart Utilities
- Industrial IoT

Description

The L-com LCANOM1112 is a 5-in-1 combination antenna designed for public safety, emergency services, mobile base stations, autonomous vehicles, fleet management, smart cities, smart utilities, or industrial IoT applications. This vertically polarized omnidirectional antenna has SMA male and N male connectors with 17 feet cable leads. Our high-quality mobile antenna with 5 ports has a typical input VSWR of 2:1.

The IoT combination antenna from L-com has an overall length of 7 inches, width of 7 inches, and weight of 4 lbs. This LCANOM1112 mobile antenna is IP69K-rated and has a black-colored radome made of UV-stabilized ABS. The 4 cellular, 1 GPS combination antenna has an impedance of 50 Ohms and a maximum input power of 10 Watts.

Our vertically polarized mobile antenna can operate at temperatures ranging from -40 to 70 degrees C. This MIMO-capable IoT antenna features four 4G/5G, and one L1/G1 GPS band elements in one radome. Emergency services, first responders, and fleets can rely on our 5-in-1 combination antenna to maintain a secure link between vehicles and dispatch centers.

Configuration

| | |
|-------------------|------------------|
| Design | Mobile |
| Radiation Pattern | Omni Directional |
| Polarization | Vertical |
| Connector Type | N Male |
| Interface 2 | SMA Male |
| Number of Ports | 5 |

Electrical Specifications

| Description | Minimum | Typical | Maximum | Units |
|--------------------------------|-----------|-------------|-------------|-----------------|
| Input VSWR | | 2:1 | | |
| Impedance | | 50 | | Ohms |
| Input Power | | | 10 | Watts |
| Cellular Specifications | | | | |
| Frequency Range | 617 - 960 | 1690 - 2700 | 3300 - 4200 | 4900 - 6000 MHz |
| Peak Gain | 4 | 6 | 7 | 8 dBi |
| Port Count | | 4 | | |
| Cable Type | | RG58 | | |
| Cable Length | | 17 [5] | | ft [m] |
| Connector Type | | N Male | | |

4 Cellular, 1 GPS Combination Antenna
4 N Type, 1 SMA Connector Black



LCANOM1112

| GPS Specifications | | |
|--------------------------------|--------------------------|-----|
| Frequency Range | 1562 - 1612 | MHz |
| VSWR | <2.0:1 ± 4 MHz | |
| LNA Gain | 26 | dB |
| Out of band rejection | >40 dB (@ > +/- 100 MHz) | |
| Typical Noise Figure | ≤ 2.7 | dB |
| Notch Filter rejection @787MHz | 24 | dB |
| Operating Voltage | 3 - 5 | VDC |
| Typical Current | 15 | mA |
| Cable Type / Length | RG174 / 17 ft [5 m] | |
| Connector Type | SMA Male | |

Mechanical Specifications

| | |
|-----------------|--------------------|
| Radome Material | UV Stabilized ABS |
| Size | |
| Length | 7 in [177.8 mm] |
| Width | 7 in [177.8 mm] |
| Height | 3.15 in [80.01 mm] |
| Weight | 4 lbs [1.81 kg] |

Environmental Specifications

| | |
|--------------------|------------------|
| Temperature | |
| Operating Range | -40 to +70 deg C |
| Ingress Protection | IP69K |

Compliance Certifications (see [product page](#) for current document)

Plotted and Other Data

Notes:

4 Cellular, 1 GPS Combination Antenna
4 N Type, 1 SMA Connector Black



LCANOM1112

Typical Radiation Pattern

Appendix

Electrical Downtilt: Angle in the antenna's elevation pattern in which the maximum gain occurs.

Gain: Antenna's average gain.

Front to Back Ratio @ 180°±30°: Average difference between the antenna's maximum gain and the maximum gain in the antenna's back lobe over ±30° angles.

Cross-polarization Ratio (dB): Typical difference between the co-polarization and cross-polarization gain across the sector's 3 dB Beam Width.

Dedicated to serving the needs of the Wireless Internet Service Provider (WISP) market, KP Performance Antennas offers purpose built products that reliably perform in the field. KP Performance Antennas product line consists of Yagi, Grid, Omni, Dish and other style antennas that operate in the 900 MHz, 2.4 GHz, 3 GHz, and 5 GHz frequencies.

4 Cellular, 1 GPS Combination Antenna 4 N Type, 1 SMA Connector Black from L-com has same day shipment for domestic and International orders. Our portfolio includes coaxial cable assemblies, connectors, adapters and custom products as well as lightning and surge protectors, NEMA rated enclosures, and an RF product line which includes antennas, amplifiers, passive, and active components.

URL: <https://www.l-com.com/iot-mobile-antenna-omnidirectional-n-connectors-black-lcanom1112-p.aspx>

The information contained within this document is accurate to the best of our knowledge and representative of the part described herein. It may be necessary to make modifications to the part and/or the documentation of the part in order to implement improvements. L-com reserves the right to make such changes as required. Unless otherwise stated, all specifications are nominal. L-com does not make any representation or warranty regarding the suitability of the part described herein for any particular purpose, and L-com does not assume liability arising out of the use of any part or document.

LCANOM1112 CAD Drawing

4 Cellular, 1 GPS Combination Antenna 4 N Type, 1 SMA Connector Black

