

2.15 dBi, UHF Rubber Duck Antenna, 412-520 MHz,
MOTO Connector, Vertical Polarization



LCANRBD1009

Features

- 412 MHz to 520 MHz, 2.15 dBi Gain
- MOTO connector
- Heliflex whip antenna
- Plug and play
- 20W power handling
- VSWR < 3:1
- Vertical polarization

Applications

- PtP or PtMP applications
- Trunking for two-way radio comms
- UHF applications
- Public Safety / Emergency services
- Tetra and P-25 applications exclusively supported
- Land and Private mobile radio (LMR) (PMR)
- Fixed and mobile services

Description

The LCANRBD1009 rubber duck antenna from L-Com is part of our extensive line of directional antennas that we offer with global same-day shipping from our facilities certified to ISO 9001:2015. L-Com's high-quality single-band rubber duck antenna has a 2.15 dBi nominal gain and can be procured with no order limit. This rubber duck single-band 2.15 dBi antenna has a frequency range of 412 MHz to 520 MHz.

We lead the industry in supplying products like this 412 MHz to 520 MHz single-band antenna, along with other RF, microwave, and millimeter wave components. This rubber duck antenna from L-Com uses a MOTO connector and has a maximum input power of 20 watts. Use our single-band rubber duck antenna with vertical polarization for fixed and mobile services, public safety or emergency services, trunking for two-way radio communications, land and private mobile radio (LMR) (PMR), PtP or PtMP, tetra, and P-25 applications.

L-Com's rubber duck antenna with 2.15 dBi gain has a MOTO-type connector. This MOTO-series connectorized omnidirectional antenna is 0.5 inches tall, 0.5 inches wide, and 6.69 inches long. The LCANRBD1009 UHF antenna has 360-degrees of horizontal and 80-degrees of vertical HPBW. Our high-quality antenna has a maximum input VSWR (voltage standing wave ratio) of 3:1.

L-Com's 50 Ohms impedance antenna can operate at temperatures ranging from -40 °C to 60 °C. This single-band rubber duck antenna is offered with expert technical support, PDF datasheets, and CAD drawings with dimensions and specifications. Order your 2.15 dBi UHF rubber duck antennas now and enjoy our international or domestic same-day shipping.

Configuration

Design	Rubber Duck
Band Type	Single
Radiation Pattern	Omni Directional
Polarization	Vertical
Connector Type	MOTO

Electrical Specifications

Description	Minimum	Typical	Maximum	Units
Frequency Range	412		520	MHz

Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications:
[2.15 dBi, UHF Rubber Duck Antenna, 412-520 MHz, MOTO Connector, Vertical Polarization LCANRBD1009](#)

2.15 dBi, UHF Rubber Duck Antenna, 412-520 MHz,
MOTO Connector, Vertical Polarization



LCANRBD1009


Input VSWR		3:1	
Impedance	50		Ohms
Gain	2.15		dBi
Horizontal (Azimuth) HPBW	Omnidirectional		
Vertical (Elevation) HPBW	80		Degrees
Input Power		20	Watts

2.15 dBi, UHF Rubber Duck Antenna, 412-520 MHz,
MOTO Connector, Vertical Polarization

LCANRBD1009



VSWR plot:



Mechanical Specifications

Size

Length	6.49606 in [165 mm]
Width	0.5 in [12.7 mm]
Height	0.5 in [12.7 mm]
Weight	0.048 lbs [21.77 g]

2.15 dBi, UHF Rubber Duck Antenna, 412-520 MHz,
MOTO Connector, Vertical Polarization

LCANRBD1009



Environmental Specifications

Temperature

Operating Range -40 to +60 deg C

Compliance Certifications (see [product page](#) for current document)

Plotted and Other Data

Notes:

2.15 dBi, UHF Rubber Duck Antenna, 412-520 MHz, MOTO Connector, Vertical Polarization from L-com has same day shipment for domestic and International orders. Our portfolio includes coaxial cable assemblies, connectors, adapters and custom products as well as lightning and surge protectors, NEMA rated enclosures, and an RF product line which includes antennas, amplifiers, passive, and active components.

The information contained within this document is accurate to the best of our knowledge and representative of the part described herein. It may be necessary to make modifications to the part and/or the documentation of the part in order to impliment improvements. L-com reserves the right to make such changes as required. Unless otherwise stated, all specifications are nominal. L-com does not make any representation or warranty regarding the suitability of the part described herein for any particular purpose, and L-com does not assume liability arising out of the use of any part or document.

2.15 dBi, UHF Rubber Duck Antenna, 412-520 MHz, MOTO Connector, Vertical Polarization

L-com CAD Drawing

