

27 MHz Omni Antenna 4 dBi Gain, Spring UHF  
Male Connector, Stainless Steel

## LCANOM1066



### Features

- Vertically Polarized
- 4 dBi Gain
- UHF Male Connector
- Stainless Steel
- 1.5:1 VSWR Max
- 50 Watt Max Input Power

### Applications

- Offroad/Overland Vehicles
- Mining/Industrial Heavy Equipment
- Commercial Trucking
- Fleet Management
- Farm Equipment

### Description

The L-com LCANOM1066 is a single band antenna that ships on the same day as ordered. Our vertical polarized antenna with 26 to 28 MHz frequency range has a UHF male connectors. This antenna made of stainless steel has an overall length of 57.09 in, a width of 2 in, and a weight of 1 lbs.

L-com's LCANOM1066 is a single band antenna operating from 26 to 28 MHz with 4 dBi gain. The omni directional antenna has a maximum input VSWR of 1.5:1.

L-com has one of the largest in-stock collections of omni directional antennas with our wide selection of superior quality RF parts, that ship same day. Make your online purchase right now to take advantage of our same-day shipping. For further information on similar products, our expert technical support and knowledgeable sales team can help you get the ideal single band antenna as per your requirement.

### Configuration

Band Type	Single
Radiation Pattern	Omni Directional
Polarization	Vertical
Connector Type	UHF Male

### Electrical Specifications

Description	Minimum	Typical	Maximum	Units
Frequency Range	26		28	MHz
Input VSWR			1.5:1	
Impedance		50		Ohms
Gain		4		dBi
Input Power			50	Watts

### Mechanical Specifications

Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications:  
[27 MHz Omni Antenna 4 dBi Gain, Spring UHF Male Connector, Stainless Steel LCANOM1066](#)

27 MHz Omni Antenna 4 dBi Gain, Spring UHF  
Male Connector, Stainless Steel

**LCANOM1066**



Radome Material	Stainless Steel
<b>Size</b>	
Length	57.09 in [145.01 cm]
Width	2 in [50.8 mm]
Height	2 in [50.8 mm]
Weight	1 lbs [453.59 g]

**Environmental Specifications**

<b>Temperature</b>	
Operating Range	-40 to +80 deg C

**Compliance Certifications** (see [product page](#) for current document)

**Plotted and Other Data**


Notes:

27 MHz Omni Antenna 4 dBi Gain, Spring UHF Male Connector, Stainless Steel from L-com has same day shipment for domestic and International orders. Our portfolio includes coaxial cable assemblies, connectors, adapters and custom products as well as lightning and surge protectors, NEMA rated enclosures, and an RF product line which includes antennas, amplifiers, passive, and active components.

The information contained within this document is accurate to the best of our knowledge and representative of the part described herein. It may be necessary to make modifications to the part and/or the documentation of the part in order to impliment improvements. L-com reserves the right to make such changes as required. Unless otherwise stated, all specifications are nominal. L-com does not make any representation or warranty regarding the suitability of the part described herein for any particular purpose, and L-com does not assume liability arising out of the use of any part or document.

# 27 MHz Omni Antenna 4 dBi Gain, Spring UHF Male Connector, Stainless Steel

## L-com CAD Drawing



REVISION			
ZONE	REV.	DESCRIPTION	DATE
	A	INITIAL RELEASE	2/21/2023
		CHANGED BY	HBAKKE
		APPROVED BY	KHIETPAS

**L-com**  
an INFINITE brand  
Website: [www.L-com.com](http://www.L-com.com)  
Phone: 1.800.341.5266 | 1.978.682.6936

INTERPRET ALL DIMENSIONS AND TOLERANCES PER ASME Y14.5  
SCALE NONE  
SHEET 1 OF 1

UNLESS OTHERWISE SPECIFIED, LEADING DIMENSIONS ARE INCHES, DIMENSIONS IN [ ] ARE MILLIMETERS.  
TOLERANCES:  
X = ±.2 [5] FRACTIONS  
XX = ±.02 [5] ±.132  
XXX = ±.005 [13] ANGLES ± 1°  
CABLE LENGTH TOLERANCES:  
> 12 [305] = ±.125 / -0  
> 60 [1524] = ±.25 / -0  
> 120 [3048] = ±.50 / -0  
> 300 [7620] = ±.125 / -0

DESCRIPTION  
27 MHZ OMNI ANTENNA 4 DBI, VEHICLE SPRING UHF, 57 IN.  
BLACK

SIZE A CAGE CODE 43321 DRAWN BY HBAKKE ITEM NO. LCOM1066

ALL DIMENSIONS ARE FOR REFERENCE ONLY AND SUBJECT TO CHANGE WITHOUT NOTICE

THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF INFINITE ELECTRONICS, INC. ANY REPRODUCTION IN PART OR WHOLE WITHOUT THE WRITTEN PERMISSION OF INFINITE ELECTRONICS, INC. IS PROHIBITED. THESE COMMODITIES, TECHNOLOGY OR SOFTWARE WERE EXPORTED FROM THE UNITED STATES IN ACCORDANCE WITH THE EXPORT ADMINISTRATION REGULATIONS. DIVERSION CONTRARY TO U.S. LAW PROHIBITED.

T-Rev: 01