

GLOBAL CONNECTIVITY SOLUTIONS

A I I

BNC Male to BNC Male Cable Assembly using RG178 Coax, 2 FT

LCCA30055-FT2

Configuration

- Connector 1: BNC Male
- Connector 2: BNC Male
- Cable Type: RG178

Features

- Max Frequency 1 GHz
- 70% VoP

Applications

· General Purpose

- FEP Jacket
- Heat Shrink Strain Relief
- · Laboratory Use



Description

L-com's LCCA30055-FT2 is a BNC male to BNC male cable assembly using RG178 coax, 2 FT and ships same-day. The RG178 coax of this BNC cable uses the PTFE dielectric with a VoP of 70%. These flexible RF cable assemblies are ideal for applications where flexure is required. Our L-com BNC to BNC cable assembly has a male to male gender configuration with flexible RG178 series coax and operates to 1 GHz. The shielding of this BNC cable is comprised of silver plated copper braid.

Custom versions of this BNC male to BNC male cable, along with the rest of L-com's other RF assemblies, can also be built and shipped same day. Other available RF cable assembly value added services from L-com include connector orientation or clocking, heat shrink booting and custom labeling. RF testing can also be performed to document the electrical performance of your cable assembly. Contact a sales representative for testing or custom RF cable quotes. Part number LCCA30055-FT2 L-com BNC Male to BNC Male Cable Assembly using RG178 Coax, 2 FT data sheet PDF includes details of the RF product specifications, CAD drawing(s) and dimensions below.



BNC Male to BNC Male Cable Assembly using RG178 Coax, 2 FT



LCCA30055-FT2

Electrical Specifications

Description	Minimum	Typical	Maximum	Units
Frequency Range	DC		1,000	MHz
VSWR			1.35:1	
Velocity of Propagation		70		%
Capacitance		29.4 [96.46]		pF/ft [pF/m]
Operating Voltage (AC)			500	Vrms

Specifications by Frequency

Description	F1	F2	F3	F4	F5	Units	
Frequency	50	100	250	500	1,000	MHz	
Insertion Loss (Max.)	0.43	0.48	0.62	0.82	1.09	dB	

Electrical Specification Notes:

The Insertion Loss data above is based on the performance specifications of the coax cable and connectors used in this assembly. The Insertion Loss is estimated as 0.1 dB per connector.

Mechanical Specifications

Cable Assembly Length Diameter	24 in [609.6 mm] 0.072 in [1.83 mm]
Cable Cable Type Impedance Inner Conductor Type Inner Conductor Material and Plating Dielectric Type Number of Shields Shield Layer 1 Jacket Material Jacket Diameter	RG178 50 Ohms Stranded Copper, Silver PTFE 1 Silver Plated Copper Braid FEP, Tan 0.072 in [1.83 mm]
Repeated Minimum Bend Radius	0.4 in [10.16 mm]

LCCA30055-FT2 REV 1.0 | © 2019 Infinite Electronics, Inc. L-com is a registered trademark of Infinite Electronics, Inc.



BNC Male to BNC Male Cable Assembly using RG178 Coax, 2 FT

LCCA30055-FT2

Connectors

Description	Connector 1	Connector 2
Туре	BNC Male	BNC Male
Specification	MIL-STD-348A	MIL-STD-348A
Impedance	50 Ohms	50 Ohms
Contact Material and Plating	Brass, Gold	Brass, Gold
Contact Plating Specification	30 µin minimum	30 µin minimum
Dielectric Type	PTFE	PTFE
Body Material and Plating	Brass, Nickel	Brass, Nickel
Body Plating Specification	100 µin minimum	100 µin minimum
Coupling Nut Material and Plating	Brass, Nickel	Brass, Nickel
Coupling Nut Plating Specification	100 µin minimum	100 µin minimum

Environmental Specifications

Temperature

Operating Range

-55 to +200 deg C

Compliance Certifications (see product page for current document)

Plotted and Other Data

Notes:

Values at 25°C, sea level.





Al a second

BNC Male to BNC Male Cable Assembly using RG178 Coax, 2 FT

LCCA30055-FT2

How to Order

Example:

Part Number Configuration: LCCA30055 - XX uu Unit of Measure: cm = Centimeters <blank> = Inches Length Base Number LCCA30055-12 = 12 inches long cable LCCA30055-100cm = 100 cm long cable


BNC Male to BNC Male Cable Assembly using RG178 Coax, 2 FT from L-com has same day shipment for domestic and International orders. L-com is a leading manufacturer of wired and wireless connectivity products and committed to in-stock availability and same day shipping. Our portfolio includes coaxial cable assemblies, connectors, adapters and custom products as well as lightning and surge protectors, NEMA rated enclosures, and an RF product line which includes antennas, amplifiers, passive, and active components.

The information contained within this document is accurate to the best of our knowledge and representative of the part described herein. It may be necessary to make modifications to the part and/or the documentation of the part in order to impliment improvements. L-com reserves the right to make such changes as required. Unless otherwise stated, all specifications are nominal. L-com does not make any representation or warranty regarding the suitability of the part described herein for any particular purpose, and L-com does not assume liability arising out of the use of any part or document.ontained within this document is accurate to the best of our knowledge and representative of the part described herein. It may be necessary to make modifications to the part and/or the documentation of the part in order to impliment improvements. L-com reserves the right to make such changes as required. Unless otherwise stated, all specifications are nominal. L-com does not make any representation or warranty regarding the suitability of the part described herein for any particular purpose, and L-com does not assume liability arising out of the use of any part or document.





L-com CAD Drawing



USA & Canada (800) 341-5266 | International (978) 682-6936 | I-com.com