

MMCX Plug to MMCX Plug Cable Assembly using RG178 Coax, 2 FT



**LCCA30065-FT2**

**Configuration**

- Connector 1: MMCX Plug
- Connector 2: MMCX Plug
- Cable Type: RG178

**Features**

- Max Frequency 3 GHz
- 70% VoP
- FEP Jacket
- Heat Shrink Strain Relief

**Applications**

- General Purpose
- Laboratory Use



**Description**

L-com's LCCA30065-FT2 is a MMCX plug to MMCX plug cable assembly using RG178 coax, 2 FT and ships same-day. The RG178 coax of this MMCX cable uses the PTFE dielectric with a VoP of 70%. These flexible RF cable assemblies are ideal for applications where flexure is required. Our L-com MMCX to MMCX cable assembly has a plug to plug gender configuration with flexible RG178 series coax and operates to 3 GHz. The shielding of this MMCX cable is comprised of silver plated copper braid.

Custom versions of this MMCX plug to MMCX plug cable, along with the rest of L-com's other RF assemblies, can also be built and shipped same day. Other available RF cable assembly value added services from L-com include connector orientation or clocking, heat shrink booting and custom labeling. RF testing can also be performed to document the electrical performance of your cable assembly. Contact a sales representative for testing or custom RF cable quotes. Part number LCCA30065-FT2 L-com MMCX Plug to MMCX Plug Cable Assembly using RG178 Coax, 2 FT data sheet PDF includes details of the RF product specifications, CAD drawing(s) and dimensions below.

MMCX Plug to MMCX Plug Cable Assembly using RG178 Coax, 2 FT



## LCCA30065-FT2

### Electrical Specifications

Description	Minimum	Typical	Maximum	Units
Frequency Range	DC		3	GHz
Velocity of Propagation		70		%
Capacitance		29.4 [96.46]		pF/ft [pF/m]

### Specifications by Frequency

Description	F1	F2	F3	F4	F5	Units
Frequency	0.1	0.25	0.5	1	3	GHz
Insertion Loss (Max.)	0.48	0.62	0.82	1.09	1.77	dB

#### Electrical Specification Notes:

The Insertion Loss data above is based on the performance specifications of the coax cable and connectors used in this assembly. The Insertion Loss is estimated as 0.1 dB per connector.

### Mechanical Specifications

#### Cable Assembly

Length 24 in [609.6 mm]  
Diameter 0.072 in [1.83 mm]

#### Cable

Cable Type RG178  
Impedance 50 Ohms  
Inner Conductor Type Stranded  
Inner Conductor Material and Plating Copper, Silver  
Dielectric Type PTFE  
Number of Shields 1  
Shield Layer 1 Silver Plated Copper Braid  
Jacket Material FEP, Tan  
Jacket Diameter 0.072 in [1.83 mm]

Repeated Minimum Bend Radius 0.4 in [10.16 mm]

MMCX Plug to MMCX Plug Cable Assembly using RG178 Coax, 2 FT



## LCCA30065-FT2

### Connectors

Description	Connector 1	Connector 2
Type	MMCX Plug	MMCX Plug
Impedance	50 Ohms	50 Ohms
Contact Material and Plating	Gold	Gold
Dielectric Type	PTFE	PTFE
Body Material and Plating	Brass, Gold	Brass, Gold

### Environmental Specifications

#### Temperature

Operating Range -55 to +200 deg C

**Compliance Certifications** (see [product page](#) for current document)

### Plotted and Other Data

Notes:

- Values at 25°C, sea level.

MMCX Plug to MMCX Plug Cable Assembly using RG178 Coax, 2 FT




## LCCA30065-FT2

### How to Order

Part Number Configuration:

**LCCA30065 - xx uu**



Example: LCCA30065-12 = 12 inches long cable  
LCCA30065-100cm = 100 cm long cable

MMCX Plug to MMCX Plug Cable Assembly using RG178 Coax, 2 FT from L-com has same day shipment for domestic and International orders. L-com is a leading manufacturer of wired and wireless connectivity products and committed to in-stock availability and same day shipping. Our portfolio includes coaxial cable assemblies, connectors, adapters and custom products as well as lightning and surge protectors, NEMA rated enclosures, and an RF product line which includes antennas, amplifiers, passive, and active components.

The information contained within this document is accurate to the best of our knowledge and representative of the part described herein. It may be necessary to make modifications to the part and/or the documentation of the part in order to implement improvements. L-com reserves the right to make such changes as required. Unless otherwise stated, all specifications are nominal. L-com does not make any representation or warranty regarding the suitability of the part described herein for any particular purpose, and L-com does not assume liability arising out of the use of any part or document contained within this document is accurate to the best of our knowledge and representative of the part described herein. It may be necessary to make modifications to the part and/or the documentation of the part in order to implement improvements. L-com reserves the right to make such changes as required. Unless otherwise stated, all specifications are nominal. L-com does not make any representation or warranty regarding the suitability of the part described herein for any particular purpose, and L-com does not assume liability arising out of the use of any part or document.

# MMCX Plug to MMCX Plug Cable Assembly using RG178 Coax, 2 FT

## L-com CAD Drawing

REVISIONS			
REV.	DESCRIPTION	DATE	APPROVED
A	INITIAL RELEASE	01/31/2020	SELLIS

LENGTH MEASURED FROM CONTACT TO CONTACT

2x HEAT SHRINK TUBE, BLACK

RG178 COAX CABLE

MMCX PLUG

MMCX PLUG

WWW.L-COM.COM  
L-COM P/N  
(SEE NOTE 1)

<p>UNLESS OTHERWISE SPECIFIED LEADING DIMENSIONS ARE INCHES DIMENSIONS IN [ ] ARE MILLIMETERS</p> <p><b>TOLERANCES:</b></p> <table style="width: 100%; border: none;"> <tr> <td style="border: none;">.X ± .2 [ .008 ]</td> <td style="border: none;">FRACTIONS ± 1/32</td> </tr> <tr> <td style="border: none;">.XX ± .02 [ .51 ]</td> <td style="border: none;">ANGLES ± 1°</td> </tr> <tr> <td style="border: none;">.XXX ± .005 [ .13 ]</td> <td style="border: none;">CABLE LENGTH (L) TOLERANCES:</td> </tr> <tr> <td style="border: none;">12 [305] &lt; L ≤ 60 [1524] = +2 [61] / -0</td> <td style="border: none;">L ≤ 12 [305] = +1 [25] / -0</td> </tr> <tr> <td style="border: none;">60 [1524] &lt; L ≤ 120 [3048] = +4 [102] / -0</td> <td style="border: none;">120 [3048] &lt; L ≤ 300 [7620] = +6 [152] / -0</td> </tr> <tr> <td style="border: none;">300 [7620] &lt; L = +5%L / -0</td> <td style="border: none;">ALL DIMENSIONS SHOWN ARE FOR REFERENCE ONLY.</td> </tr> </table>	.X ± .2 [ .008 ]	FRACTIONS ± 1/32	.XX ± .02 [ .51 ]	ANGLES ± 1°	.XXX ± .005 [ .13 ]	CABLE LENGTH (L) TOLERANCES:	12 [305] < L ≤ 60 [1524] = +2 [61] / -0	L ≤ 12 [305] = +1 [25] / -0	60 [1524] < L ≤ 120 [3048] = +4 [102] / -0	120 [3048] < L ≤ 300 [7620] = +6 [152] / -0	300 [7620] < L = +5%L / -0	ALL DIMENSIONS SHOWN ARE FOR REFERENCE ONLY.	<p style="text-align: center;"><b>THIRD-ANGLE PROJECTION</b></p> <p>THE INFORMATION AND DESIGN IN THIS DOCUMENT IS THE PROPERTY OF L-COM GLOBAL CONNECTIVITY. ALL RIGHTS RESERVED.</p> <p>SHEET 1 OF 1</p> <p>SCALE N/A</p> <p style="text-align: center;">REV A</p>
.X ± .2 [ .008 ]	FRACTIONS ± 1/32												
.XX ± .02 [ .51 ]	ANGLES ± 1°												
.XXX ± .005 [ .13 ]	CABLE LENGTH (L) TOLERANCES:												
12 [305] < L ≤ 60 [1524] = +2 [61] / -0	L ≤ 12 [305] = +1 [25] / -0												
60 [1524] < L ≤ 120 [3048] = +4 [102] / -0	120 [3048] < L ≤ 300 [7620] = +6 [152] / -0												
300 [7620] < L = +5%L / -0	ALL DIMENSIONS SHOWN ARE FOR REFERENCE ONLY.												

**NOTES:**

- CABLES 36" AND UNDER HAVE 1 LABEL CENTERED. CABLES OVER 36" HAVE 2 LABELS, ONE AT EACH END, 6.0" FROM THE FRONT OF THE CONNECTOR.

THESE COMMODITIES, TECHNOLOGY OR SOFTWARE WERE EXPORTED FROM THE UNITED STATES IN ACCORDANCE WITH THE EXPORT ADMINISTRATION REGULATIONS. DIVERSION CONTRARY TO U.S. LAW PROHIBITED.