

SMA Male Right Angle to SMA Male Right Angle Cable Assembly using LC085TBJ Coax, 4 FT

LCCA30133-FT4

Configuration

- Connector 1: SMA Male Right AngleConnector 2: SMA Male Right Angle
- Cable Type: LC085TBJ


Features

- Max Frequency 10 GHz
- Shielding Effectivity > 100dB
- PTFE Dielectric with 69.5% VoP

Applications

- · General Purpose
- · Laboratory Use

- Hand Formable
- Tin Filled Copper Composite Braid Outer Conductor
- FEP Jacket
- · System Interconnect



Description

L-com's LCCA30133-FT4 is a SMA male right angle to SMA male right angle cable assembly using LC085TBJ coax, 4 FT and ships same-day. The LC085TBJ coax of this SMA cable uses the PTFE dielectric with a VoP of 69.5%. These formable RF cable assemblies are a great alternative to expensive semi-rigid assemblies because they can be hand formed to fit specific designs. Our L-com SMA to SMA cable assembly has a male to male gender configuration with formable LC085TBJ series coax and operates to 10 GHz. The jacketed tinned copper composite braid outer conductor is easily formed by hand with an overall diameter of 0.105 inches and excellent shielding effectiveness greater than 100dB. This right angle SMA cable interface on the LC085TBJ coax allows for easier connections in tight spaces.

Custom versions of this SMA male to SMA male cable, along with the rest of L-com's other RF assemblies, can also be built and shipped same day. Other available RF cable assembly value added services from L-com include connector orientation or clocking, heat shrink booting and custom labeling. RF testing can also be performed to document the electrical performance of your cable assembly. Contact a sales representative for testing or custom RF cable quotes. Part number LCCA30133-FT4 L-com SMA Male Right Angle to SMA Male Right Angle Cable Assembly using LC085TBJ Coax, 4 FT data sheet PDF includes details of the RF product specifications, CAD drawing(s) and dimensions below.



SMA Male Right Angle to SMA Male Right Angle Cable Assembly using LC085TBJ Coax, 4 FT



LCCA30133-FT4

Electrical Specifications

Description	Minimum	Typical	Maximum	Units
Frequency Range	DC		10	GHz
Velocity of Propagation		69.5		%
RF Shielding	100			dB
Group Delay		1.43 [4.69]		ns/ft [ns/m]
Capacitance		29.4 [96.46]		pF/ft [pF/m]
DC Resistance Inner Conduc	tor	65.7 [215.55]		Ohms/1000ft [Ohms/Km]
DC Resistance Outer Conduc	ctor	10.2 [33.46]		Ohms/1000ft [Ohms/Km]
Operating Voltage (AC)			1,500	Vrms

Specifications by Frequency

Description	F1	F2	F3	F4	F5	Units
Frequency	0.5	1	2.5	5	10	GHz
Insertion Loss (Max.)	1	1.3	1.79	2.6	3.65	dB

Electrical Specification Notes:

The Insertion Loss data above is based on the performance specifications of the coax cable and connectors used in this assembly. The Insertion Loss is estimated as 0.2 dB per connector.

Mechanical Specifications

Cable Assembly

Length 48 in [121.92 cm] Diameter 0.105 in [2.67 mm]

Cable

Cable Type LC085TBJ 50 Ohms Impedance Inner Conductor Type Solid

Copper Clad Steel, Silver Inner Conductor Material and Plating

Dielectric Type PTFE Number of Shields

Outer Conductor Material and Plating Tinned Copper Composite Braid

Outer Conductor Diameter 0.085 in [2.16 mm]

Jacket Material

FEP Jacket Diameter 0.105 in [2.67 mm]

One Time Minimum Bend Radius 0.5 in [12.7 mm]



SMA Male Right Angle to SMA Male Right Angle Cable Assembly using LC085TBJ Coax, 4 FT

LCCA30133-FT4

Repeated Minimum Bend Radius

0.787 in [19.99 mm]

Connectors

Description	Connector 1	Connector 2		
Туре	SMA Male Right Angle	SMA Male Right Angle		
Impedance	50 Ohms	50 Ohms		
Contact Material and Plating	Brass, Gold over Nickel	Brass, Gold over Nickel		
Contact Plating Specification	8 µin minimum	8 µin minimum		
Dielectric Type	PTFE	PTFE		
Body Material and Plating	Brass, Gold over Nickel	Brass, Gold over Nickel		
Body Plating Specification	4 μin minimum	4 μin minimum		
Coupling Nut Material and Plating	Passivated Stainless Steel	Passivated Stainless Steel		
Hex Size	5/16 inch	5/16 inch		
Torque	10 in-lbs 1.13 Nm	10 in-lbs 1.13 Nm		

Environmental Specifications

Temperature

Operating Range

-55 to +125 deg C

Compliance Certifications (see product page for current document)

Plotted and Other Data

Notes:


• Values at 25°C, sea level.



SMA Male Right Angle to SMA Male Right Angle Cable Assembly using LC085TBJ Coax, 4 FT

LCCA30133-FT4

How to Order



Example: LCCA30133-12 = 12 inches long cable

LCCA30133-100cm = 100 cm long cable

SMA Male Right Angle to SMA Male Right Angle Cable Assembly using LC085TBJ Coax, 4 FT from L-com has same day shipment for domestic and International orders. L-com is a leading manufacturer of wired and wireless connectivity products and committed to in-stock availability and same day shipping. Our portfolio includes coaxial cable assemblies, connectors, adapters and custom products as well as lightning and surge protectors, NEMA rated enclosures, and an RF product line which includes antennas, amplifiers, passive, and active components.

The information contained within this document is accurate to the best of our knowledge and representative of the part described herein. It may be necessary to make modifications to the part and/or the documentation of the part in order to impliment improvements. L-com reserves the right to make such changes as required. Unless otherwise stated, all specifications are nominal. L-com does not make any representation or warranty regarding the suitability of the part described herein for any particular purpose, and L-com does not assume liability arising out of the use of any part or document.ontained within this document is accurate to the best of our knowledge and representative of the part described herein. It may be necessary to make modifications to the part and/or the documentation of the part in order to impliment improvements. L-com reserves the right to make such changes as required. Unless otherwise stated, all specifications are nominal. L-com does not make any representation or warranty regarding the suitability of the part described herein for any particular purpose, and L-com does not assume liability arising out of the use of any part or document.

L-com CAD Drawing

