

Low Loss 7/16 DIN Male to N Male Right Angle Cable Assembly using LMR-600-DB Coax, 4 FT with Times Microwave Components



## LCCA30347-FT4

### Configuration


- Connector 1: 7/16 DIN Male
- Connector 2: N Male Right Angle
- Cable Type: LMR-600-DB

### Features

- Using Times Microwave Components
- Max Frequency 5.8 GHz
- Shielding Effectivity > 90 dB
- 87% Phase Velocity
- PE Jacket
- Low Insertion Loss
- Bend Radius of 6 Inches

### Applications

- General Purpose
- Laboratory Use
- Antenna Installations
- Land Mobile Radio & Other Communication Systems
- Cellular & Wi-Fi Systems



### Description

L-com's LCCA30347-FT4 is a low loss 7/16 DIN male to N male right angle cable assembly using LMR-600-DB coax, 4 FT with Times Microwave components and ships same-day. The LMR-600-DB coax of this 7/16 DIN cable uses the PE (F) dielectric with a VoP of 87%, resulting in very low insertion loss compared to solid dielectrics. These flexible RF cable assemblies are ideal for applications where flexure is required. Our L-com 7/16 DIN to N cable assembly has a male to male gender configuration with flexible LMR-600-DB series coax and operates to 5.8 GHz. The double shield of this 7/16 DIN cable is layered by tinned copper braid over aluminum tape providing shielding effectiveness greater than 90dB. This right angle N cable interface on the LMR-600-DB coax allows for easier connections in tight spaces. \*LMR™ is a trademark of Times Microwave Systems.

Custom versions of this 7/16 DIN male to 7/16 DIN male cable, along with the rest of L-com's other RF assemblies, can also be built and shipped same day. Other available RF cable assembly value added services from L-com include connector orientation or clocking, heat shrink booting and custom labeling. RF testing can also be performed to document the electrical performance of your cable assembly. Contact a sales representative for testing or custom RF cable quotes. Part number LCCA30347-FT4 L-com Low Loss 7/16 DIN Male to N Male Right Angle Cable Assembly using LMR-600-DB Coax, 4 FT with Times Microwave Components data sheet PDF includes details of the RF product specifications, CAD drawing(s) and dimensions below.

Low Loss 7/16 DIN Male to N Male Right Angle Cable Assembly using LMR-600-DB Coax, 4 FT with Times Microwave Components



## LCCA30347-FT4

### Electrical Specifications

| Description                   | Minimum | Typical      | Maximum | Units                 |
|-------------------------------|---------|--------------|---------|-----------------------|
| Frequency Range               | DC      |              | 5.8     | GHz                   |
| VSWR                          |         |              | 1.4:1   |                       |
| Velocity of Propagation       |         | 87           |         | %                     |
| RF Shielding                  | 90      |              |         | dB                    |
| Group Delay                   |         | 1.17 [3.84]  |         | ns/ft [ns/m]          |
| Capacitance                   |         | 23.4 [76.77] |         | pF/ft [pF/m]          |
| Inductance                    |         | 0.058 [0.19] |         | uH/ft [uH/m]          |
| DC Resistance Inner Conductor |         | 0.53 [1.74]  |         | Ohms/1000ft [Ohms/Km] |
| DC Resistance Outer Conductor |         | 1.2 [3.94]   |         | Ohms/1000ft [Ohms/Km] |
| Jacket Spark                  |         |              | 8,000   | Vrms                  |

### Specifications by Frequency

| Description           | F1   | F2   | F3  | F4   | F5   | Units |
|-----------------------|------|------|-----|------|------|-------|
| Frequency             | 0.25 | 0.5  | 1   | 2.5  | 5.8  | GHz   |
| Insertion Loss (Typ.) | 0.35 | 0.37 | 0.4 | 0.48 | 0.59 | dB    |

#### Electrical Specification Notes:

The Insertion Loss data above is based on the performance specifications of the coax cable and connectors used in this assembly. The Insertion Loss includes an estimated insertion loss of 0.1 dB for the straight connector and 0.2 dB for the right angle connector.

### Mechanical Specifications

#### Cable Assembly

Length 48 in [121.92 cm]  
Diameter 1.25 in [31.75 mm]

#### Cable

Cable Type LMR-600-DB  
Impedance 50 Ohms  
Inner Conductor Type Solid  
Inner Conductor Material and Plating Copper Clad Aluminum  
Dielectric Type PE (F)  
Number of Shields 2  
Shield Layer 1 Aluminum Tape  
Shield Layer 2 Tinned Copper Braid

Low Loss 7/16 DIN Male to N Male Right Angle Cable Assembly using LMR-600-DB Coax, 4 FT with Times Microwave Components



## LCCA30347-FT4

|                              |                        |
|------------------------------|------------------------|
| Jacket Material              | PE, Black              |
| Jacket Diameter              | 0.59 in [14.99 mm]     |
| One Time Minimum Bend Radius | 1.5 in [38.1 mm]       |
| Repeated Minimum Bend Radius | 6 in [152.4 mm]        |
| Bending Moment               | 2.75 lbs-ft [3.73 N-m] |
| Flat Plate Crush             | 60 lbs/in [1.07 Kg/mm] |
| Tensile Strength             | 350 lbs [158.76 Kg]    |

### Connectors

| Description                           | Connector 1            | Connector 2            |
|---------------------------------------|------------------------|------------------------|
| Type                                  | 7/16 DIN Male          | N Male Right Angle     |
| Impedance                             | 50 Ohms                | 50 Ohms                |
| Contact Material and Plating          | Copper, Silver         | Beryllium Copper, Gold |
| Contact Plating Specification         | 196µ in. minimum       | 1.27µm minimum         |
| Dielectric Type                       | PTFE                   | PTFE                   |
| Outer Conductor Material and Plating  | Brass, Tri-Metal       |                        |
| Outer Conductor Plating Specification | 78µin. minimum         |                        |
| Body Material and Plating             | Brass, Tri-Metal       | Brass, Tri-Metal       |
| Body Plating Specification            | 78µ in. minimum        | 2µm minimum            |
| Coupling Nut Material and Plating     | Brass, Nickel          | Brass, Tri-Metal       |
| Coupling Nut Plating Specification    | 196µ in. minimum       | 2µm minimum            |
| Hex Size                              | 1 1/4 in               | 20.57 mm               |
| Torque                                | 18.417 ft-lbs 24.97 Nm | 44 in-lbs 4.97 Nm      |

### Environmental Specifications

#### Temperature

|                 |                  |
|-----------------|------------------|
| Operating Range | -40 to +85 deg C |
| Storage Range   | -70 to +85 deg C |

**Compliance Certifications** (see [product page](#) for current document)

### Plotted and Other Data

Notes:

Low Loss 7/16 DIN Male to N Male Right Angle Cable Assembly using LMR-600-DB Coax, 4 FT with Times Microwave Components



## LCCA30347-FT4

### How to Order

Part Number Configuration:

**LCCA30347 - xx uu**



Example: LCCA30347-12 = 12 inches long cable  
LCCA30347-100cm = 100 cm long cable

Low Loss 7/16 DIN Male to N Male Right Angle Cable Assembly using LMR-600-DB Coax, 4 FT with Times Microwave Components from L-com has same day shipment for domestic and International orders. L-com is a leading manufacturer of wired and wireless connectivity products and committed to in-stock availability and same day shipping. Our portfolio includes coaxial cable assemblies, connectors, adapters and custom products as well as lightning and surge protectors, NEMA rated enclosures, and an RF product line which includes antennas, amplifiers, passive, and active components.

The information contained within this document is accurate to the best of our knowledge and representative of the part described herein. It may be necessary to make modifications to the part and/or the documentation of the part in order to impliment improvements. L-com reserves the right to make such changes as required. Unless otherwise stated, all specifications are nominal. L-com does not make any representation or warranty regarding the suitability of the part described herein for any particular purpose, and L-com does not assume liability arising out of the use of any part or document.ontained within this document is accurate to the best of our knowledge and representative of the part described herein. It may be necessary to make modifications to the part and/or the documentation of the part in order to impliment improvements. L-com reserves the right to make such changes as required. Unless otherwise stated, all specifications are nominal. L-com does not make any representation or warranty regarding the suitability of the part described herein for any particular purpose, and L-com does not assume liability arising out of the use of any part or document.

Low Loss 7/16 DIN Male to N Male Right Angle Cable Assembly using LMR-600-DB Coax, 4 FT with Times Microwave Components

L-com CAD Drawing

