

SMA Male to TNC Male Cable Assembly using LC141TB Coax, 2 FT



**LCCA30422-FT2**

**Configuration**

- Connector 1: SMA Male
- Connector 2: TNC Male
- Cable Type: LC141TB

**Features**

- Max Frequency 6 GHz
- Shielding Effectivity > 100dB
- PTFE Dielectric with 69.9% VoP
- Hand Formable
- Tin Filled Copper Braid Outer Conductor

**Applications**

- General Purpose
- Laboratory Use
- System Interconnect



**Description**

L-com's LCCA30422-FT2 is a SMA male to TNC male cable assembly using LC141TB coax, 2 FT and ships same-day. The LC141TB coax of this SMA cable uses the PTFE dielectric with a VoP of 69.5%. These formable RF cable assemblies are a great alternative to expensive semi-rigid assemblies because they can be hand formed to fit specific designs. Our L-com SMA to TNC cable assembly has a male to male gender configuration with formable LC141TB series coax and operates to 6 GHz. The outer conductor is easily formed by hand with an overall diameter of inches and excellent shielding effectiveness greater than 100dB.

Custom versions of this SMA male to SMA male cable, along with the rest of L-com's other RF assemblies, can also be built and shipped same day. Other available RF cable assembly value added services from L-com include connector orientation or clocking, heat shrink booting and custom labeling. RF testing can also be performed to document the electrical performance of your cable assembly. Contact a sales representative for testing or custom RF cable quotes. Part number LCCA30422-FT2 L-com SMA Male to TNC Male Cable Assembly using LC141TB Coax, 2 FT data sheet PDF includes details of the RF product specifications, CAD drawing(s) and dimensions below.

SMA Male to TNC Male Cable Assembly using LC141TB Coax, 2 FT



## LCCA30422-FT2

### Electrical Specifications

Description	Minimum	Typical	Maximum	Units
Frequency Range	DC		6	GHz
VSWR			1.45:1	
Velocity of Propagation		69.5		%
RF Shielding	100			dB
Group Delay		1.43 [4.69]		ns/ft [ns/m]
Capacitance		29 [95.14]		pF/ft [pF/m]

### Specifications by Frequency

Description	F1	F2	F3	F4	F5	Units
Frequency	0.5	1	2.5	6		GHz
Insertion Loss (Max.)	0.36	0.44	0.57	0.84		dB

#### Electrical Specification Notes:

The Insertion Loss data above is based on the performance specifications of the coax cable and connectors used in this assembly. The Insertion Loss includes an estimated insertion loss of 0.1 dB per connector.

### Mechanical Specifications

#### Cable Assembly

Length	24 in [609.6 mm]
Diameter	0.59 in [14.99 mm]
Weight	0.068 lbs [30.84 g]

#### Cable

Cable Type	LC141TB
Impedance	50 Ohms
Inner Conductor Type	Solid
Inner Conductor Material and Plating	Copper, Silver
Dielectric Type	PTFE
Number of Shields	1
Shield Layer 1	Tinned Copper Braid
One Time Minimum Bend Radius	0.315 in [8 mm]
Repeated Minimum Bend Radius	1.57 in [39.88 mm]

SMA Male to TNC Male Cable Assembly using LC141TB Coax, 2 FT



## LCCA30422-FT2

### Connectors

Description	Connector 1	Connector 2
Type	SMA Male	TNC Male
Specification	MIL-STD-348A	
Impedance	50 Ohms	50 Ohms
Contact Material and Plating	Brass, Gold	Gold
Contact Plating Specification	50μ in. minimum	
Dielectric Type	Teflon	PTFE
Body Material and Plating	Stainless Steel, Gold	Brass, Gold
Body Plating Specification	10μ in. minimum	
Coupling Nut Material and Plating	Brass, Nickel	Brass, Nickel
Coupling Nut Plating Specification	100μ in. minimum	
Hex Size	5/16 in	
Torque	5 in-lbs 0.57 Nm	

### Environmental Specifications

#### Temperature

Operating Range -55 to +125 deg C

**Compliance Certifications** (see [product page](#) for current document)

### Plotted and Other Data

Notes:

- Values at 25°C, sea level.

SMA Male to TNC Male Cable Assembly using LC141TB Coax, 2 FT



## LCCA30422-FT2

### How to Order

Part Number Configuration:

**LCCA30422 - xx uu**



Example: LCCA30422-12 = 12 inches long cable  
LCCA30422-100cm = 100 cm long cable

SMA Male to TNC Male Cable Assembly using LC141TB Coax, 2 FT from L-com has same day shipment for domestic and International orders. L-com is a leading manufacturer of wired and wireless connectivity products and committed to in-stock availability and same day shipping. Our portfolio includes coaxial cable assemblies, connectors, adapters and custom products as well as lightning and surge protectors, NEMA rated enclosures, and an RF product line which includes antennas, amplifiers, passive, and active components.

The information contained within this document is accurate to the best of our knowledge and representative of the part described herein. It may be necessary to make modifications to the part and/or the documentation of the part in order to implement improvements. L-com reserves the right to make such changes as required. Unless otherwise stated, all specifications are nominal. L-com does not make any representation or warranty regarding the suitability of the part described herein for any particular purpose, and L-com does not assume liability arising out of the use of any part or document contained within this document is accurate to the best of our knowledge and representative of the part described herein. It may be necessary to make modifications to the part and/or the documentation of the part in order to implement improvements. L-com reserves the right to make such changes as required. Unless otherwise stated, all specifications are nominal. L-com does not make any representation or warranty regarding the suitability of the part described herein for any particular purpose, and L-com does not assume liability arising out of the use of any part or document.

# SMA Male to TNC Male Cable Assembly using LC141TB Coax, 2 FT

## L-com CAD Drawing

REVISIONS		DATE	APPROVED
REV.	DESCRIPTION		
A	INITIAL RELEASE	04/29/20	SELLIS

  

LENGTH MEASURED FROM CONTACT TO CONTACT

SMA MALE      LC141TB      TNC MALE

SOLDER      SOLDER

WWW.L-COM.COM  
L-COM P/N  
SEE NOTE 1

  

<p>UNLESS OTHERWISE SPECIFIED LEADING DIMENSIONS ARE INCHES DIMENSIONS IN [ ] ARE MILLIMETERS</p> <p><b>TOLERANCES:</b></p> <table style="width: 100%; border: none;"> <tr> <td style="border: none;">.X = ±.2</td> <td style="border: none;">[5.08]</td> <td style="border: none;">FRACTIONS</td> <td style="border: none;">±1/32</td> </tr> <tr> <td style="border: none;">.XX = ±.02</td> <td style="border: none;">[.51]</td> <td style="border: none;">ANGLES ± 1°</td> <td style="border: none;"></td> </tr> <tr> <td style="border: none;">.XXX = ±.005</td> <td style="border: none;">[.13]</td> <td style="border: none;">CABLE LENGTH (L) TOLERANCES:</td> <td style="border: none;"></td> </tr> <tr> <td style="border: none;">12 [305]</td> <td style="border: none;">&lt; L ≤ 60 [1524]</td> <td style="border: none;">= ±1 [25] / -0</td> <td style="border: none;"></td> </tr> <tr> <td style="border: none;">60 [1524]</td> <td style="border: none;">&lt; L ≤ 120 [3048]</td> <td style="border: none;">= ±4 [102] / -0</td> <td style="border: none;"></td> </tr> <tr> <td style="border: none;">120 [3048]</td> <td style="border: none;">&lt; L ≤ 300 [7620]</td> <td style="border: none;">= +6 [152] / -0</td> <td style="border: none;"></td> </tr> <tr> <td style="border: none;"></td> <td style="border: none;">300 [7620]</td> <td style="border: none;">&lt; L = +5% / -0</td> <td style="border: none;"></td> </tr> </table> <p>ALL DIMENSIONS SHOWN ARE FOR REFERENCE ONLY.</p>	.X = ±.2	[5.08]	FRACTIONS	±1/32	.XX = ±.02	[.51]	ANGLES ± 1°		.XXX = ±.005	[.13]	CABLE LENGTH (L) TOLERANCES:		12 [305]	< L ≤ 60 [1524]	= ±1 [25] / -0		60 [1524]	< L ≤ 120 [3048]	= ±4 [102] / -0		120 [3048]	< L ≤ 300 [7620]	= +6 [152] / -0			300 [7620]	< L = +5% / -0		<p style="text-align: center;"><b>THIRD-ANGLE PROJECTION</b></p> <p style="text-align: center;"> </p> <p style="font-size: small;">THE INFORMATION AND DESIGN IN THIS DOCUMENT IS THE PROPERTY OF L-COM GLOBAL CONNECTIVITY. ALL RIGHTS RESERVED.</p> <p style="text-align: center;">SHEET 1 OF 1</p> <p style="text-align: center;">SCALE N/A</p> <p style="text-align: center;">REV A</p>
.X = ±.2	[5.08]	FRACTIONS	±1/32																										
.XX = ±.02	[.51]	ANGLES ± 1°																											
.XXX = ±.005	[.13]	CABLE LENGTH (L) TOLERANCES:																											
12 [305]	< L ≤ 60 [1524]	= ±1 [25] / -0																											
60 [1524]	< L ≤ 120 [3048]	= ±4 [102] / -0																											
120 [3048]	< L ≤ 300 [7620]	= +6 [152] / -0																											
	300 [7620]	< L = +5% / -0																											

  

**NOTES:**

- CABLES 36" AND UNDER HAVE 1 LABEL CENTERED. CABLES OVER 36" HAVE 2 LABELS, ONE AT EACH END 6.0" FROM THE FRONT OF THE CONNECTOR.

THESE COMMODITIES, TECHNOLOGY OR SOFTWARE WERE EXPORTED FROM THE UNITED STATES IN ACCORDANCE WITH THE EXPORT ADMINISTRATION REGULATIONS. DIVERSION CONTRARY TO U.S. LAW PROHIBITED.