

N Female to TNC Male Cable Assembly using LC141TBJ Coax, 3 FT



LCCA30518-FT3

Configuration


- Connector 1: N Female
- Connector 2: TNC Male
- Cable Type: LC141TBJ

Features

- Max Frequency 6 GHz
- Shielding Effectivity > 100dB
- PTFE Dielectric with 70.0% VoP
- Hand Formable
- Tin Filled Copper Braid Outer Conductor
- FEP Jacket

Applications

- General Purpose
- Laboratory Use
- System Interconnect



Description

L-com's LCCA30518-FT3 is a N female to TNC male cable assembly using LC141TBJ coax, 3 FT and ships same-day. The LC141TBJ coax of this N cable uses the PTFE dielectric with a VoP of 70%. These formable RF cable assemblies are a great alternative to expensive semi-rigid assemblies because they can be hand formed to fit specific designs. Our L-com N to TNC cable assembly has a female to male gender configuration with formable LC141TBJ series coax and operates to 6 GHz. The jacketed tinned copper braid outer conductor is easily formed by hand with an overall diameter of 0.161 inches and excellent shielding effectiveness greater than 100dB.

Custom versions of this N female to N male cable, along with the rest of L-com's other RF assemblies, can also be built and shipped same day. Other available RF cable assembly value added services from L-com include connector orientation or clocking, heat shrink booting and custom labeling. RF testing can also be performed to document the electrical performance of your cable assembly. Contact a sales representative for testing or custom RF cable quotes. Part number LCCA30518-FT3 L-com N Female to TNC Male Cable Assembly using LC141TBJ Coax, 3 FT data sheet PDF includes details of the RF product specifications, CAD drawing(s) and dimensions below.

N Female to TNC Male Cable Assembly using LC141TBJ Coax, 3 FT



LCCA30518-FT3

Electrical Specifications

| Description | Minimum | Typical | Maximum | Units |
|-------------------------------|---------|--------------|---------|-----------------------|
| Frequency Range | DC | | 6 | GHz |
| VSWR | | | 1.45:1 | |
| Velocity of Propagation | | 70 | | % |
| RF Shielding | 100 | | | dB |
| Group Delay | | 1.43 [4.69] | | ns/ft [ns/m] |
| Capacitance | | 29 [95.14] | | pF/ft [pF/m] |
| DC Resistance Inner Conductor | | 7.28 [23.88] | | Ohms/1000ft [Ohms/Km] |
| DC Resistance Outer Conductor | | 5.5 [18.04] | | Ohms/1000ft [Ohms/Km] |

Specifications by Frequency

| Description | F1 | F2 | F3 | F4 | F5 | Units |
|-----------------------|------|------|------|------|----|-------|
| Frequency | 0.5 | 1 | 2.5 | 6 | | GHz |
| Insertion Loss (Typ.) | 0.45 | 0.58 | 0.77 | 1.25 | | dB |

Electrical Specification Notes:

The Insertion Loss data above is based on the performance specifications of the coax cable and connectors used in this assembly. The Insertion Loss includes an estimated insertion loss of 0.1 dB for the straight connector and 0.2 dB for the right angle connector.

Mechanical Specifications

Cable Assembly

Length 36 in [914.4 mm]
Diameter 0.63 in [16 mm]

Cable

Cable Type LC141TBJ
Impedance 50 Ohms
Inner Conductor Type Solid
Inner Conductor Material and Plating Copper, Silver
Dielectric Type PTFE
Outer Conductor Material and Plating Tinned Copper Braid
Jacket Material FEP, Black
Jacket Diameter 0.161 in [4.09 mm]

One Time Minimum Bend Radius 0.315 in [8 mm]
Repeated Minimum Bend Radius 1.575 in [40.01 mm]

N Female to TNC Male Cable Assembly using LC141TBJ Coax, 3 FT



LCCA30518-FT3

Connectors

| Description | Connector 1 | Connector 2 |
|-----------------------------------|-----------------------------------|-------------------------|
| Type | N Female | TNC Male |
| Impedance | 50 Ohms | 50 Ohms |
| Contact Material and Plating | Phosphor Bronze, Gold over Nickel | Brass, Gold over Nickel |
| Dielectric Type | PTFE | PTFE |
| Body Material and Plating | Brass, Nickel | Brass, Nickel |
| Coupling Nut Material and Plating | | Brass, Nickel |

Environmental Specifications

Temperature

Operating Range -65 to +150 deg C

Compliance Certifications (see [product page](#) for current document)

Plotted and Other Data

Notes:

N Female to TNC Male Cable Assembly using LC141TBJ Coax, 3 FT




LCCA30518-FT3

How to Order

Part Number Configuration:

LCCA30518 - xx uu



Example: LCCA30518-12 = 12 inches long cable
LCCA30518-100cm = 100 cm long cable

N Female to TNC Male Cable Assembly using LC141TBJ Coax, 3 FT from L-com has same day shipment for domestic and International orders. L-com is a leading manufacturer of wired and wireless connectivity products and committed to in-stock availability and same day shipping. Our portfolio includes coaxial cable assemblies, connectors, adapters and custom products as well as lightning and surge protectors, NEMA rated enclosures, and an RF product line which includes antennas, amplifiers, passive, and active components.

The information contained within this document is accurate to the best of our knowledge and representative of the part described herein. It may be necessary to make modifications to the part and/or the documentation of the part in order to impliment improvements. L-com reserves the right to make such changes as required. Unless otherwise stated, all specifications are nominal. L-com does not make any representation or warranty regarding the suitability of the part described herein for any particular purpose, and L-com does not assume liability arising out of the use of any part or document.ontained within this document is accurate to the best of our knowledge and representative of the part described herein. It may be necessary to make modifications to the part and/or the documentation of the part in order to impliment improvements. L-com reserves the right to make such changes as required. Unless otherwise stated, all specifications are nominal. L-com does not make any representation or warranty regarding the suitability of the part described herein for any particular purpose, and L-com does not assume liability arising out of the use of any part or document.

N Female to TNC Male Cable Assembly using LC141TBJ Coax, 3 FT

L-com CAD Drawing

| REVISIONS | | |
|-----------|-----------------|--------------------|
| REV. | DESCRIPTION | DATE |
| A | INITIAL RELEASE | 05/08/2020 |
| | | APPROVED SELLIS |

LENGTH MEASURED FROM CONTACT TO CONTACT

TNC MALE

TYPE N FEMALE

WWW.L-COM.COM
L-COM P/N
(SEE NOTE 1)

| | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | |
|--|-----------------|-------------|-----------|-------------|--------|--------|---------------|--------|-------------|--------------|----------------|--------------------------|----------------|----------------------------|-----------------|-----------------------------|-----------------|----------------|--------------|--|------|-----------|----------|----------|---|-------|------------|-----------|--|--|--|-------|
| <p>UNLESS OTHERWISE SPECIFIED, LEADING DIMENSIONS ARE INCHES DIMENSIONS IN [] ARE MILLIMETERS</p> <p>TOLERANCES:</p> <table style="width: 100%; border: none;"> <tr> <td>X = ± .2</td> <td>[.06]</td> <td>FRACTIONS</td> </tr> <tr> <td>.XX = ± .02</td> <td>[.51]</td> <td>± 1/32</td> </tr> <tr> <td>.XXX = ± .005</td> <td>[.13]</td> <td>ANGLES ± 1°</td> </tr> </table> <p>CABLE LENGTH (L) TOLERANCES:</p> <table style="width: 100%; border: none;"> <tr> <td>L ≤ 12 [305]</td> <td>= +1 [25] / -0</td> </tr> <tr> <td>12 [305] < L ≤ 60 [1524]</td> <td>= +2 [51] / -0</td> </tr> <tr> <td>60 [1524] < L ≤ 120 [3048]</td> <td>= +4 [102] / -0</td> </tr> <tr> <td>120 [3048] < L ≤ 300 [7620]</td> <td>= +6 [152] / -0</td> </tr> <tr> <td>300 [7620] < L</td> <td>= +5% L / -0</td> </tr> </table> <p>ALL DIMENSIONS SHOWN ARE FOR REFERENCE ONLY.</p> | X = ± .2 | [.06] | FRACTIONS | .XX = ± .02 | [.51] | ± 1/32 | .XXX = ± .005 | [.13] | ANGLES ± 1° | L ≤ 12 [305] | = +1 [25] / -0 | 12 [305] < L ≤ 60 [1524] | = +2 [51] / -0 | 60 [1524] < L ≤ 120 [3048] | = +4 [102] / -0 | 120 [3048] < L ≤ 300 [7620] | = +6 [152] / -0 | 300 [7620] < L | = +5% L / -0 | <div style="text-align: center;"> <p>an INFINITE brand</p> <p>50 High Street, West Mill, 3rd Floor, Suite #30 North Andover, MA 01845 USA</p> <p>Phone: 1.800.341.5266 1.978.682.6936 Fax: 1.978.689.9484 Website: www.L-com.com E-mail: CustomerService@L-com.com</p> </div> <p style="text-align: center;">THIRD-ANGLE PROJECTION</p> <div style="text-align: center;"> <p>THE INFORMATION AND DESIGN IN THIS DOCUMENT IS THE PROPERTY OF L-COM GLOBAL CONNECTIVITY. ALL RIGHTS RESERVED.</p> <p>SHEET 1 OF 1</p> <p>SCALE N/A</p> </div> <table style="width: 100%; border: none;"> <tr> <td>SIZE</td> <td>CAGE CODE</td> <td>DRAWN BY</td> <td>ITEM NO.</td> </tr> <tr> <td style="text-align: center;">A</td> <td style="text-align: center;">43321</td> <td style="text-align: center;">DFRISIELLO</td> <td style="text-align: center;">LCCA30518</td> </tr> <tr> <td></td> <td></td> <td></td> <td style="text-align: center;">REV A</td> </tr> </table> | SIZE | CAGE CODE | DRAWN BY | ITEM NO. | A | 43321 | DFRISIELLO | LCCA30518 | | | | REV A |
| X = ± .2 | [.06] | FRACTIONS | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | |
| .XX = ± .02 | [.51] | ± 1/32 | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | |
| .XXX = ± .005 | [.13] | ANGLES ± 1° | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | |
| L ≤ 12 [305] | = +1 [25] / -0 | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | |
| 12 [305] < L ≤ 60 [1524] | = +2 [51] / -0 | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | |
| 60 [1524] < L ≤ 120 [3048] | = +4 [102] / -0 | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | |
| 120 [3048] < L ≤ 300 [7620] | = +6 [152] / -0 | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | |
| 300 [7620] < L | = +5% L / -0 | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | |
| SIZE | CAGE CODE | DRAWN BY | ITEM NO. | | | | | | | | | | | | | | | | | | | | | | | | | | | | | |
| A | 43321 | DFRISIELLO | LCCA30518 | | | | | | | | | | | | | | | | | | | | | | | | | | | | | |
| | | | REV A | | | | | | | | | | | | | | | | | | | | | | | | | | | | | |

THESE COMMODITIES, TECHNOLOGY OR SOFTWARE WERE EXPORTED FROM THE UNITED STATES IN ACCORDANCE WITH THE EXPORT ADMINISTRATION REGULATIONS. DIVERSION CONTRARY TO U.S. LAW PROHIBITED.

T-RevD