

## BNC Female to N Female Cable Assembly using LC085TB Coax, 6 FT



### LCCA30573-FT6

#### Configuration

- Connector 1: BNC Female
- Connector 2: N Female
- Cable Type: LC085TB

#### Features

- Max Frequency 1 GHz
- Shielding Effectivity > 100dB
- PTFE Dielectric with 69.5% VoP
- Hand Formable
- Tin Filled Copper Composite Braid Outer Conductor

#### Applications

- General Purpose
- Laboratory Use
- System Interconnect



#### Description

L-com's LCCA30573-FT6 is a BNC female to N female cable assembly using LC085TB coax, 6 FT and ships same-day. The LC085TB coax of this BNC cable uses the PTFE dielectric with a VoP of 69.5%. These formable RF cable assemblies are a great alternative to expensive semi-rigid assemblies because they can be hand formed to fit specific designs. Our L-com BNC to N cable assembly has a female to female gender configuration with formable LC085TB series coax and operates to 1 GHz. The tin plated copper outer conductor can be easily formed by hand and has an overall diameter of 0.085 inches.

Custom versions of this BNC female to BNC female cable, along with the rest of L-com's other RF assemblies, can also be built and shipped same day. Other available RF cable assembly value added services from L-com include connector orientation or clocking, heat shrink booting and custom labeling. RF testing can also be performed to document the electrical performance of your cable assembly. Contact a sales representative for testing or custom RF cable quotes. Part number LCCA30573-FT6 L-com BNC Female to N Female Cable Assembly using LC085TB Coax, 6 FT data sheet PDF includes details of the RF product specifications, CAD drawing(s) and dimensions below.

BNC Female to N Female Cable Assembly using LC085TB Coax, 6 FT



## LCCA30573-FT6

### Electrical Specifications

| Description                   | Minimum | Typical       | Maximum | Units                 |
|-------------------------------|---------|---------------|---------|-----------------------|
| Frequency Range               | DC      |               | 1,000   | MHz                   |
| VSWR                          |         |               | 1.45:1  |                       |
| Velocity of Propagation       |         | 69.5          |         | %                     |
| Capacitance                   |         | 29 [95.14]    |         | pF/ft [pF/m]          |
| DC Resistance Inner Conductor |         | 65.7 [215.55] |         | Ohms/1000ft [Ohms/Km] |
| DC Resistance Outer Conductor |         | 10.2 [33.46]  |         | Ohms/1000ft [Ohms/Km] |

### Specifications by Frequency

| Description           | F1  | F2    | F3 | F4 | F5 | Units |
|-----------------------|-----|-------|----|----|----|-------|
| Frequency             | 500 | 1,000 |    |    |    | MHz   |
| Insertion Loss (Typ.) | 1.1 | 1.58  |    |    |    | dB    |

#### Electrical Specification Notes:

The Insertion Loss data above is based on the performance specifications of the coax cable and connectors used in this assembly. The Insertion Loss includes an estimated insertion loss of 0.1 dB per connector.

### Mechanical Specifications

#### Cable Assembly

Length 72 in [182.88 cm]

#### Cable

Cable Type LC085TB  
 Impedance 50 Ohms  
 Inner Conductor Type Solid  
 Inner Conductor Material and Plating Copper Clad Steel, Silver  
 Dielectric Type PTFE  
 Number of Shields 1  
 Outer Conductor Material and Plating Copper, Tin  
 Outer Conductor Diameter 0.085 in [2.16 mm]  
 Repeated Minimum Bend Radius 0.78 in [19.81 mm]

BNC Female to N Female Cable Assembly using LC085TB Coax, 6 FT



## LCCA30573-FT6

### Connectors

| Description                   | Connector 1     | Connector 2           |
|-------------------------------|-----------------|-----------------------|
| Type                          | BNC Female      | N Female              |
| Impedance                     | 50 Ohms         | 50 Ohms               |
| Contact Material and Plating  | Brass, Gold     | Phosphor Bronze, Gold |
| Contact Plating Specification | 30 µin minimum  |                       |
| Dielectric Type               | PTFE            | PTFE                  |
| Body Material and Plating     | Brass, Nickel   | Brass, Nickel         |
| Body Plating Specification    | 100 µin minimum |                       |
| Seal Gasket Material          | Silicone        |                       |

**Compliance Certifications** (see [product page](#) for current document)

### Plotted and Other Data

Notes:

BNC Female to N Female Cable Assembly using LC085TB Coax, 6 FT




## LCCA30573-FT6

### How to Order

Part Number Configuration:

**LCCA30573 - xx uu**



Example: LCCA30573-12 = 12 inches long cable  
LCCA30573-100cm = 100 cm long cable

BNC Female to N Female Cable Assembly using LC085TB Coax, 6 FT from L-com has same day shipment for domestic and International orders. L-com is a leading manufacturer of wired and wireless connectivity products and committed to in-stock availability and same day shipping. Our portfolio includes coaxial cable assemblies, connectors, adapters and custom products as well as lightning and surge protectors, NEMA rated enclosures, and an RF product line which includes antennas, amplifiers, passive, and active components.

The information contained within this document is accurate to the best of our knowledge and representative of the part described herein. It may be necessary to make modifications to the part and/or the documentation of the part in order to impliment improvements. L-com reserves the right to make such changes as required. Unless otherwise stated, all specifications are nominal. L-com does not make any representation or warranty regarding the suitability of the part described herein for any particular purpose, and L-com does not assume liability arising out of the use of any part or document.ontained within this document is accurate to the best of our knowledge and representative of the part described herein. It may be necessary to make modifications to the part and/or the documentation of the part in order to impliment improvements. L-com reserves the right to make such changes as required. Unless otherwise stated, all specifications are nominal. L-com does not make any representation or warranty regarding the suitability of the part described herein for any particular purpose, and L-com does not assume liability arising out of the use of any part or document.

# BNC Female to N Female Cable Assembly using LC085TB Coax, 6 FT

## L-com CAD Drawing

| REVISIONS |                 |            |          |
|-----------|-----------------|------------|----------|
| REV.      | DESCRIPTION     | DATE       | APPROVED |
| A         | INITIAL RELEASE | 06/02/2020 | SELLIS   |

LENGTH MEASURED FROM CONTACT TO CONTACT

BNC FEMALE

WWW.L-COM.COM  
L-COM P/N  
(SEE NOTE 1)

**NOTES:**

- CABLES 36" AND UNDER HAVE 1 LABEL CENTERED.  
CABLES OVER 36" HAVE 2 LABELS, ONE AT EACH END 6.0" FROM THE END OF THE CONNECTOR.

THESE COMMODITIES, TECHNOLOGY OR SOFTWARE WERE EXPORTED FROM THE UNITED STATES IN ACCORDANCE WITH THE EXPORT ADMINISTRATION REGULATIONS. DIVERSION CONTRARY TO U.S. LAW PROHIBITED.

|   |                  |                    |                 |             |                   |  |              |               |                          |               |                            |                |                             |                |                |               |   |  |
|---|------------------|--------------------|-----------------|-------------|-------------------|--|--------------|---------------|--------------------------|---------------|----------------------------|----------------|-----------------------------|----------------|----------------|---------------|---|--|
| <p>UNLESS OTHERWISE SPECIFIED LEADING DIMENSIONS ARE INCHES DIMENSIONS IN [ ] ARE MILLIMETERS</p> <p><b>TOLERANCES:</b></p> <table style="width: 100%; border: none;"> <tr> <td>.X ± .2 [5.08]</td> <td>FRACTIONS ± 1/32</td> </tr> <tr> <td>.XX ± .02 [.51]</td> <td>ANGLES ± 1°</td> </tr> <tr> <td>.XXX ± .005 [.13]</td> <td></td> </tr> </table> <p><b>CABLE LENGTH (L) TOLERANCES:</b></p> <table style="width: 100%; border: none;"> <tr> <td>L ≤ 12 [305]</td> <td>± 1 [25] / -0</td> </tr> <tr> <td>12 [305] &lt; L ≤ 60 [1524]</td> <td>± 2 [61] / -0</td> </tr> <tr> <td>60 [1524] &lt; L ≤ 120 [3048]</td> <td>± 4 [102] / -0</td> </tr> <tr> <td>120 [3048] &lt; L ≤ 300 [7620]</td> <td>± 6 [152] / -0</td> </tr> <tr> <td>300 [7620] &lt; L</td> <td>± 9% [L] / -0</td> </tr> </table> | .X ± .2 [5.08]   | FRACTIONS ± 1/32   | .XX ± .02 [.51] | ANGLES ± 1° | .XXX ± .005 [.13] |  | L ≤ 12 [305] | ± 1 [25] / -0 | 12 [305] < L ≤ 60 [1524] | ± 2 [61] / -0 | 60 [1524] < L ≤ 120 [3048] | ± 4 [102] / -0 | 120 [3048] < L ≤ 300 [7620] | ± 6 [152] / -0 | 300 [7620] < L | ± 9% [L] / -0 | <p style="text-align: center;"><b>L-com™</b><br/>an <b>INFINITE</b> brand</p> <p>50 High Street, West Mill, 3rd Floor, Suite #30<br/>North Andover, MA 01845 USA.<br/>Phone: 1.800.341.5266   1.978.682.6936<br/>Fax: 1.978.689.9484<br/>Website: www.L-com.com<br/>E-mail: CustomerService@L-com.com</p> | <p>THIRD-ANGLE PROJECTION</p> <p>THE INFORMATION AND DESIGN IN THIS DOCUMENT IS THE PROPERTY OF L-COM GLOBAL CONNECTIVITY. ALL RIGHTS RESERVED.</p> <p>SHEET 1 OF 1</p> <p>SCALE N/A</p> |
| .X ± .2 [5.08]  | FRACTIONS ± 1/32 |                    |                 |             |                   |  |              |               |                          |               |                            |                |                             |                |                |               |   |  |
| .XX ± .02 [.51]   | ANGLES ± 1°      |                    |                 |             |                   |  |              |               |                          |               |                            |                |                             |                |                |               |   |  |
| .XXX ± .005 [.13]   |                  |                    |                 |             |                   |  |              |               |                          |               |                            |                |                             |                |                |               |   |  |
| L ≤ 12 [305]  | ± 1 [25] / -0    |                    |                 |             |                   |  |              |               |                          |               |                            |                |                             |                |                |               |   |  |
| 12 [305] < L ≤ 60 [1524]  | ± 2 [61] / -0    |                    |                 |             |                   |  |              |               |                          |               |                            |                |                             |                |                |               |   |  |
| 60 [1524] < L ≤ 120 [3048]  | ± 4 [102] / -0   |                    |                 |             |                   |  |              |               |                          |               |                            |                |                             |                |                |               |   |  |
| 120 [3048] < L ≤ 300 [7620]   | ± 6 [152] / -0   |                    |                 |             |                   |  |              |               |                          |               |                            |                |                             |                |                |               |   |  |
| 300 [7620] < L  | ± 9% [L] / -0    |                    |                 |             |                   |  |              |               |                          |               |                            |                |                             |                |                |               |   |  |
| SIZE A  | CAGE CODE 43321  | ITEM NO. LCCA30573 | REV A           |             |                   |  |              |               |                          |               |                            |                |                             |                |                |               |   |  |