

1880-1900 MHz, 3 dBi, Stamped Metal DECT Embedded Antenna-50 Pack



## LCSMA1009-50PK

### Features

- High Efficiency
- Isotropic radiation patterns
- Linear polarization
- Ultra-Compact design
- Low loss material - Bare CP wire
- Extended operating temperatures
- On board mount
- Frequency stabilization
- 50-pack for easy buy

### Applications

- IoT, M2M, Telemetry
- Industrial/Commercial Equipment
- Digital Enhanced Cordless
- Telecommunications Standard (DECT)
- 3G compatibility
- Remote Technology / Monitoring
- Consumer Tracking
- Smart Home / Wearables /Devices
- Agriculture, healthcare, digital signage

### Description

The L-com LCSMA1009-50PK is a single band stamped metal antenna that ships on the same day as ordered. Our linear polarized antenna has a maximum frequency of 1900 MHz and a minimum frequency of 1880 MHz. This 50-pack stamped metal antenna has an overall length of 1.14 inches and a width of 0.6 inches.

L-com's LCSMA1009-50PK is a single band antenna operating from 1880 to 1900 MHz with a 3 dBi gain. The omni directional antenna has a maximum input VSWR of 2:1. This 50-pack stamped metal antenna has an impedance of 50 Ohms.

L-com has one of the largest in-stock collections of omni directional antennas with our wide selection of superior quality RF parts that ship same day. Make your online purchase right now to take advantage of our same-day shipping. For further information on similar products, our expert technical support and knowledgeable sales team can help you get the ideal 50-pack stamped metal antenna as per your requirements.

### Configuration

Design	Stamped Metal
Band Type	single
Radiation Pattern	Omni Directional
Polarization	Linear

### Electrical Specifications

Description	Minimum	Typical	Maximum	Units
Frequency Range	1,880		1,900	MHz
Input VSWR			2:1	
Impedance		50		Ohms
Gain		3		dBi
Input Power			1	Watt

Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications:  
[1880-1900 MHz, 3 dBi, Stamped Metal DECT Embedded Antenna-50 Pack LCSMA1009-50PK](#)

1880-1900 MHz, 3 dBi, Stamped Metal DECT Embedded Antenna-50 Pack



## LCSMA1009-50PK

### Mechanical Specifications

#### Size

Length	1.14 in [28.96 mm]
Width	0.6 in [15.24 mm]
Height	0.03 in [0.76 mm]

### Environmental Specifications

#### Temperature

Operating Range	-20 to +65 deg C
-----------------	------------------

**Compliance Certifications** (see [product page](#) for current document)

### Plotted and Other Data


Notes:

1880-1900 MHz, 3 dBi, Stamped Metal DECT Embedded Antenna-50 Pack from L-com has same day shipment for domestic and International orders. Our portfolio includes coaxial cable assemblies, connectors, adapters and custom products as well as lightning and surge protectors, NEMA rated enclosures, and an RF product line which includes antennas, amplifiers, passive, and active components.

The information contained within this document is accurate to the best of our knowledge and representative of the part described herein. It may be necessary to make modifications to the part and/or the documentation of the part in order to impliment improvements. L-com reserves the right to make such changes as required. Unless otherwise stated, all specifications are nominal. L-com does not make any representation or warranty regarding the suitability of the part described herein for any particular purpose, and L-com does not assume liability arising out of the use of any part or document.

1880-1900 MHz, 3 dBi, Stamped Metal DECT Embedded Antenna-50 Pack

L-com CAD Drawing



ZONE		REV		DESCRIPTION		DATE		CHANGED BY		APPROVED	
	A			INITIAL RELEASE		04/07/2023		HBAKKE		KHIETPAS	

REVISION	

**L-com**  
an INFINITE brand  
Website: www.L-com.com  
Phone: 1.800.341.5266 | 1.978.682.6936

INTERPRET ALL DIMENSIONS AND TOLERANCES PER ASME Y.14.5  
SCALE NONE 1 OF 1 SHEET

UNLESS OTHERWISE SPECIFIED, LEADING DIMENSIONS ARE INCHES DIMENSIONS IN [ ] ARE MILLIMETERS  
TOLERANCES: X = +.2 [5] FRACTIONS XX = +.02 [5] +.132 ANGLES ± 1° XXX = ±.005 [13] CABLE LENGTH TOLERANCES: ≤ 12 [305] ± .001 [25] / -0 > 12 [305] ≤ 60 [1524] ± .001 [25] / -0 > 60 [1524] ≤ 120 [3048] ± .001 [25] / -0 > 120 [3048] ≤ 300 [7620] ± .001 [25] / -0 > 300 [7620] ± .001 [25] / -0

DESCRIPTION: 1880 - 1900 MHz 3 dBi, Stamped Metal Antenna - 50 Pack  
SIZE: A CAGE CODE: 43321 DRAWN BY: HBAKKE ITEM NO.: LCSMA1009-50PK  
REV: A

THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF INFINITE ELECTRONICS, INC. ANY REPRODUCTION IN PART OR WHOLE WITHOUT THE WRITTEN PERMISSION OF INFINITE ELECTRONICS, INC. IS PROHIBITED. THESE COMMODITIES, TECHNOLOGY OR SOFTWARE WERE EXPORTED FROM THE UNITED STATES IN ACCORDANCE WITH THE EXPORT ADMINISTRATION REGULATIONS. DIVERSION CONTRARY TO U.S. LAW PROHIBITED.

T-Rev: 02