


14x12x7 Inch Weatherproof Enclosure with 802.3af (PoE) Power-Over-Ethernet Interface and Solid State Fan Controller - Model: NB141207-40FSAF

Applications

- Remote Wireless LAN WiFi equipment installations
- Indoor and outdoor installations
- Hot temperature environments
- Rapid deployment installations
- Corrosive environments

Features

- Molded fiberglass reinforced polyester (FRP) industrial enclosure with integral mounting flange
- Stainless steel quick release latches with padlock hasps
- NEMA Type 3R, 3RX / IP24 rated
- Fully gasketed raised vented lid with removable filters
- Aluminum mounting plate with 802.3af compatible Power-Over-Ethernet (PoE) interface with CAT5 surge protection & solid state controlled cooling system



Description

Start with the Box...

The box is a rugged weatherproof enclosure that is ideal for both indoor and outdoor applications. Constructed from molded fiberglass reinforced polyester, it is well suited for high temperature or corrosive environments. The mounting flange allows it to be wall mounted as well as on a flat surface. The raised lid features a stainless steel continuous hinge and stainless steel quick release latches with padlock hasps. The raised lid is fully gasketed. The enclosure material is UV stabilized and comes in machine tool gray.

Mounting Plate

The aluminum mounting plate has provisions to mount WLAN equipment from Cisco®, Symbol®, D-Link®, HyperLink and more. With the optional HGX-AMOUNT02 bracket a wide array of HyperLink Amplifiers, Power-Over-Ethernet products and Power Supplies can be mounted as well. Two of these brackets can be mounted side by side. Also available is the HGX-NMOUNT03 Universal Mounting Shelf that can be attached to the mounting plate and can accommodate additional equipment to be placed in the enclosure.

Power-Over-Ethernet (PoE)

The Mounting Plate features an 802.3af compatible PoE interface to power the thermostatically controlled cooling fan. The fan can be powered by the majority of 802.3af compliant Switches, Midspans or injectors operating in Mode A or B with normal or inverted polarity. The caveat is the fan requires its own PoE interface, usually from a spare port on the Switch or Midspan. At least two Ethernet cables must be pulled to the enclosure, one to power the fan, and one or more for the equipment. This eliminates the need for a separate passive PoE injector as required by other L-com PoE enclosures.

Cooling Fan

The NB141207-40FSAF comes with a high CFM 48 VDC cooling fan installed. The high airflow, low noise fan featuring sealed ball bearings, evacuates heat from the top of the enclosure. The fan is controlled by L-Com's exclusive solid state fan controller. The standard unit has a fan turn-on temperature of +90° F. The controller features improved temperature set point accuracy and can be factory modified for other temperature set points. No extra room for the controller is required since it is mounted underneath the plate.



Lightning Protection

For optimum protection, L-com recommends that surge protection be added to the enclosure. L-com offers a wide array of Coaxial and Data Line surge protectors that can be mounted in the enclosure. The unit can accept up to two optional bulkhead-mount N-Type lightning protectors to protect the coaxial cable runs. Data line protectors can be mounted to the mounting plate.

Specifications

Enclosure Material	Fiberglass Reinforced Polyester
Enclosure Color	Machine Tool Gray
Mounting Plate Material	.10 in. (2.5mm) Thick Anodized Aluminum
Mounting Plate Dimensions	12.7 x 10.8 in. (32.2 x 27.4 cm)
Weight	12.3 lbs (5.6 kg)
Outside Dimensions H x W x D (max)	15.3 x 13.3 x 8.7 in. (389 x 338 x 221 mm)
Inside Dimensions H x W x D	14.0 x 12.0 x 7.3 in. (356 x 305 x 186 mm)
Flame Rating	UL 94-5V
Cable Feed	1/2 in. Cable Conduit Connector
RoHS Compliant	Yes
Ratings	NEMA Type 3R, 3RX / IP24

Temperature Controller Specification	
Fan Set Point Temperature	+32°C (+90°F)
Hysteresis Window	5°C (9°F)
Power Consumption	7 Watts
Contact us for custom fan set points	

Application Diagram

